



Search:

Parametric Search | Replacement Parts Search | View Cart  | My Account | Log In

Home > [Amplifiers and Comparators](#) > [Comparators](#)

 [Contact Us](#) |  [Print this Page](#) |  [Email this Page](#)

[Amplifiers and Comparators](#)

[Buffer Amplifiers](#)

[Comparators](#)

[Current Sense Amplifiers](#)

[Differential Amplifiers](#)

[Fiber Optic Limiting](#)

[Amplifiers](#)

[Fiber Optic Transimpedance](#)

[Amplifiers](#)

[Gain Control Amplifiers](#)

[Instrumentation Amplifiers](#)

[Isolation Amplifiers](#)

[LCD Drivers](#)

[Line Drivers](#)

[Operational Amplifiers \(Op Amps\)](#)

[Variable Gain Amplifiers](#)

[All Product Categories](#)

[Amplifiers and Comparators](#)

[Analog to Digital](#)

[Converters](#)

[Digital to Analog](#)

[Converters](#)

[Embedded Processing and](#)

[DSP](#)

[Analog Microcontrollers](#)

[Audio/Video Products](#)

[Broadband Products](#)

[Interface](#)

[MEMS and Sensors](#)

[Power and Thermal](#)

[Management](#)

[References](#)

CMP04 - Quad Low Power, Precision Comparator

[Data Sheets](#)

 [Rev D](#), (03/2003)
pdf, 282K
 [EMAIL PDF](#)

[Application Notes](#)

[Evaluation Boards](#)

[Price, Packaging,
and Availability](#)

Product Description

Four precision independent comparators comprise the CMP04. Performance highlights include a very low offset voltage, low output saturation voltage and high gain in a single supply design. The ...[More](#)

Features

- High Gain: 200 V/mV Typ
 - Single- or Dual-Supply Operation
 - Input Voltage Range Includes Ground
 - Low Power Consumption (1.5 mW/Comparator)
 - Low Input Bias Current: 100 nA Max
 - Low Input Offset Current: 10 nA Max
- Low Offset Voltage: 1 mV Max
 - Low Output Saturation Voltage: 250 mV @ 4 mA
 - Logic Output Compatible with TTL, DTL, ECL, MOS, and CMOS
 - Directly Replaces LM139/LM239/LM339 Comparators

Price, Packaging, and Availability

CMP04 Model Options

Model	Status	Package	Pins	Temp Range	Price* (1000-4999)	Available	Samples Cart	Purchase Cart
5962-8990403CA	Obs	CERDIP GLASS SEAL	14	Mil	-	-	Contact ADI	Contact ADI
CMP04BY/883C	Obs	CERDIP GLASS SEAL	14	Mil	-	-	Contact ADI	Contact ADI
CMP04FP	Obs	PLASTIC DIP	14		-	-	Contact ADI	Contact ADI
CMP04FS	Prodn	14 ld SOIC	14		\$4.75	9/24/2004	Add to Cart	Add to Cart
CMP04FS-REEL	Prodn	14 ld SOIC	14	Ind	-	4/29/2005	Contact ADI	Add to Cart
CMP04NBC	Obs	CHIPS OR DIE	-	TBD	-	-	Contact ADI	Contact ADI

New Comparators

[ADCMP561](#) - Dual High Speed PECL Comparator 16 - Lead QSOP

Design Tools

[AD8561 SPICE Macro-Model](#)
[AD8564 SPICE Macro-Model](#)
[AD8598 SPICE Macro-Model](#)
[More...](#)

Related Tech Info

[Technical Articles](#)
[Application Notes](#)

Resources

[Selection Tables](#)
[Product Highlights](#)
[Solutions Bulletins](#)
[More...](#)

[RF/IF Components](#)
[Switches/Multiplexers](#)
[Wireless Products](#)
[Other Linear](#)
[Other](#)

The pricing listed here is provided only for budgetary purposes as recommended list price in U.S. Dollars in the United States ex factor per unit for the stated volume. Pricing displayed for Evaluation Boards and Kits is based on 1-piece pricing.

[View Sales and Distribution Offices](#)

[View
Samples
Cart](#)

[View
Purchase
Cart](#)

Suggested Complementary Products

Signal Chains

Visit our [interactive signal chains](#) for more complementary products

Find Similar Products

Part#	Prop Delay (ns) typ	# Per Pkg	Supply Current (mA)	Voltage Supply (V)	No of Supplies	Input Range (V)	Logic Output	Prog. Int. Hyst	Latch Enable Pin	Package	Min Pulse Width	Price* (1000-4999)
ADCMP370	2000	1	0.005	2.25 to 5.5	1	0 to 22V	TTL/CMOS	X	-	5-Lead SC-70	5µs	\$0.28
ADCMP371	2000	1	0.005	2.25 to 5.5	1	0 to 22V	TTL/CMOS	X	-	5-Lead SC-70	5µs	\$0.28
ADCMP566	0.3	2	83	5, -5.2	2	-2 to 3V	ECL	-	X	32-Lead LFCSP	200ps	\$3.60
ADCMP551	0.75	2	16	-	1	-0.2 to Vcc-2V	PECL	-	X	16-Lead QSOP	750ps	-
AD8561	45	1	-	3 to 10	-	-5.0V to +3.0V	Diff/TTL	-	X	-	-	\$1.76
ADCMP552	0.75	2	16	-	1	-0.2 to Vcc-2V	PECL	X	X	20-Lead QSOP	750ps	-
AD8611	5.5	1	-	3 to 5	-	-0.2 to Vcc-2V	Diff/TTL	-	X	-	-	\$2.00
ADCMP553	0.75	1	8	-	1	-0.2 to Vcc-2V	PECL	-	X	8-Lead MSOP	750ns	-
AD96685	6	-	-	-	-	-2.5V to +5.0V	Diff/ECL	-	X	-	-	\$3.05
ADCMP561	0.75	2	23	5, -5.2	2	-2 to 3V	PECL	-	X	16-Lead LFCSP	700ps	\$2.40
ADCMP350	2000	1	0.015	2.25 to 5.5	1	0 to 22V	TTL/CMOS	X	-	4-Lead SC-70	-	-

ADCMP562	0.75	2	23	5, -5.2	2	-2 to 3V	PECL	X	X	16-Lead LFCSP	700ps	\$3.00
ADCMP352	2000	1	0.015	2.25 to 5.5	1	0 to 22V	TTL/CMOS	X	-	4-Lead SC-70	25µs	-
ADCMP563	0.75	2	23	5, -5.2	2	-2 to 3V	ECL	-	X	16-Lead QSOP	700ps	\$2.40
ADCMP354	2000	1	0.015	2.25 to 5.5	1	0 to 22V	TTL/CMOS	-	-	4-Lead SC-70	25µs	-
ADCMP564	0.75	2	23	5, -5.2	2	-2 to 3V	ECL	X	X	20-Lead QSOP	700ps	\$3.00
ADCMP356	2000	1	0.015	2.25 to 5.5	1	0 to 22V	TTL/CMOS	X	-	4-Lead SC-70	-	-
ADCMP572	0.15	1	44	-	1	-0.2 to V _{cc} -2V	CML	X	X	16-Lead LFCSP	80ps	-
ADCMP567	0.3	2	83	5, -5.2	2	-2 to 3V	PECL	-	X	32-Lead LFCSP	200ps	\$3.60
ADCMP573	0.15	1	66	-	1	-0.2 to V _{cc} -2V	PECL	X	X	16-Lead LFCSP	80ps	-
AD8564	8	4	-	+/- 5	-	0 to 2.75V	TTL/CMOS	-	-	-	-	\$3.69
ADCMP580	0.15	1	50	-	2	-2 to 3V	CML	X	X	16-Lead LFCSP	80ps	-
AD96687	-	-	-	-	-	-2.5V to +5.0V	-	-	-	-	-	\$3.05
ADCMP581	0.15	1	34	-	2	-2 to 3V	ECL	X	X	16-Lead LFCSP	80ps	-
ADCMP353	2000	1	0.015	2.25 to 5.5	1	0 to 22V	TTL/CMOS	X	-	4-Lead SC-70	-	-
ADCMP582	0.15	1	75	-	2	-2 to 3V	PECL	X	X	16-Lead LFCSP	80ps	-
ADCMP357	2000	1	0.015	2.25 to 5.5	1	0 to 22V	TTL/CMOS	X	-	4-Lead SC-70	-	-
AD8612	5.5	2	-	3 to 5	-	0 to V _{cc} -2	Diff/TTL	-	X	-	-	\$3.37
ADCMP351	2000	1	0.015	2.25 to 5.5	1	0 to 22V	TTL/CMOS	X	-	4-Lead SC-70	25µs	-
ADCMP355	2000	1	0.015	2.25 to 5.5	1	0 to 22V	TTL/CMOS	X	-	4-Lead SC-70	-	-
AD790	45	1	-	+/-15	-	-V _s to V _s -2V	Open Collector	-	X	-	-	\$3.67
CMP04	-	-	-	-	-	0 to V+ -1.5	-	-	-	-	-	\$4.75

CMP401	-	-	-	-	-	-5.0V to +4.0V	-	-	-	-	-	\$3.35
CMP402	-	-	-	-	-	-5.0V to +4.0V	-	-	-	-	-	\$3.37
ADCMP565	0.3	2	83	5, -5.2	2	-2 to 3V	ECL	-	X	20-Lead QSOP	200ps	\$4.90

* The pricing listed here is provided only for budgetary purposes as recommended list price in U.S. Dollars in the United States ex factor per unit for the stated volume. Pricing displayed for Evaluation Boards and Kits is based on 1-piece pricing.

[Privacy/Security](#)

[myAnalog](#)

[Contact ADI](#)

[Site Map](#)

[Registration](#)

[Technical Support](#)

[Terms of Use](#)

© 1995-2004 Analog Devices, Inc. All Rights Reserved
This site is **optimized for IE 6.0+, NN 7.1, and Mozilla.**