



10		9		8		7		6		5		4		3		2		19003	
MATERIAL # LOOSE PCS	MATERIAL # CONTINUOUS	MATERIAL # TAPE MNT	ENGINEERING PART NO.	INS. COLOR	WIRE RANGE AWG	FITS MALE TAB SIZE		STOCK THICK REF	"A" MAX	"B" MIN. (B1)	"C" MAX.	"D" MWID	"E" MAX.	"H" ±.02/0.5 (B1)					
I90030008	I90030009	I90030010	AA-2201X	SALMON	22-18	.250x.032 (6.35x0.81)		.016 (0.4)	.94 /23.9	.056/1.42	.380 /9.66	.230 /5.84	.180 /4.58	.56/14.2					
NOTE 5	NOTE 5	NOTE 5	AA-2213X	SALMON	22-18	.205x.020 (5.21x0.51)		.016 (0.4)	.86 /21.8	.056/1.42	.316 /8.03	.230 /5.84	.160 /4.07	.60/15.3					
NOTE 5	NOTE 5	NOTE 5	AA-2214X	PINK	22-18	.205x.032 (5.21x0.81)		.016 (0.4)	.86 /21.8	.056/1.42	.316 /8.03	.230 /5.84	.160 /4.07	.60/15.3					
I90030014	I90030015	I90030016	AA-2202X	SALMON	22-18	.187x.020 (4.75x0.51)		.016 (0.4)	.86 /21.8	.056/1.42	.316 /8.03	.230 /5.84	.160 /4.07	.60/15.3					
I90030021	I90030022	I90030023	AA-2203X	PINK	22-18	.187x.032 (4.75x0.81)		.016 (0.4)	.86 /21.8	.056/1.42	.316 /8.03	.230 /5.84	.160 /4.07	.60/15.3					
I90030027	I90030028	I90030029	AA-2204X	SALMON	22-18	.110x.020 (2.79x0.51)		.012 (0.3)	.86 /21.8	.056/1.42	.230 /5.85	.230 /5.84	.150 /3.81	.61/15.5					
I90030033	I90030034	I90030035	AA-2205X	PINK	22-18	.110x.032 (2.79x0.81)		.012 (0.3)	.86 /21.8	.056/1.42	.230 /5.85	.230 /5.84	.150 /3.81	.61/15.5					
I90030047	I90030048	I00030049	BB-2206X	BLUE	16-14	.250x.032 (6.35x0.81)		.016 (0.4)	.94 /23.9	.079/2.00	.380 /9.66	.260 /6.60	.180 /4.58	.56/14.2					
NOTE 5	NOTE 5	NOTE 5	BB-2215X	BLUE	16-14	.205x.020 (5.21x0.51)		.016 (0.4)	.86 /21.8	.079/2.00	.316 /8.03	.260 /6.60	.170 /4.32	.60/15.3					
NOTE 5	NOTE 5	NOTE 5	BB-2216X	AQUA	16-14	.205x.032 (5.21x0.81)		.016 (0.4)	.86 /21.8	.079/2.00	.316 /8.03	.260 /6.60	.170 /4.32	.60/15.3					
I90030053	I90030054	I90030055	BB-2207X	BLUE	16-14	.187x.020 (4.75x0.51)		.016 (0.4)	.86 /21.8	.079/2.00	.316 /8.03	.260 /6.60	.170 /4.32	.60/15.3					
I90030059	I90030060	I90030061	BB-2208X	AQUA	16-14	.187x.032 (4.75x0.81)		.016 (0.4)	.86 /21.8	.079/2.00	.316 /8.03	.260 /6.60	.170 /4.32	.60/15.3					
I90050010	I90050014	I90050015	C-2265	YELLOW	12-10	.250x.032 (6.35x0.81)		.018 (0.5)	1.04 /26.4	.144/3.65	.380 /9.66	.275 /6.98	.290 /7.37	.51/12.9					



CUSTOMER DRAWING

- 1. MATERIAL: BRASS
- 2. FINISH: ELECTRO-TIN PLATING
- 3. INSULATION: NYLON
- 4. MWID= MAXIMUM WIRE INSULATION DIAMETER
- 5. CONSULT FACTORY FOR AVAILABILITY
- 6. PART IS ROHS COMPLIANT.

ID, H TOLERANCES EC NO: WNA2011-0433 DRAWN:THRODAHL 2011/02/28 CHKD: JMACNEIL 2011/02/28 APPR: JMACNEIL 2011/03/03 B1	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY RCM	DATE 1994/06/17	FULLY INSULATED QUICK DISCONNECTS EXPANDED FLARE			
			4 PLACES	± ---	± ---	CHECKED BY JM	DATE 1994/06/17				
			3 PLACES	± ---	± ---	APPROVED BY FP	DATE 1994/06/17				
			2 PLACES	± ---	± ---	MOLEX MOLEX INCORPORATED					
			1 PLACE	± ---	± ---					MATERIAL NO. SEE CHART	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								