


THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	RoHS Compliancy	06-01-06	DP



NOTES:

MATERIAL:

HOUSING: THERMOPLASTIC
TERMINAL: COPPER ALLOY

RATING:

UL,CSA: 15A 250V AC
VDE: 10A 250V AC

INSULATION RESISTANCE: OVER 100M OHM 500V DC
DIELECTRIC STRENGTH: 2000V AC ONE MINUTE

APPROVALS: UL,CSA,VDE
PANEL THICKNESS: 0.8~1.5mm
RoHS COMPLIANT

CONTROLLED

2	Contact PIN Bronze Strip t=0.8mm Tin-Plated	3
1	Body Insulator PC or NY Black Color	1
Qualtek Electronics Corp. PPC DIVISION		
Dim range (mm)	Tolerance +/- (mm)	Part Number: 716W-X2/02 RoHS Compliant
0-1	0.15	Description: AC RECEPTACLE
1-6	0.20	
6-18	0.30	UNIT: mm REV. B
18-50	0.50	
50-120	0.70	Drawn / Date
120-250	0.90	Checked / Date
250-500	1.20	Approved / Date
B.ZHANG 07-14-05		JJH / 07-14-05

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Qualtek:](#)

[716W-X2/02](#)