



DWG NO.		CAA622-01000		SH	REV
				2	B
REV	SCR NO.	DESCRIPTION	BY	DATE	APPROVED
		SEE SHEET 1			

NOTES:

- 1
- CONTACT MATERIALS:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC, BLACK, UL 94V-0
CONTACT: HIGH PERFORMANCE COPPER ALLOY
- 2
- CONTACT PLATING:
PRESS-FIT TAIL: 0.5 - 2.0µm PURE TIN OVER NICKEL
SEPARABLE INTERFACE: 0.76µm MIN GOLD OVER NICKEL
- 3
- PRODUCT SPECIFICATION: TB-2162
- 4
- APPLICATION SPECIFICATION: TB-2163
- 5
- PRODUCT MARKING, (PART NUMBER & LOT CODE) ON THIS SURFACE
- 6
- MINIMUM NOMINAL PCB THICKNESS: 1.6mm
- 7
- REFER TO CUSTOMER DRAWING CAA-PCB-5000 FOR INFORMATION REGARDING
PCB LAYOUT,DRILL,AND FINISH DIAMETERS OF POWER AND GUIDE MODULES RELATIVE TO SIGNAL MODULES.





INTERPRET PER ANSI Y14.5

CODE IDENT 31413

TOLERANCES		DWN 01/30/07 HCL-BS	Amphenol TCS A Division of Amphenol Corporation 44 Simon Street, Nashua, N.H. 03060 (603) 879-3000		
.00	± 0.2	CHK 01/30/07 K.LEBLANC			
.000	± 0.1	APVD 01/30/07 K.LEBLANC			
.0000	± 0.05				
ANGLES	± 2°				
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS			TITLE AIRMAX VS RA HEADER ASSY POWER,PRESS-FIT,2X2 POS,12MM		
CUSTOMER USE DRAWING			PART NO. AA622-01000		REV A
			DRAWING NO. CAA622-01000		REV B
			SIZE B	SCALE 3:1	SHEET 2 OF 2

DWG NO.

CAA622-01000

SH

2

REV

B