

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE		DIMENSIONS in. [mm]				
	ENGLISH	METRIC	L ± [0,8]	W ± [0,3]	C ± [0,5]	M ± [0,8]	H ± [0,3]
PM2-3F*	--	M3	.63 [16,00]	.23 [5,84]	.22 [5,59]	.49 [12,45]	.13 [3,30]
P14-6F	#6	M3,5	.63 [16,00]	.28 [7,11]	.20 [5,08]	.49 [12,45]	.15 [3,81]
P14-6FN	#6	M3,5	.63 [16,00]	.24 [6,10]	.20 [5,08]	.49 [12,45]	.15 [3,81]
P14-8F	#8	M4	.69 [17,53]	.31 [7,87]	.23 [5,84]	.53 [13,46]	.17 [4,32]
P14-10F	#10	--	.71 [18,03]	.34 [8,64]	.25 [6,35]	.55 [13,97]	.20 [5,08]
P14-10FN	#10	--	.71 [18,03]	.31 [7,87]	.25 [6,35]	.55 [13,97]	.20 [5,08]
PM2-5F*	--	M5	.71 [18,03]	.34 [8,64]	.27 [6,86]	.55 [13,97]	.21 [5,33]
P14-14F	1/4"	M6	.88 [22,35]	.44 [11,18]	.33 [8,38]	.63 [16,00]	.27 [6,86]

*NOT CSA CERTIFIED

NOTES:

1. UL LISTED & CSA CERTIFIED FOR:

- A. #18-14 AWG [1,0-2,5 mm²] SOLID OR STRANDED COPPER WIRE
- B. 302°F [150°C] MAX OPERATING TEMPERATURE
- C. 2000 VOLTS MAX

2. SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES

3. MATERIAL:

- A. STAMPING: .032" [0,8] THK COPPER, TIN PLATED

4. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT


5. WIRE STRIP LENGTH: 9/32" ^{+1/32}₋₀ [7,1mm ^{+0,8}₋₀]

UL & CSA TOOLS

CT-100A
CT-200
CT-600-A (CT-570CH)
CT-1570
CT-2500 (CT-2570CH)

PANDUIT APPROVED TOOLS

CT-160
CT-260



TITLE				#18-14 BARREL NON-INSULATED FORK			
ITEM REVISION NAME				CUSTOMER DRAWING			
N41255BA/11				PANDUIT™			
DATASET FILE NAME				N41255BA_DC/11A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL:			
.X ± .XXX ± .XX ± ANGLES ±				SEE NOTES			
THIRD ANGLE PROJECTION				DRAWING NUMBER:			
A41255				SHEET 1 OF 1			
REV				DATE			
BY				CHK			
APR				DESCRIPTION			
ECN				SCALE			
MS				NONE			
SIZE				A			