

Magnecraft

191 Waukegan Rd, Ste 206

Northfield, IL 60093-2743



Phone: (847)441-2526**Fax:** (847)441-2522**Email:** relays@magnecraft.com**Item # W117SIP-3, Miniature Reed PCB Relay / SPST-NO, 0.5 Amp Rated****QUOTE****Miniature Reed PCB Relay / SPST-NO, 0.5 Amp Rated**

Ø

Magnecraft SIPS and DIPS can withstand a lead-free solder re-flow process, making pin-thru-paste applications possible.

Designed for simple routing on PCB

Requires only 0.500 spacing from adjacent relays

[CONTACT CHARACTERISTICS](#) · [COIL CHARACTERISTICS](#) · [PERFORMANCE CHARACTERISTICS](#) · [ENVIRONMENT](#) · [PRODUCT CERTIFICATIONS](#)**CONTACT CHARACTERISTICS**

Current Rating	0.5 A
Contact Configuration	SPST-NO
Contact Materials	Rhodium
Switching Voltage (AC)	120 VAC
Switching Voltage (DC)	200 VDC

COIL CHARACTERISTICS

Coil Resistance	1000 Ohm
Nominal Input Voltage	12 VDC

Operating Range - % of Nominal (DC)	80 to 110 %
Average Consumption (DC)	0.29 W
Drop-out Voltage Threshold (DC)	10 %

PERFORMANCE CHARACTERISTICS

Electrical Life, Operations at Rated Current (Resistive)	50000000
Mechanical Life, Unpowered	100000000
Operating Time (Response Time)	0.45 ms
Dielectric Strength - Between Poles (AC)	150 V(rms) 500 V(rms)

ENVIRONMENT

Ambient Air Temperature around the Device - Storage	-40 to +85 °C
Ambient Air Temperature around the Device - Operation	-40 to +55 °C
Vibration Resistance - Operational	20 g-n at 10-200 Hz
Shock Resistance	50 g-n

PRODUCT CERTIFICATIONS

Agency Approvals	RoHS
------------------	------