


1 | 2


3 |

4

	DESCRIPTION	PART NUMBER	10012838-001LF	10012838-004LF	10012838-003LF	REMARK
			Q'TY	Q'TY	Q'TY	
1	TOP COVER	10017335-001	1	1	N/A	WITH "M" LOGO
		10017335-002	N/A	N/A	1	WITHOUT "M" LOGO
2	17P DATA PLUG ASS'Y	10028885-001LF	1	1	1	
3	BOTTOM COVER	10017334-001	1	1	1	
REMARK				Special package		



10012838-001LF/001/004LF



10012838-003LF

Notes:

- The housing of 10028885-xxx will withstand exposure to 260°C peak temperature for 10 seconds in a convection, infra red vapor phase reflow oven
- 10012838-001LF meets European union directives and other country regulations as described in GS-22-008
- Lead free label on the carton of 10028885-001LF per GS-14-920
- Plating specification for terminal:
1.2 um minimum nickel all over followed by:
Contact side: 0.8 um minimum Au
Solder tail side: 2.5 ~ 10 um pure Sn for 10028885-001LF/003LF



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	FCI			
litr	ecr no	dr	date				www.fciconnect.com			
C	T03-0322	M W	08/06/03	linear	.X ± 0.15	projection	title			
D	T04-0217	M W	05/19/04		.XX ± 0.10		17P DATA PLUG ASS'Y			
E	pg04-0077	P M	10/12/04	angles	.XXX ±					
F	pg04-0096	P M	12/16/04	dr	.0° ± 2°	MM				
G	pg05-0098	P M	07/11/05	enrg		scale	product family		MOBILE I/O	code
H	pg06-0452	C L	11/07/06	chr		2:1	size		dwg no	sheet
J	pg07-0027	C L	01/22/07	appd			A4		10012838	1 of 4
sheet index	revision sheet	J G	C C							
		1 2	3 4							

1 | 2

3 |

4






Notes:

1. The housing of 10028885-xxx will withstand exposure to 260°C peak temperature for 10 seconds in a convection, infra red vapor phase reflow oven
2. 10012838-002LF meets European union directives and other country regulations as described in GS-22-008
3. Lead free label on the carton of 10028885-002LF per GS-14-920
4. Plating specification for terminal:
1.2 um minimum nickel all over followed by:
Contact side: 0.8 um minimum Au
Solder tail side: 2.5 ~ 10 um pure Sn for 10028885-002LF



	DESCRIPTION	PART NUMBER	10012838-002LF
			Q'TY
1	TOP COVER	10017335-001	1
2	6P DATA PLUG ASS'Y	10028885-002LF	1
3	BOTTOM COVER	10017334-001	1





mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		FCI www.fciconnect.com				
ltr	ecn no	dr	date	linear	.X ± 0.15			projection 	title 17P DATA PLUG ASS'Y				
C					.XX ± 0.10								
					.XXX ±								
				angles	.0° ± 2°				product family MOBILE I/O				
				dr	MAGGIE WU	05/22/03							
				enr	LEIF SHEN	05/22/03							
				chr	PAUL WANG	05/22/03							
				appd	JENN TSAO	05/22/03							
sheet index		revision sheet						scale 2:1	A4	10012838			

cage code
22526

PART NUMBER 10012838-002LF



DETAIL J
SCALE 3:1



DETAIL H
SCALE 3:1

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	FCI		
ltr	ecn no	dr	date	linear	.X ± 0.15 .XX ± 0.10 .XXX ± .0" ± 2"		www.fciconnect.com		
C				angles		projection	title		
				dr	MAGGIE WU 05/22/03	MM	17P DATA PLUG ASS'Y		
				enrg	LEIF SHEN 05/22/03		product family MOBILE I/O		code
				chr	PAUL WANG 05/22/03	scale	size dwg no		—
				appd	JENN TSAO 05/22/03		A4 10012838		sheet 4 of 4
sheet index	revision sheet								

cage code
22526