




LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			H1	REVISED PER ECO-15-010569	23JUL2015	NK	MM



- | | |
|---|---|
| 1 | ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS |
| 2 | TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD |
| 3 | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING |
| 4 | POINT OF MEASUREMENT FOR PLATING THICKNESS |
| 5 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |



		3.984	3.900	39	80	4-102977-0	
5 OBSOLETE		3.884	3.800	38	78	3-102977-9	
		3.784	3.700	37	76	3-102977-8	
		3.684	3.600	36	74	3-102977-7	
		3.584	3.500	35	72	3-102977-6	
5 OBSOLETE		3.484	3.400	34	70	3-102977-5	
		3.384	3.300	33	68	3-102977-4	
		3.284	3.200	32	66	3-102977-3	
5 OBSOLETE		3.184	3.100	31	64	3-102977-2	
		3.084	3.000	30	62	3-102977-1	
		2.984	2.900	29	60	3-102977-0	
		2.884	2.800	28	58	2-102977-9	
		2.784	2.700	27	56	2-102977-8	
		2.684	2.600	26	54	2-102977-7	
5 OBSOLETE		2.584	2.500	25	52	2-102977-6	
		2.484	2.400	24	50	2-102977-5	
5 OBSOLETE		2.384	2.300	23	48	2-102977-4	
		2.284	2.200	22	46	2-102977-3	
		2.184	2.100	21	44	2-102977-2	
5 OBSOLETE		2.084	2.000	20	42	2-102977-1	
		1.984	1.900	19	40	2-102977-0	
5 OBSOLETE		1.884	1.800	18	38	1-102977-9	
		1.784	1.700	17	36	1-102977-8	
		1.684	1.600	16	34	1-102977-7	
		1.584	1.500	15	32	1-102977-6	
		1.484	1.400	14	30	1-102977-5	
		1.384	1.300	13	28	1-102977-4	
		1.284	1.200	12	26	1-102977-3	
		1.184	1.100	11	24	1-102977-2	
		1.084	1.000	10	22	1-102977-1	
		.984	.900	9	20	1-102977-0	
	5 OBSOLETE		.884	.800	8	18	102977-9
			.784	.700	7	16	102977-8
		.684	.600	6	14	102977-7	
		.584	.500	5	12	102977-6	
		.484	.400	4	10	102977-5	
		.384	.300	3	8	102977-4	
		.284	.200	2	6	102977-3	
		.184	.100	1	4	102977-2	
		.084	—	—	2	102977-1	
		C	B	A	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL		150CT87				TE Connectivity			
		CHK T. CLARK		200CT87							
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T. CLARK		200CT87		NAME			
		1 PLC ± —		PRODUCT SPEC		HEADER ASSY, MOD II, BREAKAWAY, DOUBLE ROW, .100X.100 CL, VERTICAL, WITH .025 SQ POSTS					
		2 PLC ± —		—							
		3 PLC ± .005		APPLICATION SPEC							
		4 PLC ± —		—							
ANGLES		—		—		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL		FINISH POST:		WEIGHT		A2 00779		C-102977		—	
HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK POST: COPPER ALLOY		.000030 GOLD ON CONTACT AREA, 500100—000050 MATTE TIN—LEAD ON SOLDER TAIL ALL OVER .000500NICKEL						SCALE 4:1		SHEET 1 of 1	REV H1
CUSTOMER DRAWING											