



DRAWING MADE IN THIRD ANGLE PROJECTION
THIS DRAWING IS UNPUBLISHED.
BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC				DIST				REV			
G				14				D			
P				F				D			
ZONE				LTR				REVISED & REDRAWN PER 0720-0303-93			
DATE				APPRO				8-30-93			



METRIC
DIMENSIONS LISTED IN mm [INCHES]

NOTE:
1. WIRE INSULATION DIA
10.54[.415] MAX



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C		DO NOT SCALE PRINT. DIMENSIONS SPECIFIED UNLESS SPECIFIED TOLERANCES ON: 2 DEC DEC 2 0.20(.008) 3 DEC DEC 2 0.25(.010) ANGLES 2 2		DR 8-30-93 S.S. GOLDER		QTY 100		LOOSE PC		324659	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600 V MAX		CIRCUULAR MIL AREA: 10.54-16.77mm² (20,800-39,100)		FINISH TIN PLATE PER MIL-T-10727		APPLICATION SPEC		SIZE 00779 CAGE CODE 00779 DRAWING NO 324659	
FOR APPLICATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		STRANDED		MATERIAL COPPER PER ASTM B-152 MILN, COLOR: BLUE		WEIGHT		SCALE		SHEET 1 OF 1	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AND THE COMPANY'S POLICY ON DOCUMENTATION SHOULD BE CONSULTED FOR THE LATEST REVISION.		PRODUCT SPEC		N/A		N/A		N/A	

AMP 1470-15 REV 3-92
10 JAN 1994 15:17:30 AMP10744 <UJ128A>DEPT1132>AMP10744>U. TERMINL-SPLICE-CUST
CUSTOMER DRAWING