



★★★★ Traditional Cutting Tweezers

**Super Sharp Flush Cutting Blades
Made In Switzerland**

High-Grade Carbon Steel

15A-GW ★★★★★ 4 ½"

General purpose cutting tweezers with ESD safe epoxy handle for use on .010" or smaller soft wire.

15A-GW-PB

Parallel Cutting Blades

15A-GW-OF

Optimum Flush Cutting Blades

A:	0.393	(10 mm)
B:	4.500"	(115 mm)
C:	0.215"	(5.5 mm)
D:	0.375"	(9.5 mm)
E:	70°	



NEW suffix "-OF"
Special **Optimum Flush**
available on select models.

15A-RW ★★★★★ 4 ½"

Fine round tip cutting tweezers with ESD safe epoxy handle for use on .010" or smaller soft wire.

15A-RW-OF

Same as above with Optimum Flush Cutting Blades

A:	0.393"	(10 mm)
B:	4.500"	(115 mm)
C:	0.095"	(2.5 mm)
D:	0.200"	(5.2 mm)
E:	70°	



15A-C ★★★★★ 4 ½"

Short fine blade cutting tweezers with ESD safe epoxy handle. Cutting capacity .010" soft wire.

A:	0.393"	(10 mm)
B:	4.500"	(115 mm)
C:	0.215"	(5.5 mm)
D:	0.275"	(7.8 mm)
E:	70°	



15A-SW ★★★★★ 4 ½"

Radius face cutting tweezers with ESD safe epoxy handle provide greater visibility. Designed for cutting soft wire. Cutting capacity .010" soft wire.

A:	0.393"	(10 mm)
B:	4.500"	(115 mm)
C:	0.095"	(2.5 mm)
D:	0.375"	(9.5 mm)
E:	70°	



15A-SW-OF

Same as above with Optimum Flush Cutting Blades

15 ★★★★★ 4 ½"

Transverse end cutting tweezers with narrow head design. Cutting capacity .010" soft wire.

A:	0.393"	(10 mm)
B:	4.500"	(115 mm)
C:	0.098"	(2.5 mm)
D:	0.157"	(2.0 mm)
E:		

