

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19203-0379

Status:


Active

Overview:

Quick-Disconnect Terminals

Description:

Krimptite™ Quick Disconnect, Female Steel 900 Degree F/383 Degree C, 10-12 AWG, Tab 6.35mm



Series

image - Reference only

- Documents:
- Drawing (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-013 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family	Quick Disconnects
Series	19203
Crimp Quality Equipment	Yes
Insulated	No
Overview	Quick-Disconnect Terminals
Product Name	Krimptite™
Type	Quick Disconnect
UPC	822348424689

Physical

Barrel Type	Closed
Gender	Male
Glow-Wire Compliant	No
Insulation	Nylon (PA)
Lock to Mating Part	None
Material - Metal	Steel
Material - Plating Mating	Nickel
Material - Plating Termination	Nickel
Net Weight	0.693/g
Orientation	Straight
Packaging Type	Bag
Tab Thickness	0.80mm
Tab Width	7.70mm
Temperature Range - Operating	-65°C to +105°C
Wire Size AWG	10, 12

Electrical

Voltage - Maximum	N/A
-------------------	-----

Material Info

Reference - Drawing Numbers

Product Specification	PS-19902-011, PS-19902-013
Sales Drawing	SD-19203-025

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19203Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Tool for High Temperature Female Quick Disconnects	0640031500

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19203-0379](#)