



**austriamicrosystems AG**

**is now**

**ams AG**

The technical content of this austriamicrosystems datasheet is still valid.

**Contact information:**

**Headquarters:**

ams AG

Tobelbaderstrasse 30

8141 Unterpremstaetten, Austria

Tel: +43 (0) 3136 500 0

e-Mail: [ams\\_sales@ams.com](mailto:ams_sales@ams.com)

Please visit our website at [www.ams.com](http://www.ams.com)

## AS1916 - AS1918

### Microprocessor Supervisory Circuits with Manual Reset and Watchdog

## 1 General Description

The AS1916 - AS1918 microprocessor supervisory circuits were designed to generate a reset when the monitored supply voltage falls below a factory-trimmed threshold. The reset remains asserted for a minimum timeout period after the supply voltage stabilizes.

Guaranteed to be in the correct state for  $V_{CC}$  higher than +1.0V, these devices are ideal for portable and battery-powered systems with strict monitoring requirements.

The devices feature factory-trimmed thresholds to monitor a supply voltage between 1.8 and 3.6V.

The devices are available with the reset output types listed in Table 1.

Table 1. Standard Products

| Model  | Reset Output Type     |
|--------|-----------------------|
| AS1916 | Active-Low Push/Pull  |
| AS1917 | Active-High Push/Pull |
| AS1918 | Active-Low Open-Drain |

The AS1916 - AS1918 include a manual-reset input for systems that never fully power down the microprocessor.

Additionally, these devices feature a watchdog timer to help ensure that the processor is operating within proper code boundaries.

The AS1916 - AS1918 are available in a 5-pin SOT23 package.


## 2 Key Features

- $V_{CC}$  Supervisory Range: +1.8 to +3.6V
- Guaranteed Reset Valid Down to  $V_{CC} = +1.0V$
- Reset Timeout Delay: 215ms
- Manual Reset Input
- Three Reset Output Types
  - Active-Low Push/Pull (AS1916)
  - Active-High Push/Pull (AS1917)
  - Active-Low Open-Drain (AS1918)
- Watchdog Timeout Period: 1.5s
- Immune to Fast Negative  $V_{CC}$  Transients
- External Components Not Required
- Operating Temperature Range: -40 to +125°C
- 5-pin SOT23 Package

## 3 Applications


The devices are ideal for portable and battery-powered systems, embedded controllers, intelligent instruments, automotive systems, and critical CPU monitoring applications.

Figure 1. Typical Application Diagram



## 4 Pin Assignments

Figure 2. Pin Assignments (Top View)



### 4.1 Pin Descriptions

Table 2. Pin Descriptions

| Pin Number | Pin Name | Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
|------------|----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1          | RESETN   | Active-Low Reset Output (AS1916, AS1918). The RESETN signal toggles from high to low when VCC, or MRN is pulled low, or the watchdog triggers a reset. This output signal remains low for the reset timeout period after all supervised voltages exceed their reset threshold, or MRN goes low to high, or the watchdog triggers a reset.                                                                                                                                                                                                                                                                                                                                                             |
|            | RESET    | Active-High Reset Output (AS1917). The RESET signal toggles from low to high when VCC, or MRN is pulled low, or the watchdog triggers a reset. This output signal remains high for the reset timeout period (see <a href="#">tRP</a> on <a href="#">page 4</a> ) after all supervised voltages exceed their reset threshold, or MRN goes low to high, or the watchdog triggers a reset.                                                                                                                                                                                                                                                                                                               |
| 2          | GND      | Ground                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| 3          | MRN      | Active-Low Manual Reset Input. Pulling this pin low asserts a reset. This pin is connected to the internal 50k $\Omega$ pullup to VCC. This reset remains active as long as MRN is low and for the reset timeout period (see <a href="#">tRP</a> on <a href="#">page 4</a> ) after MRN goes high.<br><b>Note:</b> If the manual reset feature is not used, this pin should be unconnected or connected to VCC.                                                                                                                                                                                                                                                                                        |
| 4          | WDI      | Watchdog Input. If WDI remains high or low for longer than the watchdog timeout period (see <a href="#">tWD</a> on <a href="#">page 5</a> ), the internal watchdog timer period expires and a reset is triggered for the reset timeout period (see <a href="#">tRP</a> on <a href="#">page 4</a> ). The internal watchdog timer clears whenever a reset is asserted or when WDI senses a rising or falling edge.<br><b>Note:</b> To disable the watchdog feature, this pin must be unconnected or connected to a tri-state buffer output. WDI must be low or unconnected (tristate) during the reset timeout period <a href="#">tRP</a> , (see <a href="#">Figure 11</a> on <a href="#">page 8</a> ). |
| 5          | VCC      | Supervised Voltage Input. This pin serves as the supervised supply voltage input.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |

## 5 Absolute Maximum Ratings

Stresses beyond those listed in [Table 3](#) may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in [Electrical Characteristics on page 4](#) is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Table 3. Absolute Maximum Ratings

| Parameter                                               | Min  | Max                   | Units | Comments                                                                                                                                                                                                                                                                          |
|---------------------------------------------------------|------|-----------------------|-------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Electrical Parameters                                   |      |                       |       |                                                                                                                                                                                                                                                                                   |
| V <sub>CC</sub> to GND                                  | -0.3 | +5.0                  | V     |                                                                                                                                                                                                                                                                                   |
| Open-Drain RESETN                                       | -0.3 | +7.0                  | V     |                                                                                                                                                                                                                                                                                   |
| Push/Pull RESET, RESETN                                 | -0.3 | V <sub>CC</sub> + 0.3 | V     |                                                                                                                                                                                                                                                                                   |
| MRN, WDI to GND                                         | -0.3 | V <sub>CC</sub> + 0.3 | V     |                                                                                                                                                                                                                                                                                   |
| Input Current (V <sub>CC</sub> )                        |      | 20                    | mA    |                                                                                                                                                                                                                                                                                   |
| Output Current (RESET, RESETN)                          |      | 20                    | mA    |                                                                                                                                                                                                                                                                                   |
| Continuous Power Dissipation                            |      |                       |       |                                                                                                                                                                                                                                                                                   |
| Continuous Power Dissipation (T <sub>AMB</sub> = +70°C) |      | 696                   | mW    | Derate 8.7mW/°C above +70°C                                                                                                                                                                                                                                                       |
| Temperature Ranges and Storage Conditions               |      |                       |       |                                                                                                                                                                                                                                                                                   |
| Junction Temperature                                    |      | +150                  | °C    |                                                                                                                                                                                                                                                                                   |
| Storage Temperature Range                               | -55  | +150                  | °C    |                                                                                                                                                                                                                                                                                   |
| Package Body Temperature                                |      | +260                  | °C    | The reflow peak soldering temperature (body temperature) specified is in accordance with IPC/JEDEC J-STD-020 "Moisture/Reflow Sensitivity Classification for Non-Hermetic Solid State Surface Mount Devices". The lead finish for Pb-free leaded packages is matte tin (100% Sn). |
| Humidity non-condensing                                 | 5    | 85                    | %     |                                                                                                                                                                                                                                                                                   |
| Moisture Sensitive Level                                |      | 1                     |       | Represents a max. floor life time of unlimited                                                                                                                                                                                                                                    |

## 6 Electrical Characteristics

$V_{CC} = +2.7$  to  $+3.6$ V for AS19xx-T/S/R,  $V_{CC} = +2.1$  to  $+2.75$ V for AS19xx-Z/Y,  $V_{CC} = +1.53$  to  $+2.0$ V for AS19xx-W/V; Typical values @  $T_{AMB} = +25^{\circ}\text{C}$  (unless otherwise specified).

Table 4. Electrical Characteristics

| Symbol    | Parameter <sup>1</sup>                                 | Conditions                                                                                                  | Min                 | Typ               | Max   | Units                      |
|-----------|--------------------------------------------------------|-------------------------------------------------------------------------------------------------------------|---------------------|-------------------|-------|----------------------------|
| $T_{AMB}$ | Operating Temperature Range                            |                                                                                                             | -40                 |                   | +125  | $^{\circ}\text{C}$         |
| $V_{CC}$  | Operating Voltage Range                                | $T_{AMB} = 0$ to $+85^{\circ}\text{C}$                                                                      | 1.0                 |                   | 3.6   | V                          |
|           |                                                        | $T_{AMB} = -40$ to $+125^{\circ}\text{C}$                                                                   | 1.2                 |                   | 3.6   |                            |
| $I_{CC}$  | $V_{CC}$ Supply Current<br>(MRN and WDI Not Connected) | $V_{CC} = +3.6$ V, No Load,<br>$T_{AMB} = -40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$                     |                     | 5.5               | 12    | $\mu\text{A}$              |
|           |                                                        | $V_{CC} = +3.6$ V, No Load,<br>$T_{AMB} = -40$ to $+125^{\circ}\text{C}$                                    |                     |                   | 19    |                            |
| $V_{TH}$  | $V_{CC}$ Reset Threshold<br>( $V_{CC}$ Falling)        | $T_{AMB} = -40$ to $+85^{\circ}\text{C}$                                                                    | 2.994               | 3.08              | 3.154 | V                          |
|           |                                                        | $T_{AMB} = -40$ to $+125^{\circ}\text{C}$                                                                   | 2.972               |                   | 3.179 |                            |
|           |                                                        | $T_{AMB} = -40$ to $+85^{\circ}\text{C}$                                                                    | 2.848               | 2.93              | 3.000 |                            |
|           |                                                        | $T_{AMB} = -40$ to $+125^{\circ}\text{C}$                                                                   | 2.827               |                   | 3.024 |                            |
|           |                                                        | $T_{AMB} = -40$ to $+85^{\circ}\text{C}$                                                                    | 2.556               | 2.63              | 2.693 |                            |
|           |                                                        | $T_{AMB} = -40$ to $+125^{\circ}\text{C}$                                                                   | 2.538               |                   | 2.714 |                            |
|           |                                                        | $T_{AMB} = -40$ to $+85^{\circ}\text{C}$                                                                    | 2.255               | 2.32              | 2.376 |                            |
|           |                                                        | $T_{AMB} = -40$ to $+125^{\circ}\text{C}$                                                                   | 2.239               |                   | 2.394 |                            |
|           |                                                        | $T_{AMB} = -40$ to $+85^{\circ}\text{C}$                                                                    | 2.129               | 2.19              | 2.243 |                            |
|           |                                                        | $T_{AMB} = -40$ to $+125^{\circ}\text{C}$                                                                   | 2.113               |                   | 2.260 |                            |
|           |                                                        | $T_{AMB} = -40$ to $+85^{\circ}\text{C}$                                                                    | 1.623               | 1.67              | 1.710 |                            |
|           |                                                        | $T_{AMB} = -40$ to $+125^{\circ}\text{C}$                                                                   | 1.612               |                   | 1.723 |                            |
|           |                                                        | $T_{AMB} = -40$ to $+85^{\circ}\text{C}$                                                                    | 1.536               | 1.58              | 1.618 |                            |
|           |                                                        | $T_{AMB} = -40$ to $+125^{\circ}\text{C}$                                                                   | 1.525               |                   | 1.631 |                            |
|           | Reset Threshold<br>Temperature Coefficient             |                                                                                                             |                     | 60                |       | ppm/<br>$^{\circ}\text{C}$ |
|           | Reset Threshold Hysteresis                             |                                                                                                             |                     | $8 \times V_{TH}$ |       | mV                         |
| trD       | $V_{CC}$ to Reset<br>Output Delay                      | $V_{CC} = V_{TH}$ to $(V_{TH} - 100\text{mV})$                                                              |                     | 55                |       | $\mu\text{s}$              |
| trP       | Reset Timeout Period                                   | $T_{AMB} = -40$ to $+85^{\circ}\text{C}$                                                                    | 140                 | 215               | 280   | ms                         |
|           |                                                        | $T_{AMB} = -40$ to $+125^{\circ}\text{C}$                                                                   | 100                 |                   | 320   |                            |
| $V_{OL}$  | RESETN Output Low<br>(Push/Pull or Open-Drain)         | $V_{CC} \geq 1.0$ V, $I_{SINK} = 50\mu\text{A}$ ,<br>Reset Asserted, $T_{AMB} = 0$ to $+85^{\circ}\text{C}$ |                     |                   | 0.3   | V                          |
|           |                                                        | $V_{CC} \geq 1.2$ V, $I_{SINK} = 100\mu\text{A}$ , Reset Asserted                                           |                     |                   | 0.3   |                            |
|           |                                                        | $V_{CC} \geq 2.55$ V, $I_{SINK} = 1.2$ mA,<br>Reset Asserted                                                |                     |                   | 0.3   |                            |
|           |                                                        | $V_{CC} \geq 3.3$ V, $I_{SINK} = 3.2$ mA,<br>Reset Asserted                                                 |                     |                   | 0.4   |                            |
| $V_{OH}$  | RESETN Output High<br>(Push/Pull Only)                 | $V_{CC} \geq 1.8$ V, $I_{SOURCE} = 200\mu\text{A}$ ,<br>Reset Not Asserted                                  | $0.8 \times V_{CC}$ |                   |       | V                          |
|           |                                                        | $V_{CC} \geq 3.15$ V, $I_{SOURCE} = 500\mu\text{A}$ ,<br>Reset Not Asserted                                 | $0.8 \times V_{CC}$ |                   |       |                            |
|           |                                                        | $V_{CC} \geq 3.3$ V, $I_{SOURCE} = 800\mu\text{A}$ ,<br>Reset Not Asserted                                  | $0.8 \times V_{CC}$ |                   |       |                            |
| ILKG      | Open-Drain RESETN Output Leakage<br>Current            | RESETN Not Asserted                                                                                         |                     |                   | 1.0   | $\mu\text{A}$              |
|           |                                                        | $T_{AMB} = +25^{\circ}\text{C}$                                                                             |                     |                   | 0.2   |                            |

Table 4. Electrical Characteristics

| Symbol             | Parameter <sup>1</sup>                | Conditions                                                      | Min          | Typ | Max          | Units |
|--------------------|---------------------------------------|-----------------------------------------------------------------|--------------|-----|--------------|-------|
| VOH                | RESET Output High<br>(Push/Pull Only) | VCC ≥ 1.0V, ISOURCE = 1μA,<br>Reset Asserted, TAMB = 0 to +85°C | 0.8 x<br>VCC |     |              | V     |
|                    |                                       | VCC ≥ 1.50V, ISOURCE = 100μA,<br>Reset Asserted                 | 0.8 x<br>VCC |     |              |       |
|                    |                                       | VCC ≥ 2.55V, ISOURCE = 500μA,<br>Reset Asserted                 | 0.8 x<br>VCC |     |              |       |
|                    |                                       | VCC ≥ 3.3V, ISOURCE = 800μA,<br>Reset Asserted                  | 0.8 x<br>VCC |     |              |       |
| VOL                | RESET Output Low<br>(Push/Pull Only)  | VCC ≥ 1.8V, ISINK = 500μA,<br>Reset Asserted                    |              |     | 0.3          | V     |
|                    |                                       | VCC ≥ 3.15V, ISINK = 1.2mA,<br>Reset Asserted                   |              |     | 0.3          |       |
|                    |                                       | VCC ≥ 3.3V, ISINK = 3.2mA,<br>Reset Asserted                    |              |     | 0.4          |       |
| Manual Reset Input |                                       |                                                                 |              |     |              |       |
| VIL                | MRN Input voltage                     |                                                                 |              |     | 0.3 x<br>VCC | V     |
| VIH                |                                       |                                                                 | 0.7 x<br>VCC |     |              |       |
|                    | MRN Minimum Input Pulse               |                                                                 | 1            |     |              | μs    |
|                    | MRN Transient Rejection               |                                                                 |              | 90  |              | ns    |
|                    | MRN to Reset Delay                    |                                                                 |              | 130 |              | ns    |
|                    | MRN Pullup Resistance                 |                                                                 | 25           | 50  | 75           | kΩ    |
| Watchdog Input     |                                       |                                                                 |              |     |              |       |
| tWD                | Watchdog Timeout Period               | TAMB = -40 to +85°C                                             | 1.12         | 1.5 | 2.4          | s     |
|                    |                                       | TAMB = -40 to +125°C                                            | 0.80         |     | 2.60         |       |
| tWDI               | WDI Pulse Width <sup>2</sup>          |                                                                 | 20           |     |              | ns    |
| VIL                | WDI Input Voltage                     |                                                                 |              |     | 0.3 x<br>VCC | V     |
| VIH                |                                       |                                                                 | 0.7 x<br>VCC |     |              |       |
| IWDI               | WDI Input Current                     | WDI = VCC, Time Average                                         |              | 80  | 160          | μA    |
|                    |                                       | WDI = 0, Time Average                                           | -20          | -11 |              |       |

1. Over-temperature limits are guaranteed by design and not production tested. Devices tested at +25°C.

2. Guaranteed by design and not production tested.

**Note:** All limits are guaranteed. The parameters with min and max values are guaranteed with production tests or SQC (Statistical Quality Control) methods.

## 7 Typical Operating Characteristics

$T_{AMB} = +25^{\circ}\text{C}$  (unless otherwise specified).

Figure 3. Normalized Reset Threshold Delay vs. Temperature Active-Low (Typ)




Figure 4.  $V_{OUT}$  vs.  $V_{CC}$ ,  $V_{TH} = 1.58\text{V}$




Figure 5. Reset Timeout Period vs. Temperature




Figure 6. Supply Current vs. Temperature




Figure 7.  $V_{OH}$  vs.  $I_{SOURCE}$ ;  $V_{CC} = 3.2\text{V}$





Figure 8.  $V_{OL}$  vs.  $I_{SINK}$ ;  $V_{CC} = 3.2\text{V}$



## 8 Detailed Description

The AS1916 - AS1918 supervisory circuits were designed to generate a reset when the monitored supply voltage falls below its factory-trimmed trip threshold (see  $V_{TH}$  on [page 4](#)), and to maintain the reset for a minimum timeout period (see  $t_{RP}$  on [page 4](#)) after the supply has stabilized.

The integrated watchdog timer ([see Watchdog Input on page 8](#)) helps mitigate against bad programming code or clock signals, and/or poor peripheral response.

The active-low manual reset input ([see Manual Reset Input on page 8](#)) allows for an externally activated system reset.

### 8.1 RESET/RESETN

Whenever the monitored supply voltage falls below its reset threshold, the RESET output asserts low or the RESETN output asserts high. Once the monitored voltage has stabilized, an internal timer keeps the reset asserted for the reset timeout period ( $t_{RP}$ ). After the  $t_{RP}$  period, the RESET/RESETN output returns to its original state ([see Figure 10](#)).

Figure 9. Functional Diagram of VCC Supervisory Application





Figure 10. Reset Timing Diagram






## 8.2 Watchdog Input

The integrated watchdog feature can be used to monitor processor activity via pin WDI, and can detect pulses as short as 50ns. The watchdog requires that the processor toggle the watchdog logic input at regular intervals, within a specified minimum timeout period (1.5s, typ). A reset is asserted for the reset timeout period. As long as reset is asserted, the timer remains cleared and is not incremented. When reset is deasserted, the watchdog timer starts counting (Figure 11).

**Note:** The watchdog timer can be cleared with a reset pulse or by toggling WDI.

Figure 11. Watchdog Timing Relationship



The watchdog is internally driven low during most (87.5%) of the watchdog timeout period (see tWD on page 5) and high for the rest of the watchdog timeout period. When pin WDI is left unconnected, this internal driver clears the watchdog timer every 1.4s. When WDI is tri-stated or is not connected, the maximum allowable leakage current is 10µA and the maximum allowable load capacitance is 200pF.

**Note:** The watchdog function can be disabled by leaving pin WDI unconnected or connecting it to a tri-state output buffer.

## 8.3 Manual Reset Input

The active-low pin MRN is used to force a manual reset. This input can be driven by CMOS logic levels or with open-drain collector outputs.


Pulling MRN low asserts a reset which will remain asserted as long as MRN is kept low, and for the timeout period (see tRP on page 4) after MRN goes high (140ms min). The manual reset circuitry has an internal 50kΩ pullup resistor, thus it can be left open if not used.

To create a manual-reset circuit, connect a normally open momentary switch from pin MRN to GND (see Figure 1 on page 1); external debounce circuitry is not required in this configuration.

If MRN is driven via long cables or the device is used in a noisy environment, a 0.1µF capacitor between pin MRN and GND will provide additional noise immunity.



Figure 13. Example Watchdog Programming Flowchart



## 10 Package Drawings and Markings

Figure 14. 5-pin SOT23 Marking





Figure 15. 5-pin SOT23 Package



## 11 Ordering Information

The devices are available as the standard products shown in [Table 5](#).

Table 5. Ordering Information

| Ordering Code | Marking | Description                                                              | Threshold | Delivery Form | Package     |
|---------------|---------|--------------------------------------------------------------------------|-----------|---------------|-------------|
| AS1916S-T     | ASIO    | Active-Low Push/Pull Supervisory Circuit with Watchdog and Manual Reset  | 2.93V     | Tape and Reel | 5-pin SOT23 |
| AS1916R-T     | ASIP    | Active-Low Push/Pull Supervisory Circuit with Watchdog and Manual Reset  | 2.63V     | Tape and Reel | 5-pin SOT23 |
| AS1916Z-T     | ASIQ    | Active-Low Push/Pull Supervisory Circuit with Watchdog and Manual Reset  | 2.32V     | Tape and Reel | 5-pin SOT23 |
| AS1916V-T     | ASIR    | Active-Low Push/Pull Supervisory Circuit with Watchdog and Manual Reset  | 1.58V     | Tape and Reel | 5-pin SOT23 |
| AS1917S-T     | ASIS    | Active High Push/Pull Supervisory Circuit with Watchdog and Manual Reset | 2.93V     | Tape and Reel | 5-pin SOT23 |
| AS1917R-T     | ASIT    | Active High Push/Pull Supervisory Circuit with Watchdog and Manual Reset | 2.63V     | Tape and Reel | 5-pin SOT23 |
| AS1917Z-T     | ASIU    | Active High Push/Pull Supervisory Circuit with Watchdog and Manual Reset | 2.32V     | Tape and Reel | 5-pin SOT23 |
| AS1917V-T     | ASIV    | Active High Push/Pull Supervisory Circuit with Watchdog and Manual Reset | 1.58V     | Tape and Reel | 5-pin SOT23 |
| AS1918S-T     | ASIW    | Active-Low Open Drain Supervisory Circuit with Watchdog and Manual Reset | 2.93V     | Tape and Reel | 5-pin SOT23 |
| AS1918R-T     | ASIX    | Active-Low Open Drain Supervisory Circuit with Watchdog and Manual Reset | 2.63V     | Tape and Reel | 5-pin SOT23 |
| AS1918Z-T     | ASIY    | Active-Low Open Drain Supervisory Circuit with Watchdog and Manual Reset | 2.32V     | Tape and Reel | 5-pin SOT23 |
| AS1918V-T     | ASIZ    | Active-Low Open Drain Supervisory Circuit with Watchdog and Manual Reset | 1.58V     | Tape and Reel | 5-pin SOT23 |

**Note:** All products are RoHS compliant.

Buy our products or get free samples online at ICdirect: <http://www.austriamicrosystems.com/ICdirect>

Technical Support is found at <http://www.austriamicrosystems.com/Technical-Support>

For further information and requests, please contact us <mailto:sales@austriamicrosystems.com>  
 or find your local distributor at <http://www.austriamicrosystems.com/distributor>

## Copyrights

Copyright © 1997-2010, austriamicrosystems AG, Tobelbaderstrasse 30, 8141 Unterpremstaetten, Austria-Europe. Trademarks Registered ®. All rights reserved. The material herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner.

All products and companies mentioned are trademarks or registered trademarks of their respective companies.

## Disclaimer

Devices sold by austriamicrosystems AG are covered by the warranty and patent indemnification provisions appearing in its Term of Sale. austriamicrosystems AG makes no warranty, express, statutory, implied, or by description regarding the information set forth herein or regarding the freedom of the described devices from patent infringement. austriamicrosystems AG reserves the right to change specifications and prices at any time and without notice. Therefore, prior to designing this product into a system, it is necessary to check with austriamicrosystems AG for current information. This product is intended for use in normal commercial applications. Applications requiring extended temperature range, unusual environmental requirements, or high reliability applications, such as military, medical life-support or life-sustaining equipment are specifically not recommended without additional processing by austriamicrosystems AG for each application. For shipments of less than 100 parts the manufacturing flow might show deviations from the standard production flow, such as test flow or test location.

The information furnished here by austriamicrosystems AG is believed to be correct and accurate. However, austriamicrosystems AG shall not be liable to recipient or any third party for any damages, including but not limited to personal injury, property damage, loss of profits, loss of use, interruption of business or indirect, special, incidental or consequential damages, of any kind, in connection with or arising out of the furnishing, performance or use of the technical data herein. No obligation or liability to recipient or any third party shall arise or flow out of austriamicrosystems AG rendering of technical or other services.



## Contact Information

### Headquarters

austriamicrosystems AG  
Tobelbaderstrasse 30  
A-8141 Unterpremstaetten, Austria

Tel: +43 (0) 3136 500 0  
Fax: +43 (0) 3136 525 01

For Sales Offices, Distributors and Representatives, please visit:

<http://www.austriamicrosystems.com/contact>