


Metallized Polyester Film Capacitors MKT Radial Potted Type



FEATURES

Available taped and loose in box

Lead (Pb)-free product

RoHS-compliant product



RoHS
COMPLIANT

CAPACITANCE TOLERANCE

$\pm 10\%$; $\pm 5\%$

RATED (DC) VOLTAGE

100 V; 250 V; 400 V; 630 V

RATED (AC) VOLTAGE

63 V; 160 V; 220 V; 250 V

CLIMATIC CATEGORY

55/105/56

RATED TEMPERATURE

85 °C

MAXIMUM APPLICATION TEMPERATURE

100 °C

REFERENCE SPECIFICATIONS

IEC 60384-2

PERFORMANCE GRADE

Grade 1 (long life)

DETAIL SPECIFICATION

For more detailed data and test requirements contact:

filmcaps.roeselare@vishay.com

APPLICATIONS

Blocking and coupling. Bypass and energy reservoir

MARKING

C-value; tolerance; rated voltage; code for manufacturer; manufacturer's type designation; code for dielectric material; code for factory of origin, year and week of manufacturer

DIELECTRIC

Polyester film

ELECTRODES

Vacuum deposited aluminum

ENCAPSULATION

Flame retardant plastic case and epoxy resin
(UL-class 94 V-0)

CONSTRUCTION

Wound mono construction


LEADS

Tinned wire

CAPACITANCE RANGE (E12 SERIES)

0.0047 to 15 μ F

COMPOSITION OF CATALOG NUMBER



SPECIFIC REFERENCE DATA

DESCRIPTION	VALUE			
Tangent of loss angle: 0.33 µF < C ≤ 0.47 µF 0.47 µF < C ≤ 1.0 µF 1.0 µF < C ≤ 10 µF C > 10 µF	at 1 kHz	at 10 kHz	at 100 kHz	
	≤ 75 × 10 ⁻⁴	≤ 130 × 10 ⁻⁴	≤ 300 × 10 ⁻⁴	
	≤ 75 × 10 ⁻⁴	≤ 130 × 10 ⁻⁴	–	
	≤ 75 × 10 ⁻⁴	≤ 150 × 10 ⁻⁴	–	
	≤ 75 × 10 ⁻⁴	–	–	
Rated voltage pulse slope (dU/dt) _R : P = 15 mm P = 22.5 mm P = 27.5 mm	at 100 V (DC)	at 250 V (DC)	at 400 V (DC)	at 630 V (DC)
	14 V/µs	16 V/µs	34 V/µs	90 V/µs
	5 V/µs	7 V/µs	14 V/µs	35 V/µs
	4 V/µs	6 V/µs	12 V/µs	30 V/µs
R between leads, for C ≤ 0.33 µF: at 100 V; 1 minute at 500 V; 1 minute	> 15000 MΩ	> 30000 MΩ	> 30000 MΩ	> 30000 MΩ
RC between leads, for C > 0.33 µF: at 100 V; 1 minute at 500 V; 1 minute	> 5000 s	> 10000 s	> 10000 s	> 10000 s
R between interconnected leads and case (foil method)	> 30000 MΩ	> 30000 MΩ	> 30000 MΩ	> 30000 MΩ
Withstanding (DC) voltage (cut off current 10 mA); rise time 100 V/s	160 V; 1 minute	400 V; 1 minute	640 V; 1 minute	1008 V; 1 minute
Withstanding (DC) voltage between leads and case	200 V; 1 minute	500 V; 1 minute	800 V; 1 minute	1260 V; 1 minute



MKT 373 Compact Size

Metallized Polyester Film Capacitors Vishay BCcomponents
MKT Radial Potted Type

$U_{Rdc} = 100\text{ V}$, $U_{Rac} = 63\text{ V}$ (compact size)

C (μF)	DIMENSIONS w × h × l (mm)	MASS (g)	CATALOG NUMBER 2222 373 AND PACKAGING		
			LOOSE IN BOX		REEL
			lt = 5.0 ± 1.0 mm		SPQ
			C-tol = ± 10 %	SPQ	
			last 5 digits of catalog number		
Pitch = 15.0 ± 0.4 mm; d _t = 0.60 ± 0.06 mm					
0.33	5.0 × 11.0 × 17.5	1.1	23334	1000	1100
0.39			23394		
0.47			23474		
0.56			23564		
0.68			23684		
0.82			23824		
1			23105		
1.2			23125		
1.5			23155		
1.8			23185		
2.2	6.0 × 12.0 × 17.5	1.4	23225	1000	900

$U_{Rdc} = 250\text{ V}$, $U_{Rac} = 160\text{ V}$ (compact size)

C (μF)	DIMENSIONS w × h × l (mm)	MASS (g)	CATALOG NUMBER 2222 373 AND PACKAGING		
			LOOSE IN BOX		REEL
			lt = 5.0 ± 1.0 mm		SPQ
			C-tol = ± 10 %	SPQ	
			LAST 5 DIGITS OF CATALOG NUMBER		
Pitch = 15.0 ± 0.4 mm; d _t = 0.60 ± 0.06 mm					
0.15 0.18 0.22 0.27 0.33	5.0 × 11.0 × 17.5	1.1	43154 43184 43224 43274 43334	1000	1100
0.39 0.47	6.0 × 12.0 × 17.5	1.4	43394 43474	1000	900
Pitch = 15.0 ± 0.4 mm; d _t = 0.80 ± 0.08 mm					
0.56 0.68	7.0 × 13.5 × 17.5	1.9	43564 43684	1000	800
0.82 1	8.5 × 15.0 × 17.5	2.6	43824 43105	1000	650
1.2	10.0 × 16.5 × 17.5	3.1	43125	500	600
Pitch = 22.5 ± 0.4 mm; d _t = 0.80 ± 0.08 mm					
1.5 1.8	8.5 × 18.0 × 26.0	4.4	43155 43185	200	450
2.2 2.7	10.0 × 19.5 × 26.0	5.5	43225 43275	200	350
Pitch = 27.5 ± 0.4 mm; d _t = 0.80 ± 0.08 mm					
3.3	11.0 × 21.0 × 31.0	7.8	43335	100	
3.9 4.7	13.0 × 23.0 × 31.0	10.4	43395 43475	100	

MKT 373 Compact Size

Vishay BCcomponents Metallized Polyester Film Capacitors
MKT Radial Potted Type



$U_{Rdc} = 400\text{ V}$, $U_{Rac} = 220\text{ V}$ (compact size)

C (μF)	DIMENSIONS w × h × l (mm)	MASS (g)	CATALOG NUMBER 2222 373 AND PACKAGING		
			LOOSE IN BOX		REEL
			It = 5.0 ± 1.0 mm		SPQ
			C-tol = ± 10 %	LAST 5 DIGITS OF CATALOG NUMBER	
		SPQ	SPQ		
Pitch = 15.0 ± 0.4 mm; d _t = 0.60 ± 0.06 mm					
0.047 0.056 0.068 0.082 0.1 0.12 0.15	5.0 × 11.0 × 17.5	1.1	53473 53563 53683 53823 53104 53124 53154	1000	1100
0.18 0.22	6.0 × 12.0 × 17.5	1.4	53184 53224	1000	900
Pitch = 15.0 ± 0.4 mm; d _t = 0.80 ± 0.08 mm					
0.27 0.33	7.0 × 13.5 × 17.5	1.9	53274 53334	1000	800
0.39 0.47	8.5 × 15.0 × 17.5	2.6	53394 53474	1000	650
0.56	10.0 × 16.5 × 17.5	3.2	53564	500	600
Pitch = 22.5 ± 0.4 mm; d _t = 0.80 ± 0.08 mm					
0.68 0.82	8.5 × 18.0 × 26.0	4.4	53684 53824	200	450
1 1.2	10.0 × 19.5 × 26.0	5.5	53105 53125	200	350
Pitch = 27.5 ± 0.4 mm; d _t = 0.80 ± 0.08 mm					
1.5	11.0 × 21.0 × 31.0	7.8	53155	100	
1.8 2.2	13.0 × 23.0 × 31.0	10.5	53185 53225	100	

$U_{Rdc} = 630\text{ V}$, $U_{Rac} = 250\text{ V}$ (compact size)

C (μF)	DIMENSIONS w × h × l (mm)	MASS (g)	CATALOG NUMBER 2222 373 AND PACKAGING		
			LOOSE IN BOX		REEL
			It = 5.0 ± 1.0 mm		SPQ
			C-tol = ± 10 %	SPQ	
			LAST 5 DIGITS OF CATALOG NUMBER		
Pitch = 15.0 ± 0.4 mm; d _t = 0.60 ± 0.06 mm					
0.047 0.056	5.0 × 11.0 × 17.5	1.1	63473 63563	1000	1100
0.068 0.082	6.0 × 12.0 × 17.5	1.4	63683 63823	1000	900
Pitch = 15.0 ± 0.4 mm; d _t = 0.80 ± 0.08 mm					
0.1 0.12	7.0 × 13.5 × 17.5	1.9	63104 63124	1000	800
0.15 0.18	8.5 × 15.0 × 17.5	2.6	63154 63184	1000	650
0.22	10.0 × 16.5 × 17.5	3.2	63224	500	600
Pitch = 22.5 ± 0.4 mm; d _t = 0.80 ± 0.08 mm					
0.27 0.33	8.5 × 18.0 × 26.0	4.4	63274 63334	200	450
0.39 0.47	10.0 × 19.5 × 26.0	5.5	63394 63474	200	350
Pitch = 27.5 ± 0.4 mm; d _t = 0.80 ± 0.08 mm					
0.56	11.0 × 21.0 × 31.0	7.8	63564	100	
0.68 0.82	13.0 × 23.0 × 31.0	10.5	63684 63824	100	
1	15.0 × 25.0 × 31.0	7.8	63105	100	



MKT 373 Standard Size

Metallized Polyester Film Capacitors
MKT Radial Potted Type

Vishay BCcomponents

$U_{Rdc} = 100 \text{ V}$, $U_{Rac} = 63 \text{ V}$ (standard size)

C (μF)	DIMENSIONS w × h × l (mm)	MASS (g)	CATALOG NUMBER 2222 373 AND PACKAGING		
			LOOSE IN BOX		REEL
			lt = 5.0 ± 1.0 mm		SPQ
			C-tol = ± 10 %	LAST 5 DIGITS OF CATALOG NUMBER	
Pitch = 15.0 ± 0.4 mm; dt = 0.60 ± 0.06 mm					
0.33 0.39 0.47 0.56 0.68	5.0 × 11.0 × 17.5	1.1	21334 21394 21474 21564 21684	1000	1100
0.82 1	6.0 × 12.0 × 17.5	1.4	21824 21105	1000	900
Pitch = 15.0 ± 0.4 mm; dt = 0.80 ± 0.08 mm					
1.2 1.5	7.0 × 13.5 × 17.5	1.9	21125 21155	1000	800
1.8 2.2	8.5 × 15.0 × 17.5	2.6	21185 21225	1000	650
Pitch = 22.5 ± 0.4 mm; dt = 0.80 ± 0.08 mm					
2.7 3.3	8.5 × 18.0 × 26.0	4.4	21275 21335	200	450
3.9 4.7	10.0 × 19.5 × 26.0	5.5	21395 21475	200	350
Pitch = 27.5 ± 0.4 mm; dt = 0.80 ± 0.08 mm					
5.6 6.8	11.0 × 21.0 × 31.0	8.0	21565 21685	100	
8.2 10	13.0 × 23.0 × 31.0	10.5	21825 21106	100	
12 15	18.0 × 28.0 × 31.0	17.5	21126 21156	100	

$U_{Rdc} = 250 \text{ V}$, $U_{Rac} = 160 \text{ V}$ (standard size)

C (μF)	DIMENSIONS w × h × l (mm)	MASS (g)	CATALOG NUMBER 2222 373 AND PACKAGING		
			LOOSE IN BOX		REEL
			lt = 5.0 ± 1.0 mm		SPQ
			C-tol = ± 10 %	SPQ	
			LAST 5 DIGITS OF CATALOG NUMBER		
Pitch = 15.0 ± 0.4 mm; dt = 0.60 ± 0.06 mm					
0.15 0.18 0.22	5.0 × 11.0 × 17.5	1.1	41154 41184 41224	1000	1100
0.27 0.33 0.39 0.47	6.0 × 12.0 × 17.5	1.4	41274 41334 41394 41474	1000	900
Pitch = 15.0 ± 0.4 mm; dt = 0.80 ± 0.08 mm					
0.56 0.68	7.0 × 13.5 × 17.5	1.9	41564 41684	1000	800

MKT 373 Standard Size

Vishay BCcomponents Metallized Polyester Film Capacitors
MKT Radial Potted Type



C (μ F)	DIMENSIONS w × h × l (mm)	MASS (g)	CATALOG NUMBER 2222 373 AND PACKAGING		
			LOOSE IN BOX		REEL
			It = 5.0 ± 1.0 mm		
			C-tol = ± 10 %	SPQ	SPQ
			LAST 5 DIGITS OF CATALOG NUMBER		
0.82 1	8.5 × 15.0 × 17.5	2.6	41824 41105	1000	650
Pitch = 22.5 ± 0.4 mm; d _t = 0.80 ± 0.08 mm					
1.2 1.5	8.5 × 18.0 × 26.0	4.4	41125 41155	200	450
1.8 2.2	10.0 × 19.5 × 26.0	5.5	41185 41225	200	350
Pitch = 27.5 ± 0.4 mm; d _t = 0.80 ± 0.08 mm					
2.7 3.3	13.0 × 23.0 × 31.0	10.4	41275 41335	100	
3.9 4.7	15.0 × 25.0 × 31.0	12.5	41395 41475	100	







U_{Rdc} = 400 V, U_{Rac} = 220 V (standard size)







C (μF)	DIMENSIONS w × h × l (mm)	MASS (g)	CATALOG NUMBER 2222 373 AND PACKAGING		
			LOOSE IN BOX		REEL
			It = 5.0 ± 1.0 mm		SPQ
			C-tol = ± 10 %	SPQ	
			LAST 5 DIGITS OF CATALOG NUMBER		
Pitch = 15.0 ± 0.4 mm; d _t = 0.60 ± 0.06 mm					
0.047 0.056 0.068 0.082 0.1	5.0 × 11.0 × 17.5	1.1	51473 51563 51683 51823 51104	1000	1100
0.12 0.15	6.0 × 12.0 × 17.5	1.4	51124 51154	1000	900
Pitch = 15.0 ± 0.4 mm; d _t = 0.80 ± 0.08 mm					
0.18 0.22	7.0 × 13.5 × 17.5	1.9	51184 51224	1000	800
0.27 0.33	8.5 × 15.0 × 17.5	2.6	51274 51334	1000	650
Pitch = 22.5 ± 0.4 mm; d _t = 0.80 ± 0.08 mm					
0.39 0.47	8.5 × 18.0 × 26.0	4.4	51394 51474	200	450
0.56 0.68	10.0 × 19.5 × 26.0	4.4 5.5	51564 51684	200	350
Pitch = 27.5 ± 0.4 mm; d _t = 0.80 ± 0.08 mm					
0.82 1	11.0 × 21.0 × 31.0	7.8	51824 51105	100	
1.2 1.5	15.0 × 25.0 × 31.0	12.8	51125 51155	100	





Metallized Polyester Film Capacitors Vishay BCcomponents MKT Radial Potted Type



MAXIMUM RMS VOLTAGE (SINEWAVE) AS A FUNCTION OF FREQUENCY








CAPACITANCE



IMPEDANCE





Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[BFC237325105](#) [BFC237341105](#) [BFC237323156E3](#) [BFC237323106E3](#) [BFC237324106E3](#) [BFC237390138E3](#)
[BFC237390122E3](#) [BFC237390129E3](#) [BFC237390133E3](#) [BFC237390123E3](#) [BFC237390033](#) [BFC237390058](#)
[BFC237390092E3](#) [BFC237390079E3](#) [BFC237390023](#) [BFC237390068E3](#) [BFC237390059](#) [BFC237321105](#)
[BFC237323825E3](#) [BFC237343125](#) [BFC237324335E3](#) [BFC237351224](#) [BFC237390042](#) [BFC237390028](#)
[BFC237324126E3](#) [BFC237324156E3](#) [BFC237341684](#) [BFC237390152E3](#) [BFC237341224](#) [BFC237325684](#)
[BFC237321106](#) [BFC237321125](#) [BFC237321126](#) [BFC237321156](#) [BFC237321185](#) [BFC237321225](#) [BFC237321275](#)
[BFC237321334](#) [BFC237321335](#) [BFC237321394](#) [BFC237321395](#) [BFC237321474](#) [BFC237321475](#) [BFC237321564](#)
[BFC237321565](#) [BFC237321684](#) [BFC237321685](#) [BFC237321824](#) [BFC237321825](#) [BFC237322105](#) [BFC237322106](#)
[BFC237322125](#) [BFC237322126](#) [BFC237322155](#) [BFC237322156](#) [BFC237322185](#) [BFC237322225](#) [BFC237322275](#)
[BFC237322334](#) [BFC237322335](#) [BFC237322394](#) [BFC237322395](#) [BFC237322474](#) [BFC237322475](#) [BFC237322565](#)
[BFC237322684](#) [BFC237322685](#) [BFC237322824](#) [BFC237322825](#) [BFC237323105](#) [BFC237323125](#) [BFC237323126](#)
[BFC237323155](#) [BFC237323185](#) [BFC237323225](#) [BFC237323275](#) [BFC237323334](#) [BFC237323335](#) [BFC237323394](#)
[BFC237323395](#) [BFC237323474](#) [BFC237323475](#) [BFC237323564](#) [BFC237323565](#) [BFC237323684](#) [BFC237323824](#)
[BFC237324105](#) [BFC237324125](#) [BFC237324155](#) [BFC237324185](#) [BFC237324225](#) [BFC237324275](#) [BFC237324334](#)
[BFC237324394](#) [BFC237324395](#) [BFC237324474](#) [BFC237324475](#) [BFC237324564](#) [BFC237324565](#) [BFC237324684](#)