

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

19


© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	28		D	REV; EC 0210-0020-96	09JUL96	DS	NJ

1. ALL DIMENSIONS ARE MAXIMUM.
2. STRAIN RELIEF TO BE ASSEMBLED WITH
Ø3.18[.125] X 12.7[.500] LONG SEMI-TUBULAR
STEEL RIVETS FURNISHED BY CUSTOMER.
3. ASSEMBLY REQUIRES ONE PIECE OF EITHER:
A) 555891-1 AND 555890-1 OR 555890-3
OR
B) 555891-2 AND 555890-2 OR 555890-4.
4. RECOMMEND ARMOUR CABLE TO ACCOMMODATE
UP TO 8 INSULATED WIRES: 14.3[9/16] OR
12.7[1/2] INSIDE DIAMETER APPLIANCE
FLEX METAL CONDUIT.
5. STRAIN RELIEF ASSEMBLY CAN BE USED WITH
POWER CONNECTOR HOUSING 555930 AND
POWER CONNECTOR BASE 555929 OR LINE
CONNECTOR HOUSING 555892 AND LINE
CONNECTOR COVER 555894.
6. STRAIN RELIEF IS MARKED AS FOLLOWS:
555891-1 IS MARKED 91 1/2
555891-2 IS MARKED 91 9/16

14.3[9/16] CONDUIT	555891-2
12.7[1/2] CONDUIT	555891-1
DESCRIPTION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.			DWN	D. STRAUSSER	09JUL96	AMP AMP Incorporated Harrisburg, PA 17105-3608						
DIMENSIONS: mm [INCHES]			CHK	N. JONES	09JUL96							
			APVD	R. BOSSI	12JUL96	NAME STRAIN RELIEF, FLEXIBLE CONDUIT, LEFT						
			PRODUCT SPEC									
			APPLICATION SPEC									
			MATERIAL			WEIGHT			SIZE	CAGE CODE	DRAWING NO	
FINISH			CUSTOMER DRAWING			A2		00779	C-555891			
						SCALE		2:1	SHEET	1 OF 1	REV	D

