

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

39880-0716

Status:

Active

Overview:

Eurostyle™ Terminal Blocks

Description:

5.08mm Pitch Beau™ Eurostyle™ High Profile, Two Level Terminal Block, Modular, 16 Circuits

Documents:

3D Model

RoHS Certificate of Compliance (PDF)

Drawing (PDF)

Agency Certification

CSA

LR25562

UL

E48521

General

Product Family

Terminal Blocks

Series

39880

Application

N/A

Component Type

One Piece

Overview

Eurostyle™ Terminal Blocks

Product Name

Eurostyle™ Multi-Level

Type

Euro Block

UPC

756054629918

Physical

Circuits (Loaded)

16

Entry Angle

Horizontal

Flammability

94V-0

Lock to Mating Part

None

Net Weight

37.160/g

Number of Rows

2

Orientation

Vertical

PC Tail Length

4.00mm

PCB Retention

None

PCB Thickness - Recommended

2.40mm

Panel Mount

No

Pitch - Mating Interface

5.08mm

Pitch - Termination Interface

5.08mm

Polarized to Mating Part

N/A

Shrouded

Fully

Stackable

Yes

Temperature Range - Operating

110°C

Wire Size AWG

12, 14, 16, 18, 20, 22, 24, 26, 28, 30

Wire Size mm²

0.20 - 2.50

Electrical

Current - Maximum per Contact

24A

Voltage - Maximum

300V

Solder Process Data

Lead-free Process Capability

Wave Capable (TH only)

Material Info

Old Part Number

882416

Reference - Drawing Numbers

Sales Drawing

SD-39880-006




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

39880Series

This document was generated on 09/11/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39880-0716](#)