

# 1.8V CMOS Low Jitter XO

**FN**


7.0 x 5.0mm Ceramic SMD

## Product Features

- <1 ps RMS jitter with non-PLL design
- 1 to 166 MHz Frequency Range
- 1.8V LVCMOS compatible logic levels
- Pin-compatible with standard 7.0 x 5.0mm packages
- Designed for standard reflow and washing techniques
- Low power standby mode
- Pb-free and RoHS/Green compliant

## Product Description


The FN Series includes a 1.8V crystal clock oscillator that achieves superb jitter and stability over a broad range of operating conditions and frequencies. The output clock signal, generated internally with a non-PLL oscillator design, is compatible with JESD8-7 logic levels. The device, available on tape and reel, is contained in a 7.0 x 5.0mm surface-mount ceramic package.

## Applications


The FN Series is an ideal reference clock for applications requiring low jitter and low power, including:

- Portable Electronics
- Server & Storage platforms
- 802.11a/b/g WiFi

## Package:




## Recommended Land Pattern:



## Pin Functions:


| Pin | Function        |
|-----|-----------------|
| 1   | OE Function     |
| 2   | Ground          |
| 3   | Clock Output    |
| 4   | V <sub>DD</sub> |

## Part Ordering Information:



Following the above format, Saronix-eCera part numbers will be assigned upon confirmation of exact customer requirements.

## Legacy Ordering Information - For Reference Only:



## Electrical Performance

| Parameter                       |               | Min.                | Typ. | Max.                | Units        | Notes                          |
|---------------------------------|---------------|---------------------|------|---------------------|--------------|--------------------------------|
| Output Frequency                |               | 1                   |      | 166                 | MHz          | As specified                   |
| Supply Voltage                  |               | +1.62               | +1.8 | +1.98               | V            |                                |
| Supply Current, Output Enabled  |               |                     |      | 4                   | mA           | 1 to 36 MHz                    |
|                                 |               |                     |      | 7                   |              | 36 to 50 MHz                   |
|                                 |               |                     |      | 10                  |              | 50 to 70 MHz                   |
|                                 |               |                     |      | 20                  |              | 70 to 100 MHz                  |
|                                 |               |                     |      | 40                  |              | >100 MHz                       |
| Supply Current, Standby Mode    |               |                     |      | 10                  | μA           | 1 to <36 MHz, 100 to 166 MHz   |
|                                 |               |                     |      | 100                 | μA           | 36 to 70 MHz                   |
| Frequency Stability             |               |                     |      | ±20 to ±50          | ppm          | See Note 1 below               |
| Operating Temperature           |               | -20                 |      | +70                 | °C           | Commercial (standard)          |
|                                 |               | -40                 |      | +85                 |              | Industrial (standard)          |
| Output Logic 0, V <sub>OL</sub> |               |                     |      | 10% V <sub>DD</sub> | V            |                                |
| Output Logic 1, V <sub>OH</sub> |               | 90% V <sub>DD</sub> |      |                     | V            |                                |
| Output Load                     |               |                     |      | 15                  | pF           |                                |
| Duty Cycle                      |               | 45                  |      | 55                  | %            | Measured 50% V <sub>DD</sub>   |
| Rise and Fall Time              | up to 36 MHz  |                     |      | 4                   | ns           | Measured 20/80% of waveform    |
|                                 | 36 to 166 MHz |                     |      | 2.5                 |              |                                |
| Jitter, Phase                   | 1 to 166 MHz  |                     |      | 1                   | ps RMS (1-σ) | 10kHz to 20 MHz frequency band |
| Jitter, Accumulated             | up to 80 MHz  |                     |      | 5                   | ps RMS (1-σ) | 20.000 adjacent periods        |
|                                 | 80 to 166 MHz |                     |      | 3                   |              |                                |
| Jitter, Total                   | up to 80 MHz  |                     |      | 50                  | ps pk-pk     | 100.000 random periods         |
|                                 | 80 to 166 MHz |                     |      | 30                  |              |                                |

### Notes:

1. Stability includes all combinations of operating temperature, load changes, rated input (supply) voltage changes, initial calibration tolerance (25°C), aging (1 year at 25°C average effective ambient temperature), shock and vibration.
2. For specifications other than those listed, please contact sales.


## Output Enable / Disable Function

| Parameter                                                 |  | Min.               | Typ. | Max.               | Units | Notes          |
|-----------------------------------------------------------|--|--------------------|------|--------------------|-------|----------------|
| Input Voltage (pin 1), Output Enable                      |  | 0.7V <sub>DD</sub> |      |                    | V     | or open        |
| Input Voltage (pin 1), Output Disable (low power standby) |  |                    |      | 0.3V <sub>DD</sub> | V     | Output is Hi-Z |
| Internal Pullup Resistance                                |  | 30                 |      |                    | kΩ    |                |
| Output Disable Delay                                      |  |                    |      | 200                | ns    |                |
| Output Enable Delay                                       |  |                    |      | 10                 | ms    |                |

## Absolute Maximum Ratings


| Parameter           | Min. | Typ. | Max. | Units | Notes |
|---------------------|------|------|------|-------|-------|
| Storage Temperature | -55  |      | +125 | °C    |       |

## Test Circuit



## Reflow Soldering Profile

As per IPC/JEDEC J-STD-020C



## Reliability Test Ratings

This product is rated to meet the following test conditions:

| Type          | Parameter                    | Test Condition                                                              |
|---------------|------------------------------|-----------------------------------------------------------------------------|
| Mechanical    | Shock                        | MIL-STD-883, Method 2002, Condition B                                       |
| Mechanical    | Solderability                | JESD22-B102-D Method 2 (Preconditioning E)                                  |
| Mechanical    | Terminal strength            | MIL-STD-883, Method 2004, Condition D                                       |
| Mechanical    | Gross leak                   | MIL-STD-883, Method 1014, Condition C                                       |
| Mechanical    | Fine leak                    | MIL-STD-883, Method 1014, Condition A2 ( $R_1 = 2 \times 10^{-8}$ atm cc/s) |
| Mechanical    | Solvent resistance           | MIL-STD-202, Method 215                                                     |
| Environmental | Thermal shock                | MIL-STD-883, Method 1011, Condition A                                       |
| Environmental | Moisture resistance          | MIL-STD-883, Method 1004                                                    |
| Environmental | Vibration                    | MIL-STD-883, Method 2007, Condition A                                       |
| Environmental | Resistance to soldering heat | J-STD-020C Table 5-2 Pb-free devices (2 cycles max)                         |