



[Home](#)> [Search Tools](#) > [Part Number](#)

## Part Number Search

You Searched For:

Note: Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS.  
*ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the "Global Sales Locator" located either to the right of this data or at the top of every page.*

Sales Support

Product Overview

Our Descriptive Part Number: DAA11W1PK87F0			
Our Global Manufacturing Part Number: 112048 -0026			
Brand: Cannon	Product Category: D Sub	Product Line: D Sub	Series: D SUB

CONSULT FACTORY	RoHS compliant =	material restrictions of lead, cadmium, hexavalent chromium, mercury, poly bromated biphenyl ether (PBB) and poly bromide diphenyl ether (PBDE) according to directive 2002/95/EC
	RoHS compatible =	Compatible with lead free soldering process

Export Compliance		
	Country of Compliance	United States
	Export Compliance Notes	Commercial Shipments "C"
		Controlled by the US Department of Commerce.

Product Datasheet	
Where Sold	Americas, Asia Pacific, Europe
Product Group	D-Subminiature
Product Sub-Family	D-Sub Combo
Component Type	Connector
Application Type	Commercial
Cable or PC Board	Cable
Gender	Plug
Number of Signal Pins	10
Number of Size 8 contacts	1
Straight or Right Angle	Straight
Shell Plating	Tin (with Grounding Dimples)
Hardware	3,05 (.120) Through Holes
Other Features	Industry Standard Machined or Stamped Contacts
Contact Termination	Crimp, Contacts Sold Separatly
Shell Size	DA
Temperature Rating	-55°C to +105°C
Current Capacity	5 A for Stamped Contacts, 7 A for Machined
Contact Resistance	15 milli ohms max.
Dielectric Withstanding Voltage	1000 V AC at Sea Level
Insulator Material	Thermoplastic, UL 94V -0
Shell Material	Steel
Other Information	See Contact Section for Crimp Contacts