

Film Chip Capacitor

Type: **ECWU(C)**

Stacked metallized PEN film as dielectric with simple mold-less construction


■Features

- Small in size
- Applicable for reflow soldering

■Recommended Applications

- Coupling
- By-pass
- General purpose


■Explanation of Part Numbers



■Specifications

Category temp.range	16VDC, 50VDC : -55 to +105°C	
	100VDC, 250VDC : -40 to +85°C	
Rated voltage	16VDC, 50VDC, 100VDC, 250VDC	
Capacitance range	16VDC	0.12 to 0.47 μF (E12)
	50VDC	0.056 to 0.22 μF (E12)
	100VDC	0.012 to 1.0 μF (E12)
	250VDC	0.001 to 1.0 μF (E12)
Capacitance tolerance	16VDC,50VDC	±5%(J)
	100VDC,250VDC	±10%(K) (100VDC, C≤0.15 μF ±5%(J), ±10%(K))
Withstand voltage	Between terminals 16VDC, 50VDC : Rated volt. (VDC)×175% 1 to 5s 100VDC, 250VDC : Rated volt. (VDC)×150% 60s	
Dissipation factor	≤1.0% (20°C, 1kHz)	
Insulation resistance	C≤0.33 μF	16VDC : ≥3000MΩ · (20°C, 10VDC, 60s) 50VDC : ≥3000MΩ · (20°C, 50VDC, 60s) 100VDC, 250VDC : ≥3000MΩ · (20°C, 100VDC, 60s)
	C>0.33 μF	16VDC : 1000MΩ · μF min. (20°C, 10VDC, 60s) 100VDC, 250VDC : 1000MΩ · μF min. (20°C, 100VDC, 60s)
Soldering conditions	Reflow soldering 16VDC, 50VDC : 240°C max. and 30 s max. at more than 210°C (Temp. at cap. surface) 100VDC, 250VDC : 230°C max. and 30 s max. at more than 210°C (Temp. at cap. surface)	

■ Construction



■ Dimensions in mm (not to scale)

Size code	L	Tol.	W	Tol.	H	Tol.
E1	4.8		3.3		1.4	
E2	4.8		3.3		2.0	
E3a	4.8		3.3		2.4	
E3	4.8		3.3		2.8	
D1	6.0	±0.2	4.1	±0.3	1.8	±0.2
D2	6.0		4.1		2.0	
D3	6.0		4.1		2.4	
D4	6.0		4.1		2.8	
D5	6.0		4.1		3.2	
B	6.0		5.0			
Z	7.1		5.0			
X	7.7	±0.4	5.5			
Y	7.1		6.3	±0.4	※	±0.3
V	9.8		6.3			
U	9.8	±0.5	8.0			
T	15.2		8.0			
S	15.2		10.0			

※Refer to the column "Rating, Dimensions & Quantity".

■ Taping Specification for Automatic Mounting

See page 24 for automatic mounting.

■ Rating, Dimensions & Quantity/Reel

● Capacitance tolerance : ±5% (J), ±10% (K)

Cap. (μF)	Rated volt. 16VDC						Rated volt. 50VDC												
	Part No	Dimensions (mm)			Size code	Q'ty	Part No	Dimensions (mm)			Size code	Q'ty							
		L	W	H				L	W	H									
0.056							ECWU1H563□C9	4.8	3.3	2.0	E2	3000							
0.068							ECWU1H683□C9	4.8	3.3	2.0	E2								
0.082							ECWU1H823□C9	4.8	3.3	2.4	E3a	2000							
0.1							ECWU1H104□C9	4.8	3.3	2.8	E3								
0.12	ECWU1C124□C9	4.8	3.3	1.4	E1	3000	ECWU1H124□C9	6.0	4.1	1.8	D1	3000							
0.15	ECWU1C154□C9	4.8	3.3	2.0	E2		ECWU1H154□C9	6.0	4.1	2.0	D2								
0.18	ECWU1C184□C9	4.8	3.3	2.0	E2	2000	ECWU1H184□C9	6.0	4.1	2.4	D3	2000							
0.22	ECWU1C224□C9	4.8	3.3	2.4	E3a		ECWU1H224□C9	6.0	4.1	2.8	D4								
0.27	ECWU1C274□C9	6.0	4.1	1.8	D1	3000	↑ Capacitance tolerance code												
0.33	ECWU1C334□C9	6.0	4.1	2.0	D2														
0.39	ECWU1C394□C9	6.0	4.1	2.4	D3	2000													
0.47	ECWU1C474□C9	6.0	4.1	2.8	D4														

↑ Capacitance tolerance code

↑ Capacitance tolerance code

■ Recommended for Land Dimensions (mm)

Size code	Land dimensions for reflow soldering		
	A	B	C
E1,E2,E3a,E3	2.6	6.6	3.0
D1,D2,D3,D4,D5	3.8	7.8	3.8
B	3.8	7.8	4.6
Z	4.5	9.0	4.6
X	5.1	9.7	5.0
Y	4.5	9.0	5.7
V	7.2	11.9	5.7
U	7.2	11.9	7.2
T	12.6	17.3	7.2
S	12.6	17.3	9.0

■ Rating, Dimensions & Quantity/Reel

● Capacitance tolerance : $\pm 5\%$ (J), $\pm 10\%$ (K)

Cap. (μF)	Rated volt. 100VDC						Rated volt. 250VDC							
	Part No	Dimensions (mm)			Size code	Q'ty	Part No	Dimensions (mm)			Size code	Q'ty		
		L	W	H				L	W	H				
0.001	Please use 100VDC rating ECWU(X)						ECWU2102	C9	4.8	3.3	1.4	E1	3000	
0.0012							ECWU2122	C9	4.8	3.3	1.4	E1		
0.0015							ECWU2152	C9	4.8	3.3	1.4	E1		
0.0018							ECWU2182	C9	4.8	3.3	1.4	E1		
0.0022							ECWU2222	C9	4.8	3.3	1.4	E1		
0.0027							ECWU2272	C9	4.8	3.3	1.4	E1		
0.0033							ECWU2332	C9	4.8	3.3	1.4	E1		
0.0039							ECWU2392	C9	4.8	3.3	1.4	E1		
0.0047							ECWU2472	C9	4.8	3.3	1.4	E1		
0.0056							ECWU2562	C9	4.8	3.3	1.4	E1		
0.0068							ECWU2682	C9	4.8	3.3	1.4	E1		
0.0082							ECWU2822	C9	4.8	3.3	1.4	E1		
0.01							ECWU2103	C9	4.8	3.3	1.4	E1		
0.012	ECWU1123	C9	4.8	3.3	1.4	E1	3000	ECWU2123	C9	4.8	3.3	1.4	E1	2000
0.015	ECWU1153	C9	4.8	3.3	1.4	E1		ECWU2153	C9	4.8	3.3	1.4	E1	
0.018	ECWU1183	C9	4.8	3.3	1.4	E1		ECWU2183	C9	4.8	3.3	2.0	E2	
0.022	ECWU1223	C9	4.8	3.3	1.4	E1		ECWU2223	C9	4.8	3.3	2.0	E2	
0.027	ECWU1273	C9	4.8	3.3	1.4	E1		ECWU2273	C9	4.8	3.3	2.4	E3a	
0.033	ECWU1333	C9	4.8	3.3	1.4	E1		ECWU2333	C9	4.8	3.3	2.8	E3	
0.039	ECWU1393	C9	4.8	3.3	1.4	E1		ECWU2393	C9	6.0	4.1	2.0	D2	3000
0.047	ECWU1473	C9	4.8	3.3	2.0	E2		ECWU2473	C9	6.0	4.1	2.4	D3	
0.056	ECWU1563	C9	4.8	3.3	2.0	E2		ECWU2563	C9	6.0	4.1	2.8	D4	2000
0.068	ECWU1683	C9	4.8	3.3	2.4	E3a		ECWU2683	C9	6.0	4.1	3.2	D5	
0.082	ECWU1823	C9	4.8	3.3	2.8	E3	2000	ECWU2823	C9	6.0	5.0	3.2	B	1500
0.1	ECWU1104	C9	6.0	4.1	1.8	D1		ECWU2104	C9	6.0	5.0	3.8	B	
0.12	ECWU1124	C9	6.0	4.1	2.4	D3	2000	ECWU2124	C9	6.0	5.0	4.5	B	1000
0.15	ECWU1154	C9	6.0	4.1	2.8	D4		ECWU2154KCV	7.1	6.3	3.5	Y		
0.18	ECWU1184KCV	7.1	5.0	2.0	Z	1500	ECWU2184KCV	7.1	6.3	4.1	Y	1000		
0.22	ECWU1224KCV	7.1	5.0	2.4	Z		ECWU2224KCV	7.1	6.3	5.1	Y			
0.27	ECWU1274KCV	7.1	5.0	2.9	Z		ECWU2274KCV	9.8	6.3	3.9	V			
0.33	ECWU1334KCV	7.1	5.0	3.5	Z		ECWU2334KCV	9.8	6.3	4.8	V			
0.39	ECWU1394KCV	7.7	5.5	3.4	X	1000	ECWU2394KCV	9.8	8.0	4.4	U	750		
0.47	ECWU1474KCV	7.7	5.5	4.0	X		ECWU2474KCV	9.8	8.0	5.3	U			
0.56	ECWU1564KCV	9.8	6.3	3.0	V		ECWU2564KCZ	15.2	8.0	3.7	T			
0.68	ECWU1684KCV	9.8	6.3	3.6	V	ECWU2684KCZ	15.2	8.0	4.4	T				
0.82	ECWU1824KCV	9.8	6.3	4.3	V	1000	ECWU2824KCZ	15.2	10.0	4.2	S	750		
1.0	ECWU1105KCV	9.8	6.3	5.1	V		ECWU2105KCZ	15.2	10.0	5.1	S			

↑ Capacitance tolerance code

* Please consult us capacitance tolerance $\pm 5\%$ (J).