

Not Recommended for New Designs

This product was manufactured for Maxim by an outside wafer foundry using a process that is no longer available. It is not recommended for new designs. The data sheet remains available for existing users.

A Maxim replacement or an industry second-source may be available. Please see the QuickView data sheet for this part or contact technical support for assistance.

For further information, [contact Maxim's Applications Tech Support](#).

MAXIM

17μA Max, Dual/Quad, Single-Supply, Precision Op Amps

MXL1178/MXL1179

General Description

Maxim's MXL1178 and MXL1179 are dual and quad micropower, precision op amps. They feature an extremely low 17μA max per op amp supply current, as well as precision offset specifications: 30μV offset voltage, and 50pA offset current. Both offset parameters have low drift over temperature and time.

The MXL1178 and MXL1179 can operate from a single supply (e.g., one lithium cell or two NiCd cells). The input voltage range includes ground. The output stage swings to within a few millivolts of ground while sinking current, which eliminates pull-down resistors and saves power.


Both devices are optimized for +5V single-supply operation, but specifications for ±15V operation are also provided.

Maxim's MXL1178 and MXL1179 are pin compatible with industry standards such as the LT1178 and LT1179. For applications that require smaller packaging, see the MAX478/MAX479 data sheet. For applications that require lower power, see the MAX406/MAX407/MAX409 1μA op amp data sheet.

Applications

Battery- or Solar-Powered Systems:
 Portable Instrumentation
 Remote Sensor Amplifier
 Satellite Circuitry
 Micropower Sample-and-Hold
 Thermocouple Amplifier
 Micropower Filters
 Single Lithium Cell-Powered Systems

Typical Operating Circuit




Features

- ◆ 17μA Max Supply Current per Amplifier
- ◆ 70μV Max Offset Voltage
- ◆ 250pA Max Offset Current
- ◆ 5nA Max Input Bias Current
- ◆ 0.9μV_{p-p} 0.1Hz to 10Hz Voltage Noise
- ◆ 1.5pA_{p-p} 0.1Hz to 10Hz Current Noise
- ◆ 0.5μV/°C Offset-Voltage Drift
- ◆ 85kHz Gain-Bandwidth Product
- ◆ 0.04V/μs Slew Rate
- ◆ Single-Supply Operation:
 Input Voltage Range Includes Ground
 Output Swings to Ground while Sinking Current
 No Pull-Down Resistors Required
- ◆ Output Sources and Sinks 5mA Load Current

Ordering Information

PART	TEMP. RANGE	PIN-PACKAGE
MXL1178ACN8	0°C to +70°C	8 Plastic DIP
MXL1178CN8	0°C to +70°C	8 Plastic DIP
MXL1178S	0°C to +70°C	16 Wide SO
MXL1178IN8	-40°C to +85°C	8 Plastic DIP
MXL1179ACN	0°C to +70°C	14 Plastic DIP
MXL1179CN	0°C to +70°C	14 Plastic DIP
MXL1179S	0°C to +70°C	16 Wide SO
MXL1179IN	-40°C to +85°C	14 Plastic DIP

Pin Configurations



17μA Max, Dual/Quad, Single-Supply, Precision Op Amps

ABSOLUTE MAXIMUM RATINGS

Supply Voltage.....±22V
Differential Input Voltage.....±30V
Input Voltage.....Equal to Positive Supply Voltage
.....5V Below Negative Supply Voltage
Output Short-Circuit Duration.....Continuous
Continuous Power Dissipation (T_A = +70°C)
8-Pin Plastic DIP (derate 9.09mW/°C above +70°C) . . 727mW
14-Pin Plastic DIP (derate 10.00mW/°C above +70°C) 800mW
16-Pin Wide SO (derate 9.52mW/°C above +70°C) . . 762mW

Operating Temperature Ranges:

MXL117_AC_/C_/S.....0°C to +70°C
MXL117_I.....-40°C to +85°C
Storage Temperature Range.....-65°C to +150°C
Lead Temperature (soldering, 10sec).....+300°C

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS

(V_S = 5V, 0V, V_{CM} = 0.1V, V_O = 1.4V, T_A = +25°C, unless otherwise noted.)

PARAMETER	SYMBOL	CONDITIONS	MXL1178AC MXL1179AC			MXL1178C/S MXL1179C/S			UNITS
			MIN	TYP	MAX	MIN	TYP	MAX	
Input Offset Voltage	V _{OS}	MXL1178		30	70		40	120	μV
		MXL1179		35	100		40	150	
		MXL1178S					80	450	
		MXL1179S					90	600	
Long-Term Input Offset-Voltage Stability	$\frac{\Delta V_{OS}}{\Delta \text{Time}}$			0.5			0.6		μV/Mo
Input Offset Current	I _{OS}			0.05	0.25		0.05	0.35	nA
Input Bias Current	I _B			3	5		3	6	nA
Input Noise Voltage	e _n	0.1Hz to 10Hz (Note 1)		0.9	2.0		0.9		μV _{p-p}
Input Noise Voltage Density		f _O = 10Hz (Note 1)		50	75		50		nV/√Hz
		f _O = 1000Hz (Note 1)		49	65		49		
Input Noise Current	i _n	0.1Hz to 10Hz (Note 1)		1.5	2.5		1.5		pA _{p-p}
Input Noise Current Density		f _O = 10Hz (Note 1)		0.03	0.07		0.03		pA/√Hz
		f _O = 1000Hz		0.01			0.01		
Input Resistance	R _{IN}	Differential mode (Note 1)	0.8	2.0		0.6	2.0		GΩ
		Common mode		12			12		
Input Voltage Range			3.5	3.9		3.5	3.9		V
			0	-0.3		0	-0.3		
Common-Mode Rejection Ratio	CMRR	V _{CM} = 0V to 3.5V	93	103		90	102		dB
Power-Supply Rejection Ratio	PSRR	V _S = 2.2V to 12V	94	104		92	104		dB
Large-Signal Voltage Gain	A _{VOL}	V _O = 0.03V to 4V, no load (Note 1)	140	700		110	700		V/mV
		V _O = 0.03V to 3.5V, R _L = 50kΩ	80	200		70	200		
Maximum Output Voltage Swing	V _{OUT}	Output low, no load		6.5	9.0		6.5	9.0	mV
		Output low, 2kΩ to GND		0.2	0.6		0.2	0.6	
		Output low, I _{SINK} = 100μA		120	160		120	160	
		Output high, no load	4.2	4.4		4.2	4.4	V	
		Output high, 2kΩ to GND	3.5	3.8		3.5	3.8		
Slew Rate	SR	A _V = +1, C _L = 10pF (Note 1)	0.013	0.025		0.013	0.025	V/μs	
Gain-Bandwidth Product	GBW	f _O ≤ 5kHz		60		60		kHz	
Supply Current per Amplifier	I _S	V _S = 5V, 0V, V _O = 1.4V		13	18		14	21	μA
		V _S = ±1.5V, V _O = 0V		12	17		13	20	
Channel Separation		ΔV _{IN} = 3V, R _L = 10kΩ		130		130		dB	
Minimum Supply Voltage	V _S	(Note 2)		2.0	2.2		2.0	2.2	V

17 μ A Max, Dual/Quad, Single-Supply, Precision Op Amps

MXL1178/MXL1179

ELECTRICAL CHARACTERISTICS

(V_S = 5V, 0V, V_{CM} = 0.1V, V_O = 1.4V, T_A = -40°C to +85°C for I grades, T_A = 0°C to +70°C for S grades, unless otherwise noted.)
(Note 3)

PARAMETER	SYMBOL	CONDITIONS	MXL1178I MXL1179I			MXL1178S MXL1179S			UNITS
			MIN	TYP	MAX	MIN	TYP	MAX	
Input Offset Voltage	V _{OS}	MXL1178		80	315		120	650	μ V
		MXL1179		80	345		130	800	
Input Offset-Voltage Drift	$\frac{\Delta V_{OS}}{\Delta T}$	(Note 1)		0.6	3.0		0.8	4.5	μ V/°C
Input Offset Current	I _{OS}			0.07	0.7		0.06	0.50	nA
Input Bias Current	I _B			4	8		3	7	nA
Common-Mode Rejection Ratio	CMRR	V _{CM} = 0.05V to 3.2V for I grade	84	98					dB
		V _{CM} = 0V to 3.4V for S grade				86	100		
Power-Supply Rejection Ratio	PSRR	V _S = 3.0V to 12V for I grade	86	100					dB
		V _S = 2.5V to 12V for S grade				88	102		
Large-Signal Voltage Gain	A _{VOL}	V _O = 0.05V to 4V, no load (Note 1)	55	350		80	500		V/mV
		V _O = 0.05V to 3.5V, R _L = 50k Ω	35	130		45	160		
Maximum Output Voltage Swing	V _{OUT}	Output low, no load		9	13		8	11	mV
		Output low, I _{SINK} = 100 μ A		160	220		140	190	
		Output high, no load	3.9	4.2		4.1	4.3		V
		Output high, 2k Ω to GND	3.0	3.7		3.3	3.8		
Supply Current per Amplifier	I _S			15	27		15	24	μ A

ELECTRICAL CHARACTERISTICS

(V_S = 5V, 0V, V_{CM} = 0.1V, V_O = 1.4V, T_A = 0°C to +70°C, unless otherwise noted.)

PARAMETER	SYMBOL	CONDITIONS	MXL1178AC MXL1179AC			MXL1178C MXL1179C			UNITS
			MIN	TYP	MAX	MIN	TYP	MAX	
Input Offset Voltage	V _{OS}	MXL1178		50	170		65	250	μ V
		MXL1179		60	200		70	290	
Input Offset-Voltage Drift	$\frac{\Delta V_{OS}}{\Delta T}$	(Note 1)		0.5	2.2		0.6	3.0	μ V/°C
Input Offset Current	I _{OS}			0.06	0.35		0.06	0.50	nA
Input Bias Current	I _B			3	6		3	7	nA
Common-Mode Rejection Ratio	CMRR	V _{CM} = 0V to 3.4V	90	101		86	100		dB
Power-Supply Rejection Ratio	PSRR	V _S = 2.5V to 12V	90	102		88	102		dB
Large-Signal Voltage Gain	A _{VOL}	V _O = 0.05V to 4V, no load (Note 1)	105	500		80	500		V/mV
		V _O = 0.05V to 3.5V, R _L = 50k Ω	55	160		45	160		
Maximum Output Voltage Swing	V _{OUT}	Output low, no load		8	11		8	11	mV
		Output low, I _{SINK} = 100 μ A		140	190		140	190	
		Output high, no load	4.1	4.3		4.1	4.3		V
		Output high, 2k Ω to GND	3.3	3.8		3.3	3.8		
Supply Current per Amplifier	I _S			14	21		15	24	μ A

17 μ A Max, Dual/Quad, Single-Supply, Precision Op Amps

ELECTRICAL CHARACTERISTICS

(V_S = $\pm$ 15V, T_A = +25°C, unless otherwise noted.)

PARAMETER	SYMBOL	CONDITIONS	MXL1178AC MXL1179AC			MXL1178C/VS MXL1179C/VS			UNITS
			MIN	TYP	MAX	MIN	TYP	MAX	
Input Offset Voltage	V _{OS}		80	350		100	480		μ V
		MXL1178S				150	900		
		MXL1179S				160	1050		
Input Offset Current	I _{OS}		0.05	0.25		0.05	0.35		nA
Input Bias Current	I _B		3	5		3	6		nA
Input Voltage Range			13.5 -15.0	13.9 -15.3		13.5 -15.0	13.9 -15.3		V
Common-Mode Rejection Ratio	CMRR	V _{CM} = +13.5V, -15V	97	106		94	106		dB
Power-Supply Rejection Ratio	PSRR	V _S = 5V, 0V to $\pm$ 18V	96	112		94	112		dB
Large-Signal Voltage Gain	A _{VOL}	V _O = $\pm$ 10V, R _L = 50k Ω	300	1200		250	1000		V/mV
		V _O = $\pm$ 10V, no load	600	2500		400	2500		
Maximum Output Voltage Swing	V _{OUT}	R _L = 50k Ω	$\pm$ 13.0	$\pm$ 14.2		$\pm$ 13.0	$\pm$ 14.2		V
		R _L = 2k Ω	$\pm$ 11.0	$\pm$ 12.7		$\pm$ 11.0	$\pm$ 12.7		
Slew Rate	SR	A _V = +1V	0.02	0.04		0.02	0.04		V/ μ s
Gain Bandwidth Product	GBW	f ₀ $\leq$ 5kHz		85			85		kHz
Supply Current per Amplifier	I _S		16	21		17	25		μ A

ELECTRICAL CHARACTERISTICS

(V_S = $\pm$ 15V, T_A = -40°C to +85°C for I grades, T_A = 0°C to +70°C for S grades, unless otherwise noted.)

PARAMETER	SYMBOL	CONDITIONS	MXL1178I MXL1179I			MXL1178S MXL1179S			UNITS
			MIN	TYP	MAX	MIN	TYP	MAX	
Input Offset Voltage	V _{OS}	MXL1178	130	740		190	1150		μ V
		MXL1179	130	740		200	1300		
Input Offset-Voltage Drift	$\frac{\Delta V_{OS}}{\Delta T}$	(Note 1)	0.7	4.0		0.9	5.5		μ V/ $^{\circ}$ C
Input Offset Current	I _{OS}		0.07	0.7		0.06	0.35		nA
Input Bias Current	I _B		4	8		3	7		nA
Large-Signal Voltage Gain	A _{VOL}	V _O = $\pm$ 10V, R _L = 50k Ω	100	500		150	750		V/mV
Common-Mode Rejection Ratio	CMRR	V _{CM} = +13V, -14.9V	88	103		91	104		dB
Power-Supply Rejection Ratio	PSRR	V _S = 5V, 0V to $\pm$ 18V	88	109		91	110		dB
Maximum Output Voltage Swing	V _{OUT}	R _L = 5k Ω	$\pm$ 11.0	$\pm$ 13.5		$\pm$ 11.0	$\pm$ 13.5		V
Supply Current per Amplifier	I _S		19	30		18	28		μ A

17 μ A Max, Dual/Quad, Single-Supply, Precision Op Amps

MXL1178/MXL1179

ELECTRICAL CHARACTERISTICS

($V_S = \pm 15V$, $T_A = 0^\circ C$ to $+70^\circ C$, unless otherwise noted.)




PARAMETER	SYMBOL	CONDITIONS	MXL1178AC MXL1179AC			MXL1178C MXL1179C			UNITS
			MIN	TYP	MAX	MIN	TYP	MAX	
Input Offset Voltage	V_{OS}			100	480		130	660	μV
Input Offset-Voltage Drift	$\frac{\Delta V_{OS}}{\Delta T}$	(Note 1)		0.6	2.8		0.7	4.0	$\mu V/^\circ C$
Input Offset Current	I_{OS}			0.06	0.35		0.06	0.35	nA
Input Bias Current	I_B			3	6		3	7	nA
Large-Signal Voltage Gain	A_{VOL}	$V_O = \pm 10V$, $R_L = 50k\Omega$	200	800		150	750		V/mV
Common-Mode Rejection Ratio	CMRR	$V_{CM} = +13V$, $-15V$	94	104		91	104		dB
Power-Supply Rejection Ratio	PSRR	$V_S = 5V$, $0V$ to $\pm 18V$	93	110		91	110		dB
Maximum Output Voltage Swing	V_{OUT}	$R_L = 5k\Omega$	± 11.0	± 13.6		± 11.0	± 13.6		V
Supply Current per Amplifier	I_S			17	24		18	28	μA

Note 1: Guaranteed by design.

Note 2: Power-supply rejection ratio is measured at the minimum supply voltage. The op amps actually work at 1.7V supply, but with additional input offset-voltage skew.


Note 3: During testing at $-40^\circ C$, the 5V power-supply turn-on time is less than 0.5sec.

Typical Operating Characteristics




17 μ A Max, Dual/Quad, Single-Supply, Precision Op Amps

Typical Operating Characteristics (continued)




Pin Configurations (continued)



**17μA Max, Dual/Quad, Single-Supply,
Precision Op Amps**


Package Information



MXL1178/MXL1179

17 μ A Max, Dual/Quad, Single-Supply, Precision Op Amps

Package Information (continued)



Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

8 **Maxim Integrated Products, 120 San Gabriel Drive, Sunnyvale, CA 94086 (408) 737-7600**

© 1994 Maxim Integrated Products

Printed USA

MAXIM is a registered trademark of Maxim Integrated Products.