








REV.	DATE	DESCRIPTION
NC	06/21/07	INITIAL RELEASE



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:
1. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS	DATE	Amphenol Connex								
7	CONTACT PIN	BRASS	GOLD	1		DRAWN	G.R.S.						06/21/07			
6	HEX NUT	BRASS	NICKEL	1		CHECKED										
5	WASHER	BRASS	NICKEL	1		ISSUED		PART DESCRIPTION								
4	GASKET	SILICONE	RED	1		SHEET	1 OF 1	BNC CLAMP PLUG (FOR RG-59/U CABLE)								
3	TOP HAT	BRASS	NICKEL	1				PART NO.								
2	INSULATOR	DELTRIN	NATURAL	1				112351								
1	BODY/SHELL	BRASS	NICKEL	1				DWG. NO.			112351.DWG	REV.	NC	SIZE	A	SCALE
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE			C:/112/112351.DWG							

CAD FILE
C:/112/112351.DWG