

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		A	REVISED PER 063B-0047-02	04-FEB-02	KW	CJ

D

C

B





A

D

C

B

A




1 MATERIAL: CONTACTS - BRASS
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
HOLDDOWNS: - PHOSPHOR BRONZE.


2 PLATING: CONTACTS - 0.76µm MINIMUM GOLD ON MATING END,
2.54µm MINIMUM TIN LEAD ON SOLDER TAILS, BOTH OVER
1.27µm MINIMUM NICKEL.
HOLDDOWNS: 2.54µm MINIMUM TIN-LEAD OVER 1.27µm MINIMUM NICKEL.

4 RECOMMENDED PC BOARD THICKNESS OF 1.57.

33.00	40.41	40.00	12	1-1445100-2
30.00	37.41	37.00	11	1-1445100-1
27.00	34.41	34.00	10	1-1445100-0
24.00	31.27	31.00	9	1445100-9
21.00	28.41	28.00	8	1445100-8
18.00	25.41	25.00	7	1445100-7
15.00	22.41	22.00	6	1445100-6
12.00	19.41	19.00	5	1445100-5
9.00	16.41	16.00	4	1445100-4
6.00	13.41	13.00	3	1445100-3
3.00	10.41	10.00	2	1445100-2
DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER



PCB LAYOUT COMPONENT SIDE 4



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN J.ROOT 09OCT2000	AMP Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK K. WHITAKER 17-APR-2001		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. JONES 17-APR-2001	NAME	
0 PLC ±		PRODUCT SPEC	RIGHT ANGLE SURFACE MNT HEADER ASSY,	
1 PLC ±		APPLICATION SPEC	0.76 MIC GOLD CONTACTS, W/SURF MOUNT	
2 PLC ±0.13		WEIGHT	HOLDDOWNS, SGL ROW, MICRO MATE-N-LOK™	
3 PLC ±		CUSTOMER DRAWING	SIZE A2	CAGE CODE 00779
4 PLC ±			DRAWING NO. 1445100	
ANGLES ±			SCALE 5:1	SHEET 1 OF 1
FINISH -			REV A	