



LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	OWN
			L5	REVISED PER ECO-14-015173	08OCT2014	NK

 WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
1/0 AWG STRANDED	1/0 AWG STRANDED	1/0 AWG STRANDED




- 1 STAMP AMP 1/0W* APPROX AS SHOWN
- 2 MATERIAL THK: 1.78±0.08 [.070±.003]
- 3 0.00254 [.000100] MIN TIN PLATE PER ASTM B-545
- 4 GOLD PLATE 0.00127[.000050]MIN. EXT. THK. PER ASTM B488, TYPE 1, CODE C OVER NICKEL PLATE 0.00127 [.000050] MIN. EXT. THK. PER SAE AMS QQ-N-290 OVER Cu FLASH PER SAE AMS 2418.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 42.4-60.6mm ² [83,700-119,500] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

170°C [338°F]	25	LOOSE PIECE	3	8-36917-3
260°C [500°F]	50	LOOSE PIECE	4	36917-1
170°C [338°F]	50	LOOSE PIECE	3	36917
MAX TEMP RATING	QTY	PACKAGE TYPE	FINISH	PART NO.

5 6

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 7/21/91 CHK 8/15/91 RD HEIM APVD 8/15/91 AJ KAUFFMAN	 TE Connectivity	
DIMENSIONS: mm[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME TERMINAL, RING TONGUE, SOLISTRAND	
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± ± - ANGLES	APPLICATION SPEC	SIZE	CAGE CODE
MATERIAL COPPER ASTM B-152 ANNEALED	FINISH SEE TABLE	WEIGHT -	A2	00779
CUSTOMER DRAWING		DRAWING NO G-36917	RESTRICTED TO	
SCALE 2:1		SHEET 1 of 1	REV L5	