MMT05A230T3, MMT05A260T3, MMT05A310T3

Preferred Devices

Thyristor Surge Protectors

High Voltage Bidirectional TSPD

These Thyristor Surge Protective devices (TSPD) prevent overvoltage damage to sensitive circuits by lightning, induction and power line crossings. They are breakover−triggered crowbar protectors. Turn−off occurs when the surge current falls below the holding current value.

Secondary protection applications for electronic telecom equipment at customer premises.

- High Surge Current Capability: **50 Amps** 10 x 1000 μsec; for Controlled Temperature Environments in the **SMA** package
- The MMT05A230T3 Series is used to help equipment meet various regulatory requirements including: Telcordia 1089, ITU K.20 & K.21, IEC 950 and FCC Part 68
- Bidirectional Protection in a Single Device
- Little Change of Voltage Limit with Transient Amplitude or Rate
- Freedom from Wearout Mechanisms Present in Non−Semiconductor Devices
- Fail−Safe, Shorts When Overstressed, Preventing Continued Unprotected Operation
- Surface Mount Technology (SMT)
- Ⓤ Indicates UL Registered − File #E210057
- Device Marking: MMT05A230T3: PBF; MMT05A260T3: PBG; MMT05A310T3: PBJ

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
Off−State Voltage − Maximum MMT05A230T3 MMT05A260T3 MMT05A310T3	V_{DM}	 ±170 ±200 ±270	Volts
Maximum Pulse Surge Short Circuit Current Non−Repetitive Double Exponential Decay Waveform (Notes 1 and 2) 8 x 20 μsec 10 x 160 μsec 10 x 560 μsec 10 x 1000 μsec	 I_{PPS1} I_{PPS2} I_{PPS3} I_{PPS4}	 ±150 ±100 ±70 ±50	A(pk)
Maximum Non−Repetitive Rate of Change of On−State Current Double Exponential Waveform, I_{PK} = 50 A, P_W = 15 μs	di/dt	±100	A/μs

1. Allow cooling before testing second polarity.
2. Measured under pulse conditions to reduce heating.

ON Semiconductor®

http://onsemi.com

BIDIRECTIONAL TSPD
50 AMP SURGE
265 thru 365 VOLTS

SMA
(No Polarity)
CASE 403D

MARKING DIAGRAM

xxx = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week

ORDERING INFORMATION

Device	Package	Shipping†
MMT05A230T3	SMA	12 mm Tape and Reel (5 K/Reel)
MMT05A260T3	SMA	12 mm Tape and Reel (5 K/Reel)
MMT05A310T3	SMA	12 mm Tape and Reel (5 K/Reel)

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

Preferred devices are recommended choices for future use and best overall value.

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Operating Temperature Range Blocking or Conducting State	T_{J1}	−40 to +125	°C
Overload Junction Temperature − Maximum Conducting State Only	T_{J2}	+175	°C
Instantaneous Peak Power Dissipation (I_{pk} = 50A, 10x1000 μsec @ 25°C)	P_{PK}	2000	W
Maximum Lead Temperature for Soldering Purposes 1/8″ from Case for 10 Seconds	T_L	260	°C

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Devices are bidirectional. All electrical parameters apply to forward and reverse polarities.

Characteristics		Symbol	Min	Typ	Max	Unit
Breakover Voltage (Both polarities)		$V_{(BO)}$				Volts
(dv/dt = 100 V/μs, I_{SC} = 1.0 A, Vdc = 1000 V)	MMT05A230T3		−	−	265	
	MMT05A260T3		−	−	320	
	MMT05A310T3		−	−	365	
(+65°C)						
	MMT05A230T3		−	−	280	
	MMT05A260T3		−	−	340	
	MMT05A310T3		−	−	400	
Breakover Voltage (Both polarities)		$V_{(BO)}$				Volts
(f = 60 Hz, I_{SC} = 1.0 A(rms), V_{OC} = 1000 V(rms),	MMT05A230T3		−	−	265	
R_I = 1.0 kΩ, t = 0.5 cycle) (Note 3)	MMT05A260T3		−	−	320	
	MMT05A310T3		−	−	365	
(+65°C)						
	MMT05A230T3		−	−	280	
	MMT05A260T3		−	−	340	
	MMT05A310T3		−	−	400	
Breakover Voltage Temperature Coefficient		$dV_{(BO)}/dT_J$	−	0.08	−	%/°C
Breakdown Voltage ($I_{(BR)}$ = 1.0 mA) Both polarities		$V_{(BR)}$				Volts
	MMT05A230T3		−	190	−	
	MMT05A260T3		−	240	−	
	MMT05A310T3		−	280	−	
Off State Current (V_{D1} = 50 V) Both polarities		I_{D1}	−	−	2.0	μA
(V_{D2} = V_{DM}) Both polarities		I_{D2}	−	−	5.0	
On−State Voltage (I_T = 1.0 A)		V_T	−	1.53	3.0	Volts
(PW ≤ 300 μs, Duty Cycle ≤ 2%) (Note 3)						
Breakover Current (f = 60 Hz, V_{DM} = 1000 V(rms), R_S = 1.0 kΩ) Both polarities		I_{BO}	−	230	−	mA
Holding Current (Both polarities)	(Note 3)	I_H	150	340	−	mA
V_S = 500 Volts; I_T (Initiating Current) = ±1.0 Amp						
Critical Rate of Rise of Off−State Voltage (Linear waveform, V_D = Rated V_{BR}, T_J = 25°C)		dv/dt	2000	−	−	V/μs
Capacitance (f = 1.0 MHz, 50 Vdc, 1.0 V(rms) Signal)		C_O	−	22	−	pF
(f = 1.0 MHz, 2.0 Vdc, 1.0 V(rms) Signal)			−	35	50	

3. Measured under pulse conditions to reduce heating.

Voltage Current Characteristic of TSPD (Bidirectional Device)

Symbol	Parameter
I_{D1}, I_{D2}	Off State Leakage Current
V_{D1}, V_{D2}	Off State Blocking Voltage
V_{BR}	Breakdown Voltage
V_{BO}	Breakover Voltage
I_{BO}	Breakover Current
I_H	Holding Current
V_{TM}	On State Voltage





Figure 1. Off−State Current versus Temperature



Figure 2. Typical Breakdown Voltage versus Temperature



Figure 3. Typical Breakover Voltage versus Temperature



Figure 4. Typical Holding Current versus Temperature



Figure 5. Exponential Decay Pulse Waveform



Figure 6. Peak Surge On−State Current versus Surge Current Duration, Sinusoidal Waveform





*Polymeric PTC (positive temperature coefficient) overcurrent protection device



PACKAGE DIMENSIONS

SMA
CASE 403D−02
ISSUE A



NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. 403D−01 OBSOLETE, NEW STANDARD IS 403D−02.

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
A	0.160	0.180	4.06	4.57
B	0.090	0.115	2.29	2.92
C	0.075	0.095	1.91	2.41
D	0.050	0.064	1.27	1.63
H	0.002	0.006	0.05	0.15
J	0.006	0.016	0.15	0.41
K	0.030	0.060	0.76	1.52
S	0.190	0.220	4.83	5.59

SOLDERING FOOTPRINT*



*For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303−675−2175 or 800−344−3860 Toll Free USA/Canada
Fax: 303−675−2176 or 800−344−3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800−282−9855 Toll Free USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center
2−9−1 Kamimeguro, Meguro−ku, Tokyo, Japan 153−0051
Phone: 81−3−5773−3850

ON Semiconductor Website: http://onsemi.com

Order Literature: http://www.onsemi.com/litorder

For additional information, please contact your local Sales Representative.

MMT05A230T3/D