





MICRO SWITCH
FREEPORT ILLINOIS U.S.A.
A DIVISION OF HONEYWELL
FED MFG CODE 91929

SWITCH - ENCLOSED

CATALOG LISTING
21EN360
U.S. ARMY DRAWING
19207-12294649-3



CIRCUIT DIAGRAM



CONNECTOR MS 3476W8-33PW
OR MS 3116E8-33PW

BOOT 12293286-2

ADAPTER (UNDER BOOT) 12293185-1

SLEEVING PER
MIL-1-23053/5 CLASS 3

SWITCH LABEL
2A29P1(2W6J3)

HEAT MELTABLE
TAPE 2589945-3

72.500^{+2.000}
-0.000

NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
- 3 - TO ADJUST ROLLER DIRECTION, REMOVE ROLLER GUIDE LOCK RING, SCREW ROLLER GUIDE DOWN AS FAR AS POSSIBLE, THEN UNSCREW TO DESIRED DIRECTION. SECURE BY REPLACING ROLLER GUIDE LOCK RING
- 4 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
- 5 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
- 6 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DIMENSIONS UNLESS OTHERWISE SPECIFIED

NO. PLACES	INCHES	MILLIMETERS	INCHES	MILLIMETERS
ONE PLACE	±.001	±.025	±.001	±.025
TWO PLACES	±.0005	±.0125	±.0005	±.0125
THREE PLACES	±.0002	±.005	±.0002	±.005

DESIGN UNITS
INCHES
MILLIMETERS

RAW MATERIAL-COMMERCIAL STANDARD
MICRO SWITCH STANDARDS APPLY
DIMENSIONS ARE TO BE MET BEFORE
PROTECTIVE COATINGS ARE APPLIED

WEIGHT 6.0 OZ MAX

CHARACTERISTICS	
OPERATING FORCE	6-12 LB
FULL OVERTRAVEL FORCE	30 LB MAX
RELEASE FORCE	4 LB MIN
PRETRAVEL	.040 MAX
DIFFERENTIAL TRAVEL	.020 MAX
OVERTRAVEL	.250 MIN

ELECTRICAL DATA		
CONTACT ARRANGEMENT S P D T		
28 VDC		
LOAD	SEA LEVEL	50,000 FT.
RES	4	4
IND	2	2
MOTOR	4	
LAMP		

CATALOG LISTING
21EN360
PAGE 1 OF 1
RELEASE NO PR-15117
REPLACES
ISSUE
M
17
REVISIONS
A 0000487
C S L
9 JUN 03
B 0015678
D D S
16 SEP 03
CHECK
DEC 2 DEC 86
J A S 21 NOV 86
DRAWN
RASTER