



2.4GHz WLAN Antenna + 14dB Antenna

- Panel Antenna
- 2.4 - 2.5GHz
- Active gain: +14dB
- VSWR <2.0:1
- 'U' Bolts Fixing
- RG58 Connecting Lead
- Alternative Connectors:
FME / Mini-UHF / TNC
- Max Power 100W
- Vertical Polarization



Applications

- WLAN
- Range Extension

Description

A rugged high Gain Antenna for 2.4GHz / WLAN applications where high performance is required .

Part Numbers

	Dimensions (mm)	Weight (Kg)	Mount	Connector
ANT-24PANEL14	600 x 200 x 100	2.0	U bolt	'N' Type Female

R F Solutions Ltd.,
Unit 21, Cliffe Industrial Estate,
Lewes, E. Sussex. BN8 6JL. England.

Email : sales@rfsolutions.co.uk <http://www.rfsolutions.co.uk>

Tel: +44 (0)1273 898 000 Fax: +44 (0)1273 480 661




2.4GHz WLAN Antenna + 14dB Antenna

- RG58 Connecting Lead
- 50ohm Impedance
- Horiz Bandwidth 120°
- Vertical Bandwidth 11°
- Operating Temp -40° to +80°
- Construction ABS
- Colour: Grey
- Max Wind Load 60Km/h'
- Alternative Connectors:
FME / Mini-UHF / TNC




Antenna Gain Patterns


Horizontal



Vertical



Return Loss



SWR

