


DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



ORIENTATION



1. SUPPLIED WITH SILVER PLATED
HEX NUT AND LOCKWASHER.
2. TUSONIX STANDARD PART NUMBER: 4201-001.
TUSONIX RoHS COMPLIANT PART NUMBER: 4201-001 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
3. LEAD FINISH: STANDARD PART #: 60/40 SOLDER PLATED. RoHS PART #: SILVER PLATED.
4. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.

CAP. (pF)	WORKING VOLTAGE (VWdc)		CURRENT (Idc)	I.R. MIN. @ 100 VDC	D.W.V.	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
	85°C	125 °C				10 MHz	100 MHz	1 GHz	10 GHz
1500	200	100	10 A	10 G	400 VDC	5	45	65	70

REVISION RECORD Original Release C.O. RDN TO COMP FMT & ADDED METRIC. S.M. 01-21-02 20020121-1-01 DIM'S REV'D .015 REF. WAS .031 ± .010 & .060 REF. WAS 100 ± .015 & MIN. @ 100 VDC ADDED L.E. 04-16-03 20030414-3-01 NOTES 2-4 ADDED. S.M. 04-27-05 20050420-3-02	0	--TOLERANCES-- Unless Otherwise Specified DECIMAL ± .031 [0.79] ANGLES ± 	Title BUSHING STYLE EMI FILTER	
	6		Drawn S.M. 01-21-02	Scale 4 X
	7		Approved T.C. 01-21-02	
	8		A	4201-001
		TUCSONIX TUCSON, ARIZONA		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4201-001LF](#)