





PART NO.	ENG. NO.
02-09-1119	1381-A(P901)L
02-09-1117	1381-A(P901)
02-09-1115	1381-A(P901)1
02-09-5133	1381-A(P591)L
02-09-5130	1381-A(P591)
02-09-5142	1381-A(P550)L
02-09-5143	1381-A(550)



SECT. "A-A"



SECT. "B-B"






STANDARD CHAIN


LEGEND

1381-A(****)*

- P = PREPLATE
 BLANK = POSTPLATE
- FORM
 BLANK = STD. CHAIN
 1 = STD. CHAIN WITH INTERLEAF PAPER
 L = LOOSE
- FINISH CODE



SECT. "C-C"



NOTES:

- MATERIAL: BRASS
- FINISH:
 - 901 HOT TIN DIP .000020/(0.00051) MIN.
 - 591 SELECT GOLD PLATE .000050/(0.00127) MIN. IN CONTACT AREA, OVER .000050/(0.00127) MIN. NICKEL OVERALL WITH .000010/(0.00025) MAX. GOLD FLASH OVERALL.
 - 550 SELECT GOLD PLATE .000015/(0.00038) MIN. IN CONTACT AREA, OVER .000030/(0.00076) MIN. NICKEL OVERALL WITH .000010/(0.00025) MAX. GOLD FLASH OVERALL.
- PRODUCT SPECIFICATION PS-43660-9999.
- PACKAGING INFORMATION: NOT AVAILABLE
- TERMINAL FOR USE WITH .093/(2.36) SERIES HOUSINGS AND WILL ACCEPT 18-22 AWG WIRE
- INSERTION FORCE: 3.5 LBS. MAX. WHEN TERMINAL IS INSERTED INTO AN .093 SERIES HOUSING.
- TERMINAL RETENTION: 20 LBS. MIN. FROM HOUSING.

CORRECT TOLERANCE	REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
				(UNLESS SPECIFIED)			IN/MM		6:1	INCH			
					mm	INCH	DRAWN BY	DATE	TITLE				
				4 PLACES	± ---	± ---	GEP	1987/11/06	CRIMP TERMINAL, FEMALE				
				3 PLACES	± ---	± .010	CHECKED BY	DATE	.093/(2.36) DIA.				
				2 PLACES	± 0.25	± .014	RW	1987/11/06	18-22 AWG				
				1 PLACE	± 0.35	± ---	APPROVED BY	DATE	molex				
0 PLACE	±		RAS	1987/11/06									
				ANGULAR ±1/2°			MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
				DRAFT WHERE APPLICABLE			SEE CHART		SD-1381-*		1 OF 1		
				MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						