

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

- **Low Noise**
10 Hz ... 15 nV/ $\sqrt{\text{Hz}}$
1 kHz ... 10.5 nV/ $\sqrt{\text{Hz}}$
- **10000-pF Load Capability**
- **20-mA Min Short-Circuit Output Current**
- **27-V/ μs Min Slew Rate**
- **High Gain-Bandwidth Product ... 5.9 MHz**
- **Low V_{IO} ... 500 μV Max at 25°C**
- **Single or Split Supply ... 4 V to 44 V**
- **Fast Settling Time**
340 ns to 0.1%
400 ns to 0.01%
- **Saturation Recovery ... 150 ns**
- **Large Output Swing**
 $V_{\text{CC-}} + 0.1 \text{ V}$ to $V_{\text{CC+}} - 1 \text{ V}$

description

The TLE214x and TLE214xA devices are high-performance, internally compensated operational amplifiers built using Texas Instruments complementary bipolar Excalibur process. The TLE214xA is a tighter offset voltage grade of the TLE214x. Both are pin-compatible upgrades to standard industry products.

The design incorporates an input stage that simultaneously achieves low audio-band noise of 10.5 nV/ $\sqrt{\text{Hz}}$ with a 10-Hz 1/f corner and symmetrical 40-V/ μs slew rate typically with loads up to 800 pF. The resulting low distortion and high power bandwidth are important in high-fidelity audio applications. A fast settling time of 340 ns to 0.1% of a 10-V step with a 2-k Ω /100-pF load is useful in fast actuator/positioning drivers. Under similar test conditions, settling time to 0.01% is 400 ns.

The devices are stable with capacitive loads up to 10 nF, although the 6-MHz bandwidth decreases to 1.8 MHz at this high loading level. As such, the TLE214x and TLE214xA are useful for low-droop sample-and-holds and direct buffering of long cables, including 4-mA to 20-mA current loops.

The special design also exhibits an improved insensitivity to inherent integrated circuit component mismatches as is evidenced by a 500- μV maximum offset voltage and 1.7- $\mu\text{V}/^{\circ}\text{C}$ typical drift. Minimum common-mode rejection ratio and supply-voltage rejection ratio are 85 dB and 90 dB, respectively.

Device performance is relatively independent of supply voltage over the $\pm 2\text{-V}$ to $\pm 22\text{-V}$ range. Inputs can operate between $V_{\text{CC-}} - 0.3$ to $V_{\text{CC+}} + 1.8 \text{ V}$ without inducing phase reversal, although excessive input current may flow out of each input exceeding the lower common-mode input range. The all-npn output stage provides a nearly rail-to-rail output swing of $V_{\text{CC-}} - 0.1$ to $V_{\text{CC+}} - 1 \text{ V}$ under light current-loading conditions. The device can sustain shorts to either supply since output current is internally limited, but care must be taken to ensure that maximum package power dissipation is not exceeded.

Both versions can also be used as comparators. Differential inputs of $V_{\text{CC}\pm}$ can be maintained without damage to the device. Open-loop propagation delay with TTL supply levels is typically 200 ns. This gives a good indication as to output stage saturation recovery when the device is driven beyond the limits of recommended output swing.

Both the TLE214x and TLE214xA are available in a wide variety of packages, including both the industry-standard 8-pin small-outline version and chip form for high-density system applications. The C-suffix devices are characterized for operation from 0°C to 70°C, I-suffix devices from -40°C to 105°C, and M-suffix devices over the full military temperature range of -55°C to 125°C.

■ 8961724 0107415 0T0 ■

PRODUCTION DATA Information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



TEXAS
INSTRUMENTS

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 1997, Texas Instruments Incorporated

6-287

TLE214x, TLE214xA, TLE214xY EXCALIBUR LOW-NOISE HIGH-SPEED PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2141 AVAILABLE OPTIONS

T _A	V _{IOmax} AT 25°C	PACKAGED DEVICES				CHIP FORM [‡] (Y)
		SMALL OUT- LINE [†] (D)	CHIP CARRIER (FK)	CERAMIC DIP (JG)	PLASTIC DIP (P)	
0°C to 70°C	500 μ V 900 μ V	TLE2141ACD TLE2141CD	—	—	TLE2141ACP TLE2141CP	—
–40°C to 105°C	500 μ V 900 μ V	TLE2141AID TLE2141ID	—	—	TLE2141AIP TLE2141IP	TLE2141Y
–55°C to 125°C	500 μ V 900 μ V	TLE2141AMD TLE2141MD	TLE2141AMFK TLE2141MFK	TLE2141AMJG TLE2141MJG	TLE2141AMP TLE2141MP	—

[†] The D packages are available taped and reeled. Add R suffix to device type (e.g., TLE2141ACDR).

[‡] Chip forms are tested at T_A = 25°C only.

TLE2142 AVAILABLE OPTIONS

T _A	V _{IOmax} AT 25°C	PACKAGED DEVICES					CHIP FORM [§] (Y)
		SMALL OUTLINE [†] (D)	CHIP CARRIER (FK)	CERAMIC DIP (JG)	PLASTIC DIP (P)	TSSOP [‡] (PW)	
0°C to 70°C	750 μ V 1200 μ V	TLE2142ACD TLE2142CD	— —	— —	TLE2142ACP TLE2142CP	— TLE2142CPWLE	—
–40°C to 105°C	750 μ V 1200 μ V	TLE2142AID TLE2142ID	— —	— —	TLC2142AIP TLC2142IP	— —	TLE2142Y
–55°C to 125°C	750 μ V 1200 μ V	TLE2142AMD TLE2142MD	TLE2142AMFK TLE2142MFK	TLE2142AMJG TLE2142MJG	TLC2142AMP TLC2142MP	— —	—

[†] The D packages are available taped and reeled. Add R suffix to device type (e.g., TLC2142ACDR).

[‡] The PW packages are available left-ended taped and reeled. Add LE the suffix to device type (e.g., TLC2142CPWLE).

[§] Chip forms are tested at T_A = 25°C only.

TLE2144 AVAILABLE OPTIONS

T _A	V _{IOmax} AT 25°C	PACKAGED DEVICES				CHIP FORM [‡] (Y)
		SMALL OUTLINE [†] (DW)	CHIP CARRIER (FK)	CERAMIC DIP (J)	PLASTIC DIP (N)	
0°C to 70°C	1.5 mV 2.4 mV	— TLE2144CDW	— —	— —	TLE2144ACN TLE2144CN	—
–40°C to 105°C	1.5 mV 2.4 mV	— TLE2144IDW	— —	— —	TLE2144AIN TLE2144IN	TLE2144Y
–55°C to 125°C	1.5 mV 2.5 mV	— TLE2144MDW	TLE2144AMFK TLE2144MFK	TLE2144AMJ TLE2144MJ	TLE2144AMN TLE2144MN	—

[†] The DW packages are available taped and reeled. Add R suffix to device type (e.g., TLE2144CDWR).

[‡] Chip forms are tested at T_A = 25°C only.




8961724 0107416 T37








POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY EXCALIBUR LOW-NOISE HIGH-SPEED PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997



NC – No internal connection



8961724 0107417 973


**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-289


TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS
 SLOS183 – FEBRUARY 1997

symbol



TLE2141Y chip information

This chip, when properly assembled, displays characteristics similar to the TLE2141. Thermal compression or ultrasonic bonding may be used on the doped-aluminum bonding pads. Chips may be mounted with conductive epoxy or a gold-silicon preform.



8961724 0107418 80T

TEXAS
INSTRUMENTS


POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2142Y chip information

This chip, when properly assembled, displays characteristics similar to the TLE2142. Thermal compression or ultrasonic bonding may be used on the doped-aluminum bonding pads. Chips may be mounted with conductive epoxy or a gold-silicon preform.



8961724 0107419 746

TEXAS
INSTRUMENTS

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265


6-291

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2144Y chip information

This chip, when properly assembled, displays characteristics similar to the TLE2144. Thermal compression or ultrasonic bonding may be used on the doped-aluminum bonding pads. Chips may be mounted with conductive epoxy or a gold-silicon preform.




8961724 0107420 468

 **TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS
 SLOS183 – FEBRUARY 1997



■ 8961724 0107421 3T4 ■

NOTE A: OFFSET N1 AND OFFSET N2 are only available on the TLE2241x devices.

COMPONENT	ACTUAL DEVICE COMPONENT COUNT			
	TLE2241	TLE2242	TLE2243	TLE2244
Transistors	46	65	130	130
Resistors	24	43	86	86
Diodes	8	14	28	28
Capacitors	4	8	16	16
Epi-FET	1	1	1	2

TEXAS
INSTRUMENTS

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-293

TLE214x, TLE214xA, TLE214xY EXCALIBUR LOW-NOISE HIGH-SPEED PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

Supply voltage, V_{CC+} (see Note 1)	22 V
Supply voltage, V_{CC-}	-22 V
Differential input voltage, V_{ID} (see Note 2)	± 44 V
Input voltage range, V_I (any input)	V_{CC+} to $V_{CC-} - 0.3$ V
Input current, I_I (each input)	± 1 mA
Output current, I_O	± 80 mA
Total current into V_{CC+}	80 mA
Total current out of V_{CC-}	80 mA
Duration of short-circuit current at (or below) 25°C (see Note 3)	unlimited
Continuous total dissipation	See Dissipation Rating Table
Operating free-air temperature range, T_A : C suffix	0°C to 70°C
I suffix	-40°C to 105°C
M suffix	-55°C to 125°C
Storage temperature range	-65°C to 150°C
Case temperature for 60 seconds: FK package	260°C
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds: D, DW, N, P, or PW package	260°C
Lead temperature 1,6 mm (1/16 inch) from case for 60 seconds: J or JG package	300°C

† Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. All voltage values, except differential voltages, are with respect to the midpoint between V_{CC+} and V_{CC-} .
2. Differential voltages are at $IN+$ with respect to $IN-$. Excessive current flows if input is brought below $V_{CC-} - 0.3$ V.
3. The output may be shorted to either supply. Temperature and/or supply voltages must be limited to ensure that the maximum dissipation rating is not exceeded.

DISSIPATION RATING TABLE

PACKAGE	$T_A \leq 25^\circ\text{C}$ POWER RATING	DERATING FACTOR ABOVE $T_A = 25^\circ\text{C}$	$T_A = 70^\circ\text{C}$ POWER RATING	$T_A = 105^\circ\text{C}$ POWER RATING	$T_A = 125^\circ\text{C}$ POWER RATING
D	725 mW	5.8 mW/°C	464 mW	261 mW	145 mW
DW	1025 mW	8.2 mW/°C	656 mW	369 mW	205 mW
FK	1375 mW	11.0 mW/°C	880 mW	495 mW	275 mW
J	1375 mW	11.0 mW/°C	880 mW	495 mW	275 mW
JG	1050 mW	8.4 mW/°C	672 mW	378 mW	210 mW
N	1150 mW	9.2 mW/°C	736 mW	414 mW	230 mW
P	1000 mW	8.0 mW/°C	640 mW	360 mW	200 mW
PW	525 mW	4.2 mW/°C	336 mW	—	—

recommended operating conditions

		C SUFFIX		I SUFFIX		M SUFFIX		UNIT
		MIN	MAX	MIN	MAX	MIN	MAX	
Supply voltage, $V_{CC\pm}$		± 2	± 22	± 2	± 22	± 2	± 22	V
Common-mode input voltage, V_{IC}	$V_{CC} = 5$ V	0	2.9	0	2.7	0	2.7	V
	$V_{CC\pm} = \pm 15$ V	-15	12.9	-15	12.7	-15	12.7	
Operating free-air temperature, T_A		0	70	-40	105	-55	125	°C

8961724 0107422 230



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2141C electrical characteristics at specified free-air temperature, $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS	$T_A^\dagger$	TLE2141C			TLE2141AC			UNIT
			MIN	TYP	MAX	MIN	TYP	MAX	
V_{IO} Input offset voltage	$V_O = 2.5\text{ V}$ $V_{IC} = 2.5\text{ V}$ $R_S = 50\ \Omega$	25°C		225	1400		200	1000	μV
		Full range			1700			1300	
α_{VIO} Temperature coefficient of input offset voltage		Full range		1.7			1.7		$\mu\text{V}/^\circ\text{C}$
I_{IO} Input offset current		25°C		8	100		8	100	nA
		Full range			150			150	
I_{IB} Input bias current		25°C		-0.8	-2		-0.8	-2	μA
		Full range			-2.1			-2.1	
V_{ICR} Common-mode input voltage range	$R_S = 50\ \Omega$	25°C	0 to 3	-0.3 to 3.2		0 to 3	-0.3 to 3.2		V
		Full range	0 to 2.9			0 to 2.9			
V_{OH} High-level output voltage	$I_{OH} = -150\ \mu\text{A}$	25°C	3.9	4.1		3.9	4.1		V
		Full range	3.8			3.8			
	$I_{OH} = -1.5\text{ mA}$	25°C	3.8	4		3.8	4		
		Full range	3.7			3.7			
	$I_{OH} = -15\text{ mA}$	25°C	3.2	3.7		3.2	3.7		
		Full range	3.2			3.2			
V_{OL} Low-level output voltage	$I_{OL} = 150\ \mu\text{A}$	25°C		75	125		75	125	mV
		Full range			150			150	
	$I_{OL} = 1.5\text{ mA}$	25°C		150	225		150	225	V
		Full range			250			250	
	$I_{OL} = 15\text{ mA}$	25°C		1.2	1.6		1.2	1.6	
		Full range			1.7			1.7	
A_{VD} Large-signal differential voltage amplification	$V_{CC} = \pm 2.5\text{ V}$, $R_L = 2\text{ k}\Omega$, $V_O = 1\text{ V}$ to -1.5 V	25°C	50	220		50	220		V/mV
		Full range	25			25			
r_i Input resistance		25°C		70			70		M Ω
c_i Input capacitance		25°C		2.5			2.5		pF
z_o Open-loop output impedance	$f = 1\text{ MHz}$	25°C		30			30		Ω
CMRR Common-mode rejection ratio	$V_{IC} = V_{ICRmin}$, $R_S = 50\ \Omega$	25°C	85	118		85	118		dB
		Full range	80			80			
k_{SVR} Supply-voltage rejection ratio ($\Delta V_{CC\pm}/\Delta V_{IO}$)	$V_{CC\pm} = \pm 2.5\text{ V}$ to $\pm 15\text{ V}$, $R_S = 50\ \Omega$	25°C	90	106		90	106		dB
		Full range	85			85			
I_{CC} Supply current	$V_O = 2.5\text{ V}$, No load, $V_{IC} = 2.5\text{ V}$	25°C		3.4	4.4		3.4	4.4	mA
		Full range			4.6			4.6	

† Full range is 0°C to 70°C.

8961724 0107423 1??



**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-295

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2141C operating characteristics, $V_{CC} = 5\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2141C			TLE2141AC			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	$A_{VD} = -1$, $C_L = 500\text{ pF}^\dagger$, $R_L = 2\text{ k}\Omega^\dagger$		45			45			V/ μs
SR-	Negative slew rate			42			42			
t_s	Settling time	$A_{VD} = -1$, 2.5-V step	To 0.1%	0.16			0.16			μs
			To 0.01%	0.22			0.22			
V_n	Equivalent input noise voltage	$R_S = 20\text{ }\Omega$, $f = 10\text{ Hz}$	15			15			nV/ $\sqrt{\text{Hz}}$	
		$R_S = 20\text{ }\Omega$, $f = 1\text{ kHz}$	10.5			10.5				
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$		0.48			0.48			μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$		0.51			0.51			
I_n	Equivalent input noise current	$f = 10\text{ Hz}$		1.92			1.92			pA/ $\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$		0.5			0.5			
THD + N	Total harmonic distortion plus noise	$V_O = 1\text{ V to }3\text{ V}$, $A_{VD} = 2$, $R_L = 2\text{ k}\Omega^\dagger$, $f = 10\text{ kHz}$		0.0052%			0.0052%			
B_1	Unity-gain bandwidth	$R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}^\dagger$		5.9			5.9			MHz
	Gain-bandwidth product	$R_L = 2\text{ k}\Omega^\dagger$, $f = 100\text{ kHz}$		5.8			5.8			MHz
B_{OM}	Maximum output-swing bandwidth	$V_{O(PP)} = 2\text{ V}$, $A_{VD} = 1$, $R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}^\dagger$		660			660			kHz
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}^\dagger$		57°			57°			

$^\dagger R_L$ and C_L terminated to 2.5 V.

8961724 0107424 003



TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS
 SLOS183 – FEBRUARY 1997

TLE2141C electrical characteristics at specified free-air temperature, $V_{CC\pm} = \pm 15$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS		T _A [†]	TLE2141C			TLE2141AC			UNIT
					MIN	TYP	MAX	MIN	TYP	MAX	
V _{IO}	Input offset voltage	V _{IC} = 0, V _O = 0 R _S = 50 Ω		25°C	200		900	175		500	μV
				Full range		1300		800			
α _{VIO}	Temperature coefficient of input offset voltage			Full range	1.7		1.7				μV/°C
				25°C	7		100	7		100	
I _{IO}	Input offset current			25°C	-0.7		-1.5	-0.7		-1.5	nA
				Full range		150		150			
I _{IB}	Input bias current	25°C	-0.7		-1.5	-0.7		-1.5	μA		
		Full range		-1.6		-1.6					
V _{ICR}	Common-mode input voltage range	R _S = 50 Ω		25°C	-15 to 13	-15.3 to 13.2	-15 to 13		-15.3 to 13.2	V	
				Full range	-15 to 12.9	-15.3 to 13.1	-15 to 12.9		-15.3 to 13.1		
V _{OM+}	Maximum positive peak output voltage swing	I _O = -150 μA I _O = -1.5 mA I _O = -15 mA		25°C	13.8	14.1	13.8		14.1	V	
				Full range		13.7		13.7			
				25°C	13.7	14	13.7		14		
				Full range		13.6		13.6			
				25°C	13.1	13.7	13.1		13.7		
				Full range		13		13			
V _{OM-}	Maximum negative peak output voltage swing	I _O = 150 μA I _O = 1.5 mA I _O = 15 mA		25°C	-14.7	-14.9	-14.7		-14.9	V	
				Full range		-14.6		-14.6			
				25°C	-14.5	-14.8	-14.5		-14.8		
				Full range		-14.4		-14.4			
				25°C	-13.4	-13.8	-13.4		-13.8		
				Full range		-13.3		-13.3			
A _{VD}	Large-signal differential voltage amplification	V _O = ±10 V		25°C	100	450	100		450	V/mV	
				Full range		75		75			
r _i	Input resistance	R _L = 2 kΩ		25°C	65			65		MΩ	
c _i	Input capacitance			25°C	2.5			2.5		pF	
z _o	Open-loop output impedance	f = 1 MHz		25°C	30			30		Ω	
CMRR	Common-mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω		25°C	85	108	85		108	dB	
				Full range		80		80			
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC±} / ΔV _{IO})	V _{CC±} = ±2.5 V to ±15 V, R _S = 50 Ω		25°C	90	106	90		106	dB	
				Full range		85		85			
I _{OS}	Short-circuit output current	V _O = 0	V _{ID} = 1 V	25°C	-25	-50	-25		-50	mA	
			V _{ID} = -1 V		20	31	20		31		
I _{CC}	Supply current	V _O = 0, No load		25°C	3.5		4.5	3.5		4.5	mA
				Full range		4.7		4.7			

† Full range is 0°C to 70°C.

8961724 0107425 T4T



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-297

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2141C operating characteristics, $V_{CC\pm} = \pm 15\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2141C			TLE2141AC			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	$A_{VD} = -1$, $C_L = 500\text{ pF}$	$R_L = 2\text{ k}\Omega$	27	45		27	45		$\text{V}/\mu\text{s}$
SR–	Negative slew rate			27	42		27	42		
t_s	Settling time	$A_{VD} = -1$, 10-V step	To 0.1%		0.34			0.34		μs
			To 0.01%		0.4			0.4		
V_n	Equivalent input noise voltage	$R_S = 20\text{ }\Omega$	$f = 10\text{ Hz}$		15			15		$\text{nV}/\sqrt{\text{Hz}}$
		$R_S = 20\text{ }\Omega$	$f = 1\text{ kHz}$		10.5			10.5		
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$			0.48			0.48		μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$			0.51			0.51		
I_n	Equivalent input noise current	$f = 10\text{ Hz}$			1.89			1.89		$\text{pA}/\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$			0.47			0.47		
THD + N	Total harmonic distortion plus noise	$V_{O(PP)} = 20\text{ V}$, $A_{VD} = 10$,	$R_L = 2\text{ k}\Omega$, $f = 10\text{ kHz}$		0.01%			0.01%		
B_1	Unity-gain bandwidth	$R_L = 2\text{ k}\Omega$,	$C_L = 100\text{ pF}$		6			6		MHz
	Gain-bandwidth product	$R_L = 2\text{ k}\Omega$, $f = 100\text{ kHz}$	$C_L = 100\text{ pF}$		5.9			5.9		MHz
B_{OM}	Maximum output-swing bandwidth	$V_{O(PP)} = 20\text{ V}$, $A_{VD} = 1$,	$R_L = 2\text{ k}\Omega$, $C_L = 100\text{ pF}$		668			668		kHz
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega$,	$C_L = 100\text{ pF}$		58°			58°		

8961724 0107426 986



TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS
SLOS183 – FEBRUARY 1997

TLE2142C electrical characteristics at specified free-air temperature, $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T _A [†]	TLE2142C			TLE2142AC			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
V _{IO}	Input offset voltage	V _O = 2.5 V, R _S = 50 Ω, V _{IC} = 2.5 V	25°C		220	1900		200	1500	μV
			Full range			2200			1800	
α _{VIO}	Temperature coefficient of input offset voltage		Full range		1.7			1.7		μV/°C
I _{IO}	Input offset current		25°C		8	100		8	100	nA
			Full range			150			150	
I _{IB}	Input bias current		25°C		-0.8	-2		-0.8	-2	μA
			Full range			-2.1			-2.1	
V _{ICR}	Common-mode input voltage range		R _S = 50 Ω	25°C	0 to 3	-0.3 to 3.2		0 to 3	-0.3 to 3.2	V
				Full range	0 to 2.9			0 to 2.9		
V _{OH}	High-level output voltage		I _{OH} = -150 μA	25°C	3.9	4.1		3.9	4.1	V
		Full range		3.8			3.8			
		I _{OH} = -1.5 mA	25°C	3.8	4		3.8	4		
			Full range	3.7			3.7			
		I _{OH} = -15 mA	25°C	3.4	3.7		3.4	3.7		
			Full range	3.4			3.4			
V _{OL}	Low-level output voltage	I _{OL} = 150 μA	25°C		75	125		75	125	mV
			Full range			150			150	
		I _{OL} = 1.5 mA	25°C		150	225		150	225	V
			Full range			250			250	
		I _{OL} = 15 mA	25°C		1.2	1.4		1.2	1.4	
			Full range			1.5			1.5	
A _{VD}	Large-signal differential voltage amplification	V _{CC} = ±2.5 V, R _L = 2 kΩ, V _O = 1 V to -1.5 V	25°C	50	220		50	220	V/mV	
			Full range	25			25			
r _i	Input resistance		25°C		70			70	MΩ	
c _i	Input capacitance		25°C		2.5			2.5	pF	
z _o	Open-loop output impedance	f = 1 MHz	25°C		30			30	Ω	
CMRR	Common-mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω	25°C	85	118		85	118	dB	
			Full range	80			80			
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC±} /ΔV _{IO})	V _{CC±} = ±2.5 V to ±15 V, R _S = 50 Ω	25°C	90	106		90	106	dB	
			Full range	85			85			
I _{CC}	Supply current	V _O = 2.5 V, V _{IC} = 2.5 V No load,	25°C		6.6	8.8		6.6	8.8	mA
			Full range			9.2			9.2	

† Full range is 0°C to 70°C.

8961724 0107427 812



**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-299

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2142C operating characteristics, $V_{CC} = 5\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2142C			TLE2142AC			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	$A_{VD} = -1$, $C_L = 500\text{ pF}$	$R_L = 2\text{ k}\Omega^\dagger$	45			45			V/ μs
SR-	Negative slew rate			42			42			
t_s	Settling time	$A_{VD} = -1$, 2.5-V step	To 0.1%	0.16			0.16			μs
			To 0.01%	0.22			0.22			
V_n	Equivalent input noise voltage	$R_S = 20\text{ }\Omega$, $f = 10\text{ Hz}$	15			15			nV/ $\sqrt{\text{Hz}}$	
		$R_S = 20\text{ }\Omega$, $f = 1\text{ kHz}$	10.5			10.5				
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$	0.48			0.48			μV	
		$f = 0.1\text{ Hz to }10\text{ Hz}$	0.51			0.51				
I_n	Equivalent input noise current	$f = 10\text{ Hz}$	1.92			1.92			pA/ $\sqrt{\text{Hz}}$	
		$f = 1\text{ kHz}$	0.5			0.5				
THD + N	Total harmonic distortion plus noise	$V_O = 1\text{ V to }3\text{ V}$, $A_{VD} = 2$, $R_L = 2\text{ k}\Omega^\dagger$, $f = 10\text{ kHz}$	0.0052%			0.0052%				
B1	Unity-gain bandwidth	$R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}$	5.9			5.9			MHz	
	Gain-bandwidth product	$R_L = 2\text{ k}\Omega^\dagger$, $f = 100\text{ kHz}$	5.8			5.8			MHz	
BOM	Maximum output-swing bandwidth	$V_{O(PP)} = 2\text{ V}$, $A_{VD} = 1$, $R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}$	660			660			kHz	
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}$	57°			57°				

$^\dagger R_L$ terminates at 2.5 V.

8961724 0107428 759



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS
SLOS183 – FEBRUARY 1997

TLE2142C electrical characteristics at specified free-air temperature, $V_{CC\pm} = \pm 15$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS		T _A [†]	TLE2142C			TLE2142AC			UNIT		
					MIN	TYP	MAX	MIN	TYP	MAX			
V _{IO}	Input offset voltage	V _{IC} = 0, V _O = 0 R _S = 50 Ω		25°C	290 1200			275 750			μV		
α _{VIO}	Temperature coefficient of input offset voltage			Full range				1200			μV/°C		
				Full range	1.7			1.7					
I _{IO}	Input offset current			25°C	7 100			7 100			nA		
I _{IB}	Input bias current			Full range	150			150			μA		
				25°C	-0.7 -1.5			-0.7 -1.5					
V _{ICR}	Common-mode input voltage range	Full range	-1.6			-1.6							
V _{OM+}	Maximum positive peak output voltage swing	I _O = -150 μA	25°C	13.8 14.1			13.8 14.1			V			
			Full range	13.7			13.7						
		I _O = -1.5 mA	25°C	13.7 14			13.7 14						
			Full range	13.6			13.6						
V _{OM-}	Maximum negative peak output voltage swing	I _O = -15 mA	25°C	13.3 13.7			13.3 13.7			V			
			Full range	13.2			13.2						
		I _O = 150 μA	25°C	-14.7 -14.9			-14.7 -14.9						
			Full range	-14.6			-14.6						
A _{VD}	Large-signal differential voltage amplification	V _O = ±10 V	25°C	100 450			100 450			V/mV			
			Full range	75			75						
		r _i	Input resistance	R _L = 2 kΩ	25°C	65			65			MΩ	
					2.5			2.5					
c _i	Input capacitance		25°C	2.5			2.5			pF			
z _o	Open-loop output impedance	f = 1 MHz	25°C	30			30			Ω			
CMRR	Common-mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω	25°C	85 108			85 108			dB			
			Full range	80			80						
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC±} /ΔV _{IO})	V _{CC±} = ±2.5 V to ±15 V, R _S = 50 Ω	25°C	90 106			90 106			dB			
			Full range	85			85						
I _{OS}	Short-circuit output current	V _O = 0	V _{ID} = 1 V	25°C	-25 -50		-25 -50		mA				
					20 31		20 31						
I _{CC}	Supply current	V _O = 0, No load	V _{ID} = -1 V	25°C	6.9 9		6.9 9		mA				
					Full range		9.4 9.4						

† Full range is 0°C to 70°C.

8961724 0107429 695



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-301

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2142C operating characteristics, $V_{CC\pm} = \pm 15$ V, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2142C			TLE2142AC			UNIT	
				MIN	TYP	MAX	MIN	TYP	MAX		
SR+	Positive slew rate	A _{VD} = −1, C _L = 500 pF	R _L = 2 kΩ,	27	45		27	45	V/μs		
SR−	Negative slew rate			27	42		27	42			
t _s	Settling time	A _{VD} = −1, 10-V step	To 0.1%	0.34			0.34			μs	
			To 0.01%	0.4			0.4				
V _n	Equivalent input noise voltage	R _S = 20 Ω,	f = 10 Hz	15			15			nV/√Hz	
		R _S = 20 Ω,	f = 1 kHz	10.5			10.5				
V _{N(PP)}	Peak-to-peak equivalent input noise voltage	f = 0.1 Hz to 1 Hz			0.48			0.48			μV
		f = 0.1 Hz to 10 Hz			0.51			0.51			
I _n	Equivalent input noise current	f = 10 Hz			1.89			1.89			pA/√Hz
		f = 1 kHz			0.47			0.47			
THD + N	Total harmonic distortion plus noise	V _{O(PP)} = 20 V, A _{VD} = 10,	R _L = 2 kΩ, f = 10 kHz	0.01%			0.01%				
B ₁	Unity-gain bandwidth	R _L = 2 kΩ,	C _L = 100 pF	6			6			MHz	
	Gain-bandwidth product	R _L = 2 kΩ, f = 100 kHz	C _L = 100 pF,	5.9			5.9			MHz	
B _{OM}	Maximum output-swing bandwidth	V _{O(PP)} = 20 V, A _{VD} = 1,	R _L = 2 kΩ, C _L = 100 pF	668			668			kHz	
φ _m	Phase margin at unity gain	R _L = 2 kΩ,	C _L = 100 pF	58°			58°				

8961724 0107430 307



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS
SLOS183 – FEBRUARY 1997

TLE2144C electrical characteristics at specified free-air temperature, $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T _A †	TLE2144C			TLE2144AC			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
V _{IO}	Input offset voltage	V _O = 2.5 V, V _{IC} = 2.5 V R _S = 50 Ω	25°C	0.5 3.8		0.5 3		mV		
			Full range	4.4		3.6				
α _{VIO}	Temperature coefficient of input offset voltage		Full range	1.7		1.7		μV/°C		
I _{IO}	Input offset current		25°C	8 100		8 100		nA		
			Full range	150		150				
I _{IB}	Input bias current		25°C	-0.8 -2		-0.8 -2		μA		
		Full range	-2.1		-2.1					
V _{ICR}	Common-mode input voltage range	R _S = 50 Ω	25°C	0 to 3	-0.3 to 3.2	0 to 3	-0.3 to 3.2	V		
			Full range	0 to 2.9		0 to 2.9				
V _{OH}	High-level output voltage	I _{OH} = -150 μA	25°C	3.9	4.1	3.9	4.1	V		
			Full range	3.8		3.8				
		I _{OH} = -1.5 mA	25°C	3.8	4	3.8	4			
			Full range	3.7		3.7				
		I _{OH} = -15 mA	25°C	3.4	3.7	3.4	3.7			
			Full range	3.4		3.4				
V _{OL}	Low-level output voltage	I _{OL} = 150 μA	25°C	75 125		75 125		mV		
			Full range	150		150				
		I _{OL} = 1.5 mA	25°C	150 225		150 225				
			Full range	250		250				
		I _{OL} = 15 mA	25°C	1.2 1.6		1.2 1.6		V		
			Full range	1.7		1.7				
A _{VD}	Large-signal differential voltage amplification	V _{CC} = ±2.5 V, R _L = 2 kΩ, V _O = 1 V to -1.5 V	25°C	50	95	50	95	V/mV		
			Full range	25		25				
r _i	Input resistance		25°C	70		70		MΩ		
c _i	Input capacitance		25°C	2.5		2.5		pF		
z _o	Open-loop output impedance	f = 1 MHz	25°C	30		30		Ω		
CMRR	Common-mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω	25°C	85	118	85	118	dB		
			Full range	80		80				
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC±} /ΔV _{IO})	V _{CC±} = ±2.5 V to ±15 V, R _S = 50 Ω	25°C	90	106	90	106	dB		
			Full range	85		85				
I _{CC}	Supply current	V _O = 2.5 V, No load, V _{IC} = 2.5 V	25°C	13.2	17.6	13.2	17.6	mA		
			Full range	18.5		18.5				

† Full range is 0°C to 70°C.

8961724 0107431 243



**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-303

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2144C operating characteristics, $V_{CC} = 5\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2144C			TLE2144AC			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	AVD = -1, CL = 500 pF	RL = 2 kΩ†	45			45			V/μs
SR-	Negative slew rate			42			42			
ts	Settling time	AVD = -1, 2.5-V step	To 0.1%	0.16			0.16			μs
			To 0.01%	0.22			0.22			
Vn	Equivalent input noise voltage	RS = 20 Ω,	f = 10 Hz	15			15			nV/√Hz
		RS = 20 Ω,	f = 1 kHz	10.5			10.5			
VN(PP)	Peak-to-peak equivalent input noise voltage	f = 0.1 Hz to 1 Hz		0.48			0.48			μV
		f = 0.1 Hz to 10 Hz		0.51			0.51			
In	Equivalent input noise current	f = 10 Hz		1.92			1.92			pA/√Hz
		f = 1 kHz		0.5			0.5			
THD + N	Total harmonic distortion plus noise	VO = 1 V to 3 V, AVD = 2,	RL = 2 kΩ†, f = 10 kHz	0.0052%			0.0052%			
B1	Unity-gain bandwidth	RL = 2 kΩ†,	CL = 100 pF	5.9			5.9			MHz
	Gain-bandwidth product	RL = 2 kΩ†, f = 100 kHz	CL = 100 pF,	5.8			5.8			MHz
BOM	Maximum output-swing bandwidth	VO(PP) = 2 V, AVD = 1,	RL = 2 kΩ†, CL = 100 pF	660			660			kHz
φm	Phase margin at unity gain	RL = 2 kΩ†,	CL = 100 pF	57°			57°			

$^\dagger R_L$ terminates at 2.5 V

8961724 0107432 18T



TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS
 SLOS183 – FEBRUARY 1997

TLE2144C electrical characteristics at specified free-air temperature, $V_{CC\pm} = \pm 15$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS		T _A †	TLE2144C			TLE2144AC			UNIT
					MIN	TYP	MAX	MIN	TYP	MAX	
V _{IO}	Input offset voltage	V _{IC} = 0, R _S = 50 Ω, V _O = 0		25°C	0.6 2.4			0.5 1.5			mV
	Full range			3.2			2.4				
α _{VIO}	Temperature coefficient of input offset voltage			Full range	1.7			1.7			μV/°C
I _{IO}	Input offset current			25°C	7 100			7 100			
				Full range	150			150			nA
I _{IB}	Input bias current			25°C	-0.7 -1.5			-0.7 -1.5			
		Full range	-1.6			-1.6			μA		
V _{ICR}	Common-mode input voltage range	R _S = 50 Ω	25°C	-15 to 13	-15.3 to 13.2		-15 to 13	-15.3 to 13.2		V	
			Full range	-15 to 12.9	-15.3 to 13.1		-15 to 12.9	-15.3 to 13.1			
V _{OM+}	Maximum positive peak output voltage swing	I _O = -150 μA	25°C	13.8 14.1			13.8 14.1			V	
			Full range	13.7			13.7				
		I _O = -1.5 mA	25°C	13.7 14			13.7 14				
			Full range	13.6			13.6				
		I _O = -15 mA	25°C	13.1 13.7			13.1 13.7				
			Full range	13			13				
V _{OM-}	Maximum negative peak output voltage swing	I _O = 150 μA	25°C	-14.7 -14.9			-14.7 -14.9			V	
			Full range	-14.6			-14.6				
		I _O = 1.5 mA	25°C	-14.5 -14.8			-14.5 -14.8				
			Full range	-14.4			-14.4				
		I _O = 15 mA	25°C	-13.4 -13.8			-13.4 -13.8				
			Full range	-13.3			-13.3				
A _{VD}	Large-signal differential voltage amplification	V _O = ±10 V	25°C	100 170			100 170			V/mV	
			Full range	75			75				
r _i	Input resistance	R _L = 2 kΩ	25°C	65			65			MΩ	
c _i	Input capacitance		25°C	2.5			2.5			pF	
z _o	Open-loop output impedance	f = 1 MHz	25°C	30			30			Ω	
CMRR	Common-mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω		25°C	85 108			85 108			dB
				Full range	80			80			
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC±} /ΔV _{IO})	V _{CC±} = ±2.5 V to ±15 V, R _S = 50 Ω		25°C	90 106			90 106			dB
				Full range	85			85			
I _{OS}	Short-circuit output current	V _O = 0	V _{ID} = 1 V V _{ID} = -1 V	25°C	-25 -50 20 31			-25 -50 20 31			mA
I _{CC}	Supply current	V _O = 0, No load		25°C	13.8 18			13.8 18			mA
				Full range	18.8			18.8			

† Full range is 0°C to 70°C.

8961724 0107433 016



**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-305

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2144C operating characteristics, $V_{CC\pm} = \pm 15\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2144C			TLE2144AC			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	$A_{VD} = -1$, $R_L = 2\text{ k}\Omega$, $C_L = 500\text{ pF}$		27	45		27	45		V/ μ s
SR-	Negative slew rate			27	42		27	42		
t_s	Settling time	$A_{VD} = -1$, 10-V step	To 0.1%	0.34			0.34			μ s
			To 0.01%	0.4			0.4			
V_n	Equivalent input noise voltage	$R_S = 20\text{ }\Omega$	$f = 10\text{ Hz}$	15			15			nV/ $\sqrt{\text{Hz}}$
		$R_S = 20\text{ }\Omega$	$f = 1\text{ kHz}$	10.5			10.5			
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$		0.48			0.48			μ V
		$f = 0.1\text{ Hz to }10\text{ Hz}$		0.51			0.51			
I_n	Equivalent input noise current	$f = 10\text{ Hz}$		1.89			1.89			pA/ $\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$		0.47			0.47			
THD + N	Total harmonic distortion plus noise	$V_{O(PP)} = 20\text{ V}$, $A_{VD} = 10$,	$R_L = 2\text{ k}\Omega$, $f = 10\text{ kHz}$	0.01%			0.01%			
B_1	Unity-gain bandwidth	$R_L = 2\text{ k}\Omega$	$C_L = 100\text{ pF}$	6			6			MHz
	Gain-bandwidth product	$R_L = 2\text{ k}\Omega$, $f = 100\text{ kHz}$	$C_L = 100\text{ pF}$	5.9			5.9			MHz
B_{OM}	Maximum output-swing bandwidth	$V_{O(PP)} = 20\text{ V}$, $A_{VD} = 1$,	$R_L = 2\text{ k}\Omega$, $C_L = 100\text{ pF}$	668			668			kHz
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega$	$C_L = 100\text{ pF}$	58°			58°			

8961724 0107434 T52



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2141I electrical characteristics at specified free-air temperature, $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS	$T_A^\dagger$	TLE2141I			TLE2141AI			UNIT
			MIN	TYP	MAX	MIN	TYP	MAX	
V_{IO} Input offset voltage	$V_O = 2.5\text{ V}$, $V_{IC} = 2.5\text{ V}$ $R_S = 50\ \Omega$	25°C		225	1400		200	1000	μV
		Full range			1900			1500	
α_{VIO} Temperature coefficient of input offset voltage		Full range		1.7			1.7		$\mu\text{V}/^\circ\text{C}$
I_{IO} Input offset current		25°C		8	100		8	100	nA
		Full range			200			200	
I_{IB} Input bias current		25°C		-0.8	-2		-0.8	-2	μA
		Full range			-2.2			-2.2	
V_{ICR} Common-mode input voltage range	$R_S = 50\ \Omega$	25°C	0 to 3	-0.3 to 3.2		0 to 3	-0.3 to 3.2		V
		Full range	0 to 2.7	-0.3 to 2.9		0 to 2.7	-0.3 to 2.9		
V_{OH} High-level output voltage	$I_{OH} = -150\ \mu\text{A}$	25°C	3.9	4.1		3.9	4.1		V
	$I_{OH} = -1.5\text{ mA}$		3.8	4		3.8	4		
	$I_{OH} = -15\text{ mA}$		3.2	3.7		3.2	3.7		
	$I_{OH} = -100\ \mu\text{A}$	Full range	3.8			3.8			
	$I_{OH} = -1\text{ mA}$		3.7			3.7			
	$I_{OH} = -10\text{ mA}$		3.3			3.3			
V_{OL} Low-level output voltage	$I_{OL} = 150\ \mu\text{A}$	25°C		75	125		75	125	mV
	$I_{OL} = 1.5\ \mu\text{A}$			150	225		150	225	
	$I_{OL} = 15\text{ mA}$			1.2	1.6		1.2	1.6	V
	$I_{OL} = 100\ \mu\text{A}$	Full range			175			175	mV
	$I_{OL} = 1\text{ mA}$				225			225	
	$I_{OL} = 10\text{ mA}$				1.4			1.4	V
A_{VD} Large-signal differential voltage amplification	$V_{CC} = \pm 2.5\text{ V}$, $R_L = 2\text{ k}\Omega$, $V_O = 1\text{ V to } -1.5\text{ V}$	25°C	50	220		50	220		V/mV
		Full range	10			10			
r_i Input resistance		25°C		70			70		M Ω
c_i Input capacitance		25°C		2.5			2.5		pF
z_o Open-loop output impedance	$f = 1\text{ MHz}$	25°C		30			30		Ω
CMRR Common-mode rejection ratio	$V_{IC} = V_{ICRmin}$, $R_S = 50\ \Omega$	25°C	85	118		85	118		dB
		Full range	80			80			
k_{SVR} Supply-voltage rejection ratio ($\Delta V_{CC\pm}/\Delta V_{IO}$)	$V_{CC\pm} = \pm 2.5\text{ V to } \pm 15\text{ V}$, $R_S = 50\ \Omega$	25°C	90	106		90	106		dB
		Full range	85			85			
I_{CC} Supply current	$V_O = 2.5\text{ V}$, No load, $V_{IC} = 2.5\text{ V}$	25°C		3.4	4.4		3.4	4.4	mA
		Full range			4.6			4.6	

† Full range is -40°C to 105°C .

■ 8961724 0107435 999 ■



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-307

TLE214x, TLE214xA, TLE214xY

EXCALIBUR LOW-NOISE HIGH-SPEED

PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2141I operating characteristics, $V_{CC} = 5\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2141I			TLE2141AI			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	$A_{VD} = -1$, $C_L = 500\text{ pF}$	$R_L = 2\text{ k}\Omega^\dagger$,	45			45			V/ μ s
SR-	Negative slew rate			42			42			
t_s	Settling time	$A_{VD} = -1$, 2.5-V step	To 0.1%	0.16			0.16			μ s
			To 0.01%	0.22			0.22			
V_n	Equivalent input noise voltage	$R_S = 20\text{ }\Omega$,	$f = 10\text{ Hz}$	15			15			nV/ $\sqrt{\text{Hz}}$
		$R_S = 20\text{ }\Omega$,	$f = 1\text{ kHz}$	10.5			10.5			
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$		0.48			0.48			μ V
		$f = 0.1\text{ Hz to }10\text{ Hz}$		0.51			0.51			
I_n	Equivalent input noise current	$f = 10\text{ Hz}$		1.92			1.92			pA/ $\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$		0.5			0.5			
THD + N	Total harmonic distortion plus noise	$V_O = 1\text{ V to }3\text{ V}$, $A_{VD} = 2$,	$R_L = 2\text{ k}\Omega^\dagger$, $f = 10\text{ kHz}$	0.0052%			0.0052%			
B_1	Unity-gain bandwidth	$R_L = 2\text{ k}\Omega^\dagger$,	$C_L = 100\text{ pF}^\dagger$	5.9			5.9			MHz
	Gain-bandwidth product	$R_L = 2\text{ k}\Omega^\dagger$ $f = 100\text{ kHz}$	$C_L = 100\text{ pF}^\dagger$	5.8			5.8			MHz
B_{OM}	Maximum output-swing bandwidth	$V_{O(PP)} = 2\text{ V}$, $A_{VD} = 1$,	$R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}^\dagger$	660			660			kHz
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega^\dagger$,	$C_L = 100\text{ pF}^\dagger$	57°			57°			

$^\dagger R_L$ and C_L terminated to 2.5 V.

8961724 0107436 825



TEXAS
INSTRUMENTS

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS
SLOS183 – FEBRUARY 1997

TLE2141I electrical characteristics at specified free-air temperature, $V_{CC\pm} = \pm 15$ V (unless otherwise noted)

PARAMETER	TEST CONDITIONS	$T_A^\dagger$	TLE2141I			TLE2141AI			UNIT
			MIN	TYP	MAX	MIN	TYP	MAX	
V_{IO} Input offset voltage	$V_{IC} = 0, R_S = 50 \Omega, V_O = 0$	25°C		200	900		175	500	μV
		Full range			1500			1000	
α_{VIO} Temperature coefficient of input offset voltage		Full range		1.7			1.7		$\mu V/^\circ C$
I_{IO} Input offset current		25°C		7	100		7	100	nA
		Full range			200			200	
I_{IB} Input bias current		25°C		-0.7	-1.5		-0.7	-1.5	μA
		Full range			-1.7			-1.7	
V_{ICR} Common-mode input voltage range	$R_S = 50 \Omega$	25°C	-15 to 13	-15.3 to 13.2		-15 to 13	-15.3 to 13.2		V
		Full range	-15 to 12.7	-15.3 to 12.9		-15 to 12.7	-15.3 to 12.9		
V_{OM+} Maximum positive peak output voltage swing	$I_O = -150 \mu A$	25°C	13.8	14.1		13.8	14.1		V
	$I_O = -1.5$ mA		13.7	14		13.7	14		
	$I_O = -15$ mA		13.1	13.7		13.1	13.7		
	$I_O = -100 \mu A$	Full range	13.7			13.7			
	$I_O = -1$ mA		13.6			13.6			
	$I_O = -10$ mA		13.1			13.1			
V_{OM-} Maximum negative peak output voltage swing	$I_O = 150 \mu A$	25°C	-14.7	-14.9		-14.7	-14.9		V
	$I_O = 1.5$ mA		-14.5	-14.8		-14.5	-14.8		
	$I_O = 15$ mA		-13.4	-13.8		-13.4	-13.8		
	$I_O = 100 \mu A$	Full range	-14.6			-14.6			
	$I_O = 1$ mA		-14.5			-14.5			
	$I_O = 10$ mA		-13.4			-13.4			
A_{VD} Large-signal differential voltage amplification	$V_O = \pm 10$ V, $R_L = 2$ k Ω	25°C	100	450		100	450		V/mV
		Full range	40			40			
r_i Input resistance		25°C		65			65		M Ω
c_i Input capacitance		25°C		2.5			2.5		pF
z_o Open-loop output impedance	$f = 1$ MHz	25°C		30			30		Ω
CMRR Common-mode rejection ratio	$V_{IC} = V_{ICRmin}, R_S = 50 \Omega$	25°C	85	108		85	108		dB
		Full range	80			80			
k_{SVR} Supply-voltage rejection ratio ($\Delta V_{CC\pm} / \Delta V_{IO}$)	$V_{CC\pm} = \pm 2.5$ V to ± 15 V, $R_S = 50 \Omega$	25°C	90	106		90	106		dB
		Full range	85			85			
I_{OS} Short-circuit output current	$V_O = 0$	25°C	-25	-50		-25	-50		mA
			20	31		20	31		
I_{CC} Supply current	$V_O = 0$, No load	25°C		3.5	4.5		3.5	4.5	mA
		Full range			4.7			4.7	

† Full range is -40°C to 105°C.

8961724 0107437 761



**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-309

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2141I operating characteristics, $V_{CC\pm} = \pm 15\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2141I			TLE2141AI			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	$A_{VD} = -1$, $C_L = 500\text{ pF}$		27	45		27	45	V/ μs	
SR-	Negative slew rate			27	42		27	42		
t_s	Settling time	$A_{VD} = -1$, 10-V step	To 0.1%	0.34			0.34			μs
			To 0.01%	0.4			0.4			
V_n	Equivalent input noise voltage	$R_S = 20\ \Omega$, $f = 10\text{ Hz}$		15			15			$\text{nV}/\sqrt{\text{Hz}}$
		$R_S = 20\ \Omega$, $f = 1\text{ kHz}$		10.5			10.5			
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$		0.48			0.48			μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$		0.51			0.51			
I_n	Equivalent input noise current	$f = 10\text{ Hz}$		1.89			1.89			$\text{pA}/\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$		0.47			0.47			
THD + N	Total harmonic distortion plus noise	$V_{O(PP)} = 20\text{ V}$, $A_{VD} = 10$, $R_L = 2\text{ k}\Omega$, $f = 10\text{ kHz}$		0.01%			0.01%			
B_1	Unity-gain bandwidth	$R_L = 2\text{ k}\Omega$, $C_L = 100\text{ pF}$		6			6			MHz
	Gain-bandwidth product	$R_L = 2\text{ k}\Omega$, $f = 100\text{ kHz}$		5.9			5.9			MHz
B_{OM}	Maximum output-swing bandwidth	$V_{O(PP)} = 20\text{ V}$, $A_{VD} = 1$, $R_L = 2\text{ k}\Omega$, $C_L = 100\text{ pF}$		668			668			kHz
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega$, $C_L = 100\text{ pF}$		58°			58°			

8961724 0107438 678



TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2142I electrical characteristics at specified free-air temperature, $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS	$T_A^\dagger$	TLE2142I			TLE2142AI			UNIT
			MIN	TYP	MAX	MIN	TYP	MAX	
V_{IO} Input offset voltage	$V_O = 2.5\text{ V}$, $V_{IC} = 2.5\text{ V}$ $R_S = 50\ \Omega$	25°C		220	1900		220	1500	μV
		Full range			2400			2000	
α_{VIO} Temperature coefficient of input offset voltage		Full range		1.7			1.7		$\mu\text{V}/^\circ\text{C}$
I_{IO} Input offset current		25°C		8	100		8	100	nA
		Full range			200			200	
I_{IB} Input bias current		25°C		-0.8	-2		-0.8	-2	μA
		Full range			-2.2			-2.2	
V_{ICR} Common-mode input voltage range	$R_S = 50\ \Omega$	25°C	0 to 3	-0.3 to 3.2		0 to 3	-0.3 to 3.2		V
		Full range	0 to 2.7	-0.3 to 2.9		0 to 2.7	-0.3 to 2.9		
V_{OH} High-level output voltage	$I_{OH} = -150\ \mu\text{A}$	25°C	3.9	4.1		3.9	4.1		V
	$I_{OH} = -1.5\text{ mA}$		3.8	4		3.8	4		
	$I_{OH} = -15\text{ mA}$		3.4	3.7		3.4	3.7		
	$I_{OH} = 100\ \mu\text{A}$	Full range	3.8			3.8			
	$I_{OH} = 1\text{ mA}$		3.7			3.7			
	$I_{OH} = 10\text{ mA}$		3.5			3.5			
V_{OL} Low-level output voltage	$I_{OL} = 150\ \mu\text{A}$	25°C		75	125		75	125	mV
	$I_{OL} = 1.5\text{ mA}$			150	225		150	225	
	$I_{OL} = 15\text{ mA}$			1.2	1.4		1.2	1.4	V
	$I_{OL} = 100\ \mu\text{A}$	Full range		175			175		mV
	$I_{OL} = 1\text{ mA}$			225			225		
	$I_{OL} = 10\text{ mA}$			1.2			1.2		V
A_{VD} Large-signal differential voltage amplification	$V_{IC} = \pm 2.5\text{ V}$, $R_L = 2\text{ k}\Omega$, $V_O = 1\text{ V to } -1.5\text{ V}$	25°C	50	220		50	220		V/mV
		Full range	10			10			
r_i Input resistance		25°C		70			70		$\text{M}\Omega$
c_i Input capacitance		25°C		2.5			2.5		pF
z_o Open-loop output impedance	$f = 1\text{ MHz}$	25°C		30			30		Ω
CMRR Common-mode rejection ratio	$V_{IC} = V_{ICRmin}$, $R_S = 50\ \Omega$	25°C	85	118		85	118		dB
		Full range	80			80			
kSVR Supply-voltage rejection ratio ($\Delta V_{CC} \pm / \Delta V_{IO}$)	$V_{CC} \pm = \pm 2.5\text{ V to } \pm 15\text{ V}$, $R_S = 50\ \Omega$	25°C	90	106		90	106		dB
		Full range	85			85			
I_{CC} Supply current	$V_O = 2.5\text{ V}$, $V_{IC} = 2.5\text{ V}$ No load,	25°C		6.6	8.8		6.6	8.8	mA
		Full range			9.2			9.2	

† Full range is -40°C to 105°C.

8961724 0107439 534



**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-311

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2142I operating characteristics, $V_{CC} = 5\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2142I			TLE2142AI			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	$A_{VD} = -1$, $C_L = 500\text{ pF}$	$R_L = 2\text{ k}\Omega^\dagger$	45			45			V/ μs
SR-	Negative slew rate			42			42			
t_s	Settling time	$A_{VD} = -1$, 2.5-V step	To 0.1%	0.16			0.16			μs
			To 0.01%	0.22			0.22			
V_n	Equivalent input noise voltage	$R_S = 20\text{ }\Omega$, $f = 10\text{ Hz}$		15			15			nV/ $\sqrt{\text{Hz}}$
		$R_S = 20\text{ }\Omega$, $f = 1\text{ kHz}$		10.5			10.5			
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$		0.48			0.48			μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$		0.51			0.51			
I_n	Equivalent input noise current	$f = 10\text{ Hz}$		1.92			1.92			pA/ $\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$		0.5			0.5			
THD + N	Total harmonic distortion plus noise	$V_O = 1\text{ V to }3\text{ V}$, $A_{VD} = 2$, $R_L = 2\text{ k}\Omega^\dagger$, $f = 10\text{ kHz}$		0.0052%			0.0052%			
B_1	Unity-gain bandwidth	$R_L = 2\text{ k}\Omega^\dagger$	$C_L = 100\text{ pF}$	5.9			5.9			MHz
	Gain-bandwidth product	$R_L = 2\text{ k}\Omega^\dagger$, $f = 100\text{ kHz}$	$C_L = 100\text{ pF}$	5.8			5.8			MHz
B_{OM}	Maximum output-swing bandwidth	$V_{O(PP)} = 2\text{ V}$, $A_{VD} = 1$, $R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}$		660			660			kHz
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega^\dagger$	$C_L = 100\text{ pF}$	57°			57°			

$^\dagger R_L$ terminates at 2.5 V.

8961724 0107440 256



TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2142I electrical characteristics at specified free-air temperature, $V_{CC\pm} = \pm 15$ V (unless otherwise noted)

PARAMETER	TEST CONDITIONS	T_A †	TLE2142I			TLE2142I			UNIT
			MIN	TYP	MAX	MIN	TYP	MAX	
V_{IO} Input offset voltage	$V_{IC} = 0, R_S = 50 \Omega, V_O = 0$	25°C	290	1200		275	750		μV
		Full range		1800			1400		
α_{VIO} Temperature coefficient of input offset voltage		Full range	1.7			1.7			$\mu V/^{\circ}C$
I_{IO} Input offset current		25°C	7	100		7	100		
		Full range		200			200		nA
I_{IB} Input bias current		25°C	-0.7	-1.5		-0.7	-1.5		
		Full range		-1.7			-1.7		μA
V_{ICR} Common-mode input voltage range	$R_S = 50 \Omega$	25°C	-15 to 13	-15.3 to 13.2		-15 to 13	-15.3 to 13.2		V
		Full range	-15 to 12.7	-15.3 to 12.9		-15 to 12.7	-15.3 to 12.9		
V_{OM+} Maximum positive peak output voltage swing	$I_O = -150 \mu A$	25°C	13.8	14.1		13.8	14.1		V
	$I_O = -1.5$ mA		13.7	14		13.7	14		
	$I_O = -15$ mA		13.3	13.7		13.3	13.7		
	$I_O = -100 \mu A$	Full range	13.7			13.7			
	$I_O = -1$ mA		13.6			13.6			
	$I_O = -10$ mA		13.3			13.3			
V_{OM-} Maximum negative peak output voltage swing	$I_O = 150 \mu A$	25°C	-14.7	-14.9		-14.7	-14.9		V
	$I_O = 1.5$ mA		-14.5	-14.8		-14.5	-14.8		
	$I_O = 15$ mA		-13.4	-13.8		-13.4	-13.8		
	$I_O = 100 \mu A$	Full range	-14.6			-14.6			
	$I_O = 1$ mA		-14.5			-14.5			
	$I_O = 10$ mA		-13.4			-13.4			
A_{VD} Large-signal differential voltage amplification	$V_O = \pm 10$ V, $R_L = 2$ k Ω	25°C	100	450		100	450		V/mV
		Full range	40			40			
r_i Input resistance		25°C		65			65		M Ω
c_i Input capacitance		25°C		2.5			2.5		pF
z_o Open-loop output impedance	$f = 1$ MHz	25°C		30			30		Ω
CMRR Common-mode rejection ratio	$V_{IC} = V_{ICRmin}$	25°C	85	108		85	108		dB
	$R_S = 50 \Omega$	Full range	80			80			
ksVR Supply-voltage rejection ratio ($\Delta V_{CC\pm} / \Delta V_{IO}$)	$V_{CC\pm} = \pm 2.5$ V to ± 15 V, $R_S = 50 \Omega$	25°C	90	106		90	106		dB
		Full range	85			85			
I_{OS} Short-circuit output current	$V_O = 0$	25°C	-25	-50		-25	-50		mA
			20	31		20	31		
I_{CC} Supply current	$V_O = 0$, No load	25°C		6.9	9		6.9	9	mA
		Full range			9.4			9.4	

† Full range is -40°C to 105°C.

8961724 0107441 192



TEXAS
INSTRUMENTS

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-313

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2142I operating characteristics, $V_{CC\pm} = \pm 15\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2142I			TLE2142AI			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	$A_{VD} = -1$, $C_L = 500\text{ pF}$	$R_L = 2\text{ k}\Omega$	30	45		30	45	V/ μs	
SR-	Negative slew rate			30	42		30	42		
t_s	Settling time	$A_{VD} = -1$, 10-V step	To 0.1%	0.34		0.34		μs		
			To 0.01%	0.4		0.4				
V_n	Equivalent input noise voltage	$R_S = 20\ \Omega$, $f = 10\text{ Hz}$	15		15		nV/ $\sqrt{\text{Hz}}$			
		$R_S = 20\ \Omega$, $f = 1\text{ kHz}$	10.5		10.5					
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$		0.48		0.48		μV		
		$f = 0.1\text{ Hz to }10\text{ Hz}$		0.51		0.51				
I_n	Equivalent input noise current	$f = 10\text{ Hz}$		1.89		1.89		pA/ $\sqrt{\text{Hz}}$		
		$f = 1\text{ kHz}$		0.47		0.47				
THD + N	Total harmonic distortion plus noise	$V_{O(PP)} = 20\text{ V}$, $A_{VD} = 10$, $R_L = 2\text{ k}\Omega$, $f = 10\text{ kHz}$		0.01%		0.01%				
B_1	Unity-gain bandwidth	$R_L = 2\text{ k}\Omega$	$C_L = 100\text{ pF}$	6		6		MHz		
	Gain-bandwidth product	$R_L = 2\text{ k}\Omega$, $f = 100\text{ kHz}$	$C_L = 100\text{ pF}$	5.9		5.9		MHz		
BOM	Maximum output-swing bandwidth	$V_{O(PP)} = 20\text{ V}$, $A_{VD} = 1$, $R_L = 2\text{ k}\Omega$, $C_L = 100\text{ pF}$		668		668		kHz		
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega$	$C_L = 100\text{ pF}$	58°		58°				

8961724 0107442 029



TEXAS
INSTRUMENTS

6–314

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS
SLOS183 – FEBRUARY 1997

TLE2144I electrical characteristics at specified free-air temperature, $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T _A †	TLE2144I			TLE2144AI			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
V _{IO}	Input offset voltage	V _{IC} = 0, V _O = 0	R _S = 50 Ω	25°C	0.5	3.8	0.5	3	mV	
				Full range		4.8		4		
α _{VIO}	Temperature coefficient of input offset voltage			Full range	1.7	1.7	μV/°C			
I _{IO}	Input offset current			25°C	8	100	8	100	nA	
				Full range	200	200				
I _{IB}	Input bias current			25°C	-0.8	-2	-0.8	-2	μA	
		Full range	-2.2	-2.2						
V _{ICR}	Common-mode input voltage range	R _S = 50 Ω	25°C	0 to 3	-0.3 to 3.2	0 to 3	-0.3 to 3.2	V		
			Full range	0 to 2.7	-0.3 to 2.9	0 to 2.7	-0.3 to 2.9			
V _{OH}	High-level output voltage	25°C		3.9	4.1	3.9	4.1	V		
				3.8	4	3.8	4			
				3.4	3.7	3.4	3.7			
		Full range		3.8	3.8					
				3.7	3.7					
				3.5	3.5					
V _{OL}	Low-level output voltage	25°C		75	125	75	125	mV		
				150	225	150	225			
				1.2	1.6	1.2	1.6			
		Full range		175	175					
				225	225					
				1.4	1.4					
A _{VD}	Large-signal differential voltage amplification	V _{IC} = ±2.5 V, R _L = 2 kΩ, V _O = 1 V to -1.5 V	25°C	50	95	50	95	V/mV		
			Full range	10	10					
r _i	Input resistance		25°C	70	70	MΩ				
c _i	Input capacitance		25°C	2.5	2.5	pF				
z _o	Open-loop output impedance	f = 1 MHz	25°C	30	30	Ω				
CMRR	Common-mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω	25°C	85	118	85	118	dB		
			Full range	80	80					
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC±} /ΔV _{IO})	V _{CC±} = ±2.5 V to ±15 V, R _S = 50 Ω	25°C	90	106	90	106	dB		
			Full range	85	85					
I _{CC}	Supply current	V _O = 2.5 V, V _{IC} = 2.5 V No load,	25°C	13.2	17.6	13.2	17.6	mA		
			Full range	18.4	18.4					

† Full range is -40°C to 105°C .

8961724 0107443 T65



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-315

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2144I operating characteristics, $V_{CC} = 5\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2144I			TLE2144AI			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	$A_{VD} = -1$, $C_L = 500\text{ pF}$	$R_L = 2\text{ k}\Omega^\dagger$	45			45			V/ μs
SR-	Negative slew rate			42			42			
t_s	Settling time	$A_{VD} = -1$, 2.5-V step	To 0.1%	0.16			0.16			μs
			To 0.01%	0.22			0.22			
V_n	Equivalent input noise voltage	$R_S = 20\text{ }\Omega$, $f = 10\text{ Hz}$		15			15			nV/ $\sqrt{\text{Hz}}$
		$R_S = 20\text{ }\Omega$, $f = 1\text{ kHz}$		10.5			10.5			
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$		0.48			0.48			μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$		0.51			0.51			
I_n	Equivalent input noise current	$f = 10\text{ Hz}$		1.92			1.92			pA/ $\sqrt{\text{Hz}}$
		$f = 10\text{ kHz}$		0.5			0.5			
THD + N	Total harmonic distortion plus noise	$V_O = 1\text{ V to }3\text{ V}$, $A_{VD} = 2$, $R_L = 2\text{ k}\Omega^\dagger$, $f = 10\text{ kHz}$		0.0052%			0.0052%			
B_1	Unity-gain bandwidth	$R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}$		5.9			5.9			MHz
	Gain-bandwidth product	$R_L = 2\text{ k}\Omega^\dagger$, $f = 100\text{ kHz}$	$C_L = 100\text{ pF}$	5.8			5.8			MHz
B_{OM}	Maximum output-swing bandwidth	$V_{O(PP)} = 2\text{ V}$, $A_{VD} = 1$, $R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}$		660			660			kHz
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}$		57°			57°			

$^\dagger R_L$ terminates at 2.5 V

8961724 0107444 9T1



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2144I electrical characteristics at specified free-air temperature, $V_{CC\pm} = \pm 15$ V (unless otherwise noted)

PARAMETER	TEST CONDITIONS	T_A †	TLE2144I			TLE2144AI			UNIT
			MIN	TYP	MAX	MIN	TYP	MAX	
V_{IO} Input offset voltage	$V_{IC} = 0$, $V_O = 0$ $R_S = 50\ \Omega$	25°C		0.6	2.4		0.5	1.5	mV
		Full range			3.2			2.8	
α_{IO} Temperature coefficient of input offset voltage		Full range		1.7			1.7		$\mu V/^\circ C$
I_{IO} Input offset current		25°C		7	100		7	100	nA
		Full range			200			200	
I_{IB} Input bias current		25°C		-0.7	-1.5		-0.7	-1.5	μA
		Full range			-1.7			-1.7	
V_{ICR} Common-mode input voltage range	$R_S = 50\ \Omega$	25°C	-15 to 13	-15.3 to 13.2		-15 to 13	-15.3 to 13.2		V
		Full range	-15 to 12.7	-15.3 to 12.9		-15 to 12.7	-15.3 to 12.9		
V_{OM+} Maximum positive peak output voltage swing	$I_O = -150\ \mu A$	25°C	13.8	14.1		13.8	14.1		V
	$I_O = -1.5\ mA$		13.7	14		13.7	14		
	$I_O = -15\ mA$		13.1	13.7		13.1	13.7		
	$I_O = -100\ \mu A$	Full range	13.7			13.7			
	$I_O = -1\ mA$		13.6			13.6			
	$I_O = -10\ mA$		13.1			13.1			
V_{OM-} Maximum negative peak output voltage swing	$I_O = 150\ \mu A$	25°C	-14.7	-14.9		-14.7	-14.9		V
	$I_O = 1.5\ mA$		-14.5	-14.8		-14.5	-14.8		
	$I_O = 15\ mA$		-13.4	-13.8		-13.4	-13.8		
	$I_O = 100\ \mu A$	Full range	-14.6			-14.6			
	$I_O = 1\ mA$		-14.5			-14.5			
	$I_O = 10\ mA$		-13.4			-13.4			
A_{VD} Large-signal differential voltage amplification	$V_O = \pm 10\ V$, $R_L = 2\ k\Omega$	25°C	100	170		100	170		V/mV
		Full range	40			40			
r_i Input resistance		25°C		65		65			$M\Omega$
c_i Input capacitance		25°C		2.5		2.5			pF
z_o Open-loop output impedance	$f = 1\ MHz$	25°C		30		30			Ω
CMRR Common-mode rejection ratio	$V_{IC} = V_{ICRmin}$, $R_S = 50\ \Omega$	25°C	85	108		85	108		dB
		Full range	80			80			
kSVR Supply-voltage rejection ratio ($\Delta V_{CC\pm} / \Delta V_{IO}$)	$V_{CC\pm} = \pm 2.5\ V$ to $\pm 15\ V$, $R_S = 50\ \Omega$	25°C	90	106		90	106		dB
		Full range	85			85			
I_{OS} Short-circuit output current	$V_O = 0$ $V_{ID} = 1\ V$ $V_{ID} = -1\ V$	25°C	-25	-50		-25	-50		mA
			20	31		20	31		
I_{CC} Supply current	$V_O = 0$, No load	25°C		13.8	18		13.8	18	mA
		Full range			18.8			18.8	

† Full range is -40°C to 105°C.

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2144I operating characteristics, $V_{CC\pm} = \pm 15\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2144I			TLE2144AI			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	A _{VD} = −1, C _L = 500 pF	R _L = 2 kΩ	27	45		27	45	V/μs	
SR−	Negative slew rate			27	42		27	42		
t _s	Settling time	A _{VD} = −1, 10-V step	To 0.1%	0.34			0.34			μs
			To 0.01%	0.4			0.4			
V _n	Equivalent input noise voltage	R _S = 20 Ω, f = 10 Hz		15			15			nV/√Hz
		R _S = 20 Ω, f = 1 kHz		10.5			10.5			
V _{N(PP)}	Peak-to-peak equivalent input noise voltage	f = 0.1 Hz to 1 Hz		0.48			0.48			μV
		f = 0.1 Hz to 10 Hz		0.51			0.51			
I _n	Equivalent input noise current	f = 10 Hz		1.89			1.89			pA/√Hz
		f = 1 kHz		0.47			0.47			
THD + N	Total harmonic distortion plus noise	V _{O(PP)} = 20 V, R _L = 2 kΩ, A _{VD} = 10, f = 10 kHz		0.01%			0.01%			
B ₁	Unity-gain bandwidth	R _L = 2 kΩ, C _L = 100 pF		6			6			MHz
	Gain-bandwidth product	R _L = 2 kΩ, C _L = 100 pF, f = 100 kHz		5.9			5.9			MHz
B _{OM}	Maximum output-swing bandwidth	V _{O(PP)} = 20 V, R _L = 2 kΩ, A _{VD} = 1, C _L = 100 pF		668			668			kHz
φ _m	Phase margin at unity gain	R _L = 2 kΩ, C _L = 100 pF		58°			58°			

8961724 0107446 774



TEXAS
INSTRUMENTS

6-318

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2141M electrical characteristics at specified free-air temperature, $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS	$T_A^\dagger$	TLE2141M			TLE2141AM			UNIT
			MIN	TYP	MAX	MIN	TYP	MAX	
V_{IO} Input offset voltage	$V_O = 2.5\text{ V}$ $V_{IC} = 2.5\text{ V}$ $R_S = 50\ \Omega$	25°C		225	1400		200	1000	μV
		Full range			2100			1700	
α_{VIO} Temperature coefficient of input offset voltage		Full range		1.7			1.7		$\mu\text{V}/^\circ\text{C}$
I_{IO} Input offset current		25°C		8	100		8	100	nA
		Full range			250			250	
I_{IB} Input bias current		25°C		-0.8	-2		-0.8	-2	μA
		Full range			-2.3			-2.3	
V_{ICR} Common-mode input voltage range	$R_S = 50\ \Omega$	25°C	0 to 3	-0.3 to 3.2		0 to 3	-0.3 to 3.2		V
		Full range	0 to 2.7	-0.3 to 2.9		0 to 2.7	-0.3 to 2.9		
V_{OH} High-level output voltage	$I_{OH} = -150\ \mu\text{A}$	25°C		3.9	4.1		3.9	4.1	V
	$I_{OH} = -1.5\text{ mA}$			3.8	4		3.8	4	
	$I_{OH} = -15\text{ mA}$			3.2	3.7		3.2	3.7	
	$I_{OH} = -100\ \mu\text{A}$	Full range		3.75			3.75		
	$I_{OH} = -1\text{ mA}$			3.65			3.65		
	$I_{OH} = -10\text{ mA}$			3.25			3.25		
V_{OL} Low-level output voltage	$I_{OL} = 150\ \mu\text{A}$	25°C		75	125		75	125	mV
	$I_{OL} = 1.5\ \mu\text{A}$			150	225		150	225	
	$I_{OL} = 15\text{ mA}$			1.2	1.4		1.2	1.4	V
	$I_{OL} = 100\ \mu\text{A}$	Full range		200			200		mV
	$I_{OL} = 1\text{ mA}$			250			225		
	$I_{OL} = 10\text{ mA}$			1.25			1.25		V
A_{VD} Large-signal differential voltage amplification	$V_{IC} = \pm 2.5\text{ V}$, $R_L = 2\text{ k}\Omega$, $V_O = 1\text{ V to } -1.5\text{ V}$	25°C		50	220		50	220	V/mV
		Full range		5			5		
r_i Input resistance		25°C		70			70		M Ω
c_i Input capacitance		25°C		2.5			2.5		pF
z_o Open-loop output impedance	$f = 1\text{ MHz}$	25°C		30			30		Ω
CMRR Common-mode rejection ratio	$V_{IC} = V_{ICRmin}$, $R_S = 50\ \Omega$	25°C		85	118		85	118	dB
		Full range		80			80		
kSVR Supply-voltage rejection ratio ($\Delta V_{CC} \pm \Delta V_{IO}$)	$V_{CC} \pm \pm 2.5\text{ V to } \pm 15\text{ V}$, $R_S = 50\ \Omega$	25°C		90	106		90	106	dB
		Full range		85			85		
I_{CC} Supply current	$V_O = 2.5\text{ V}$, $V_{IC} = 2.5\text{ V}$ No load,	25°C		3.4	4.4		3.4	4.4	mA
		Full range		4.6			4.6		

† Full range is $-55^\circ\text{C to } 125^\circ\text{C}$.

8961724 0107447 600



**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-319

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2141M operating characteristics, $V_{CC} = 5\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2141M			TLE2141AM			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	$A_{VD} = -1$, $C_L = 500\text{ pF}$	$R_L = 2\text{ k}\Omega^\dagger$		45			45		$\text{V}/\mu\text{s}$
SR–	Negative slew rate				42			42		
t_s	Settling time	$A_{VD} = -1$, 2.5-V step	To 0.1%		0.16			0.16		μs
			To 0.01%		0.22			0.22		
V_n	Equivalent input noise voltage	$R_S = 20\text{ }\Omega$	$f = 10\text{ Hz}$		15			15		$\text{nV}/\sqrt{\text{Hz}}$
		$R_S = 20\text{ }\Omega$	$f = 1\text{ kHz}$		10.5			10.5		
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$			0.48			0.48		μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$			0.51			0.51		
I_n	Equivalent input noise current	$f = 10\text{ Hz}$			1.92			1.92		$\text{pA}/\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$			0.5			0.5		
THD + N	Total harmonic distortion plus noise	$V_O = 1\text{ V to }3\text{ V}$, $A_{VD} = 2$, $R_L = 2\text{ k}\Omega^\dagger$, $f = 10\text{ kHz}$			0.0052%			0.0052%		
B_1	Unity-gain bandwidth	$R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}^\dagger$			5.9			5.9		MHz
	Gain-bandwidth product	$R_L = 2\text{ k}\Omega^\dagger$, $f = 100\text{ kHz}$			5.8			5.8		MHz
B_{OM}	Maximum output-swing bandwidth	$V_{O(PP)} = 2\text{ V}$, $A_{VD} = 1$, $R_L = 2\text{ k}\Omega^\dagger$			660			660		kHz
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}^\dagger$			57°			57°		

$^\dagger R_L$ and C_L terminated to 2.5 V.

8961724 0107448 547



TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2141M electrical characteristics at specified free-air temperature, $V_{CC\pm} = \pm 15$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS		T _A [†]	TLE2141M			TLE2141AM			UNIT
					MIN	TYP	MAX	MIN	TYP	MAX	
V _{IO}	Input offset voltage	V _{IC} = 0, R _S = 50 Ω		25°C	200 900			175 500			μV
	Full range			1700			1200				
α _{VIO}	Temperature coefficient of input offset voltage			Full range	1.7			1.7			μV/°C
I _{IO}	Input offset current			25°C	7 100			7 100			nA
				Full range	250			250			
I _{IB}	Input bias current			25°C	−0.7 −1.5			−0.7 −1.5			μA
		Full range	−1.8			−1.8					
V _{ICR}	Common-mode input voltage range	R _S = 50 Ω		25°C	−15 to 13	−15.3 to 13.2	−15 to 13			−15.3 to 13.2	V
				Full range	−15 to 12.7	−15.3 to 12.9	−15 to 12.7			−15.3 to 12.9	
V _{OM+}	Maximum positive peak output voltage swing			25°C	13.8	14.1	13.8			14.1	V
					13.7	14	13.7			14	
					13.1	13.7	13.1			13.7	
				Full range	13.7	13.7					
					13.6	13.6					
					13.1	13.1					
V _{OM−}	Maximum negative peak output voltage swing			25°C	−14.7	−14.9	−14.7			−14.9	V
					−14.5	−14.8	−14.5			−14.8	
					−13.4	−13.8	−13.4			−13.8	
				Full range	−14.6	−14.6					
					−14.5	−14.5					
					−13.4	−13.4					
A _{VD}	Large-signal differential voltage amplification	V _O = ±10 V, R _L = 2 kΩ		25°C	100	450	100 450			V/mV	
				Full range	20	20					
r _i	Input resistance			25°C	65			65			MΩ
c _i	Input capacitance			25°C	2.5			2.5			pF
z _o	Open-loop output impedance	f = 1 MHz		25°C	30			30			Ω
CMRR	Common-mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω		25°C	85	108	85 108			dB	
				Full range	80	80					
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC±} /ΔV _{IO})	V _{CC±} = ±2.5 V to ±15 V, R _S = 50 Ω		25°C	90	106	90 106			dB	
				Full range	85	85					
I _{OS}	Short-circuit output current	V _O = 0	V _{ID} = 1 V	25°C	−25	−50	−25 −50			mA	
			V _{ID} = −1 V		20	31	20 31				
I _{CC}	Supply current	V _O = 0, V _{IC} = 2.5 V No load,		25°C	3.5 4.5			3.5 4.5			mA
				Full range	4.7			4.7			

† Full range is -55°C to 125°C.

8961724 0107449 483



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-321

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2141M operating characteristics, $V_{CC\pm} = \pm 15\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2141M			TLE2141AM			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	$A_{VD} = -1$, $C_L = 100\text{ pF}$	$R_L = 2\text{ k}\Omega$	27	45		27	45	V/ μs	
SR-	Negative slew rate			27	42		27	42		
t_s	Settling time	$A_{VD} = -1$, 10-V step	To 0.1%	0.34			0.34			μs
			To 0.01%	0.4			0.4			
V_n	Equivalent input noise voltage	$R_S = 20\ \Omega$, $f = 10\text{ Hz}$		15			15			nV/ $\sqrt{\text{Hz}}$
		$R_S = 20\ \Omega$, $f = 1\text{ kHz}$		10.5			10.5			
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$		0.48			0.48			μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$		0.51			0.51			
I_n	Equivalent input noise current	$f = 10\text{ Hz}$		1.89			1.89			pA/ $\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$		0.47			0.47			
THD + N	Total harmonic distortion plus noise	$V_{O(PP)} = 20\text{ V}$, $A_{VD} = 10$,	$R_L = 2\text{ k}\Omega$, $f = 10\text{ kHz}$	0.01%			0.01%			
B_1	Unity-gain bandwidth	$R_L = 2\text{ k}\Omega$,	$C_L = 100\text{ pF}$	6			6			MHz
	Gain-bandwidth product	$R_L = 2\text{ k}\Omega$, $f = 100\text{ kHz}$	$C_L = 100\text{ pF}$,	5.9			5.9			MHz
B_{OM}	Maximum output-swing bandwidth	$V_{O(PP)} = 20\text{ V}$, $A_{VD} = 1$,	$R_L = 2\text{ k}\Omega$, $C_L = 100\text{ pF}$	668			668			kHz
ϕ_m	Phase margin at unity gain	$R_L = 2\text{ k}\Omega$,	$C_L = 100\text{ pF}$	58°			58°			

8961724 0107450 1T5



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2142M electrical characteristics at specified free-air temperature, $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T _A [†]	TLE2142M			TLE2142AM			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
V _{IO}	Input offset voltage	V _O = 2.5 V, V _{IC} = 2.5 V	R _S = 50 Ω,	25°C	220	1900	200	1500	μV	
				Full range	2600		2200			
α _{VIO}	Temperature coefficient of input offset voltage		Full range	1.7		1.7		μV/°C		
I _{IO}	Input offset current		25°C	8	100	8	100	nA		
			Full range	200		200				
I _{IB}	Input bias current		25°C	-0.8	-2	-0.8	-2	μA		
		Full range	-2.3		-2.3					
V _{ICR}	Common-mode input voltage range	R _S = 50 Ω	25°C	0 to 3	-0.3 to 3.2	0 to 3	-0.3 to 3.2	V		
			Full range	0 to 2.7	-0.3 to 2.9	0 to 2.7	-0.3 to 2.9			
V _{OH}	High-level output voltage	I _{OH} = -150 μA	25°C	3.9	4.1	3.9	4.1	V		
				I _{OH} = -1.5 mA	3.8	4	3.8		4	
				I _{OH} = -15 mA	3.4	3.7	3.4		3.7	
		I _{OH} = 100 μA	Full range	3.75		3.75				
				I _{OH} = 1 mA	3.65		3.65			
				I _{OH} = 10 mA	3.45		3.45			
V _{OL}	Low-level output voltage	I _{OL} = 150 μA	25°C	75	125	75	125	mV		
				I _{OL} = 1.5 mA	150	225	150		225	
				I _{OL} = 15 mA	1.2	1.4	1.2	1.4	V	
		I _{OL} = 100 μA	Full range	200		200		mV		
				I _{OL} = 1 mA	250		250			
				I _{OL} = 10 mA	1.25		1.25		V	
A _{VD}	Large-signal differential voltage amplification	V _{IC} = ±2.5 V, R _L = 2 kΩ, V _O = 1 V to -1.5 V	25°C	50	220	50	220	V/mV		
			Full range	5		5				
r _i	Input resistance		25°C	70			70		MΩ	
c _i	Input capacitance		25°C	2.5			2.5		pF	
z _o	Open-loop output impedance	f = 1 MHz	25°C	30			30		Ω	
CMRR	Common-mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω	25°C	85	118	85	118	dB		
			Full range	80		80				
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC±} /ΔV _{IO})	V _{CC±} = ±2.5 V to ±15 V, R _S = 50 Ω	25°C	90	106	90	106	dB		
			Full range	85		85				
I _{CC}	Supply current	V _O = 2.5 V, V _{IC} = 2.5 V	No load,	25°C	6.6	8.8	6.6	8.8	mA	
				Full range		9.2		9.2		

† Full range is -55°C to 125°C .

8961724 0107451 031



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-323

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2142M operating characteristics, $V_{CC} = 5\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER	TEST CONDITIONS	TLE2142M			TLE2142AM			UNIT
		MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	45			45			V/ μs
SR–	Negative slew rate							
		42			42			
t_s	Settling time	0.16			0.16			μs
V_n	Equivalent input noise voltage	15			15			nV/ $\sqrt{\text{Hz}}$
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	0.48			0.48			μV
I_n	Equivalent input noise current	1.92			1.92			pA/ $\sqrt{\text{Hz}}$
THD + N	Total harmonic distortion plus noise	0.0052%			0.0052%			
B_1	Unity-gain bandwidth	5.9			5.9			MHz
	Gain-bandwidth product	5.8			5.8			MHz
B_{OM}	Maximum output-swing bandwidth	660			660			kHz
ϕ_m	Phase margin	57°			57°			

† R_L terminates at 2.5 V.

8961724 0107452 T78



TEXAS
INSTRUMENTS

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2142M electrical characteristics at specified free-air temperature, $V_{CC\pm} = \pm 15$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS		T _A †	TLE2142M			TLE2142AM			UNIT
					MIN	TYP	MAX	MIN	TYP	MAX	
V _{IO}	Input offset voltage	V _{IC} = 0, R _S = 50 Ω		25°C	290 1200			275 750			μV
	Full range			2000			1600				
α _{VIO}	Temperature coefficient of input offset voltage			Full range	1.7			1.7			μV/°C
I _{IO}	Input offset current			25°C	7 100			7 100			
				Full range	250			250			nA
I _{IB}	Input bias current			25°C	−0.7 −1.5			−0.7 −1.5			
		Full range	−1.8			−1.8			μA		
V _{ICR}	Common-mode input voltage range	R _S = 50 Ω	25°C	−15 to 13	−15.3 to 13.2	−15 to 13			−15.3 to 13.2	V	
			Full range	−15 to 12.7	−15.3 to 12.9	−15 to 12.7			−15.3 to 12.9		
V _{OM+}	Maximum positive peak output voltage swing	I _O = −150 μA	25°C	13.8 14.1		13.8 14.1		V			
				13.7 14		13.7 14					
				13.3 13.7		13.3 13.7					
		I _O = −100 μA	Full range	13.7		13.7					
				13.6		13.6					
				13.3		13.3					
V _{OM−}	Maximum negative peak output voltage swing	I _O = 150 μA	25°C	−14.7 −14.9		−14.7 −14.9		V			
				−14.5 −14.8		−14.5 −14.8					
				−13.4 −13.8		−13.4 −13.8					
		I _O = 100 μA	Full range	−14.6		−14.6					
				−14.5		−14.5					
				−13.4		−13.4					
A _{VD}	Large-signal differential voltage amplification	V _O = ±10 V, R _L = 2 kΩ	25°C	100	450	100 450		V/mV			
			Full range	20		20					
r _i	Input resistance		25°C	65			65			MΩ	
c _i	Input capacitance		25°C	2.5			2.5			pF	
z _o	Open-loop output impedance	f = 1 MHz	25°C	30			30			Ω	
CMRR	Common-mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω		25°C	85	108	85 108		dB		
				Full range	80		80				
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC} ± /ΔV _{IO})	V _{CC} ± = ±2.5 V to ±15 V, R _S = 50 Ω		25°C	90	106	90 106		dB		
				Full range	85		85				
I _{OS}	Short-circuit output current	V _O = 0	V _{ID} = 1 V V _{ID} = −1 V	25°C	−25	−50	−25 −50		mA		
					20	31	20 31				
I _{CC}	Supply current	V _O = 0, V _{IC} = 2.5 V No load,		25°C	6.9 9		6.9 9		mA		
				Full range	9.4		9.4				

† Full range is -55°C to 125°C.

8961724 0107453 904



**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-325

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2142M operating characteristics, $V_{CC\pm} = \pm 15\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER	TEST CONDITIONS	TLE2142M			TLE2142AM			UNIT
		MIN	TYP	MAX	MIN	TYP	MAX	
SR+ Positive slew rate	$R_L = 2\text{ k}\Omega$, $A_{VD} = -1$, $C_L = 100\text{ pF}$	27	45		27	45		$\text{V}/\mu\text{s}$
SR– Negative slew rate		27	42		27	42		
t_s Settling time	$A_{VD} = -1$, 10-V step	To 0.1% 0.34			0.34			μs
		To 0.01% 0.4			0.4			
V_n Equivalent input noise voltage	$R_S = 20\text{ }\Omega$, $f = 10\text{ Hz}$ $R_S = 20\text{ }\Omega$, $f = 1\text{ kHz}$	15 10.5			15 10.5			$\text{nV}/\sqrt{\text{Hz}}$
$V_{N(PP)}$ Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$ $f = 0.1\text{ Hz to }10\text{ Hz}$	0.48 0.51			0.48 0.51			μV
I_n Equivalent input noise current	$f = 10\text{ Hz}$ $f = 1\text{ kHz}$	1.89 0.47			1.89 0.47			$\text{pA}/\sqrt{\text{Hz}}$
THD + N Total harmonic distortion plus noise	$V_{O(PP)} = 20\text{ V}$, $R_L = 2\text{ k}\Omega$, $A_{VD} = 10$, $f = 10\text{ kHz}$	0.01%			0.01%			
B_1 Unity-gain bandwidth	$R_L = 2\text{ k}\Omega$, $C_L = 100\text{ pF}$	6			6			MHz
Gain-bandwidth product	$R_L = 2\text{ k}\Omega$, $C_L = 100\text{ pF}$, $f = 100\text{ kHz}$	5.9			5.9			MHz
BOM Maximum output-swing bandwidth	$V_{O(PP)} = 20\text{ V}$, $R_L = 2\text{ k}\Omega$, $A_{VD} = 1$, $C_L = 100\text{ pF}$	668			668			kHz
ϕ_m Phase margin at unity gain	$R_L = 2\text{ k}\Omega$, $C_L = 100\text{ pF}$	58°			58°			

8961724 0107454 840



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS
SLOS183 – FEBRUARY 1997

TLE2144M electrical characteristics at specified free-air temperature, $V_{CC} = 5\text{ V}$ (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T _A [†]	TLE2144M		TLE2144AM		UNIT	
				MIN	TYP	MAX	MIN		TYP
V _{IO}	Input offset voltage	V _O = 2.5 V, V _{IC} = 2.5 V	R _S = 50 Ω,	25°C	0.5	3.8	0.5	3	mV
				Full range	5.2		4.4		
α _{VIO}	Temperature coefficient of input offset voltage		Full range	1.7		1.7		μV/°C	
I _{IO}	Input offset current		25°C	8	100	8	100	nA	
			Full range	250		250			
I _{IB}	Input bias current		25°C	-0.8	-2	-0.8	-2	μA	
		Full range	-2.3		-2.3				
V _{ICR}	Common-mode input voltage range	R _S = 50 Ω	25°C	0 to 3	-0.3 to 3.2	0 to 3	-0.3 to 3.2	V	
			Full range	0 to 2.7	-0.3 to 2.9	0 to 2.7	-0.3 to 2.9		
V _{OH}	High-level output voltage	I _{OH} = -150 μA	25°C	3.9	4.1	3.9	4.1	V	
				I _{OH} = -1.5 mA	3.8	4	3.8		4
				I _{OH} = -15 mA	3.4	3.7	3.4		3.7
		I _{OH} = 100 μA	Full range	3.75		3.75			
				I _{OH} = 1 mA	3.65		3.65		
				I _{OH} = 10 mA	3.45		3.45		
V _{OL}	Low-level output voltage	I _{OL} = 150 μA	25°C	75	125	75	125	mV	
				I _{OL} = 1.5 μA	150	225	150	225	
				I _{OL} = 15 mA	1.2	1.6	1.2	1.6	V
		I _{OL} = 100 μA	Full range	200		200		mV	
				I _{OL} = 1 mA	250		250		
				I _{OL} = 10 mA	1.45		1.45		V
A _{VD}	Large-signal differential voltage amplification	V _{IC} = ±2.5 V, R _L = 2 kΩ, V _O = 1 V to -1.5 V	25°C	50	95	50	95	V/mV	
			Full range	5		5			
r _i	Input resistance		25°C	70		70		MΩ	
c _i	Input capacitance		25°C	2.5		2.5		pF	
z _o	Open-loop output impedance	f = 1 MHz	25°C	30		30		Ω	
CMRR	Common-mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω	25°C	85	118	85	118	dB	
			Full range	80		80			
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC±} /ΔV _{IO})	V _{CC±} = ±2.5 V to ±15 V, R _S = 50 Ω	25°C	90	106	90	106	dB	
			Full range	85		85			
I _{CC}	Supply current	V _O = 2.5 V, No load, V _{IC} = 2.5 V	25°C	13.2	17.6	13.2	17.6	mA	
			Full range	18.4		18.4			

† Full range is -55°C to 125°C .

8961724 0107455 787



**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-327

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2144M operating characteristics, $V_{CC} = 5\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER		TEST CONDITIONS		TLE2144M			TLE2144AM			UNIT
				MIN	TYP	MAX	MIN	TYP	MAX	
SR+	Positive slew rate	$A_{VD} = -1$, $C_L = 500\text{ pF}$		45			45			V/ μs
SR-	Negative slew rate			42			42			
t_s	Settling time	$A_{VD} = -1$, 2.5-V step	To 0.1%	0.16			0.16			μs
			To 0.01%	0.22			0.22			
V_n	Equivalent input noise voltage	$R_S = 20\ \Omega$, $f = 10\text{ Hz}$	15			15			nV/ $\sqrt{\text{Hz}}$	
		$R_S = 20\ \Omega$, $f = 1\text{ kHz}$	10.5			10.5				
$V_{N(PP)}$	Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$		0.48			0.48			μV
		$f = 0.1\text{ Hz to }10\text{ Hz}$		0.51			0.51			
I_n	Equivalent input noise current	$f = 10\text{ Hz}$		1.92			1.92			pA/ $\sqrt{\text{Hz}}$
		$f = 1\text{ kHz}$		0.5			0.5			
THD + N	Total harmonic distortion plus noise	$V_O = 1\text{ V to }3\text{ V}$, $R_L = 2\text{ k}\Omega^\dagger$, $A_{VD} = 2$, $f = 10\text{ kHz}$		0.0052%			0.0052%			
B_1	Unity-gain bandwidth	$R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}$	5.9			5.9			MHz	
	Gain-bandwidth product	$R_L = 2\text{ k}\Omega^\dagger$, $f = 100\text{ kHz}$	5.8			5.8			MHz	
B_{OM}	Maximum output-swing bandwidth	$V_{O(PP)} = 2\text{ V}$, $R_L = 2\text{ k}\Omega^\dagger$, $A_{VD} = 1$	660			660			kHz	
ϕ_m	Phase margin	$R_L = 2\text{ k}\Omega^\dagger$, $C_L = 100\text{ pF}$	57°			57°				

$^\dagger R_L$ terminates at 2.5 V

8961724 0107456 613



TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS
SLOS183 – FEBRUARY 1997

TLE2144M electrical characteristics at specified free-air temperature, $V_{CC\pm} = \pm 15$ V (unless otherwise noted)

PARAMETER		TEST CONDITIONS		T _A †	TLE2144M			TLE2144AM			UNIT
					MIN	TYP	MAX	MIN	TYP	MAX	
V _{IO}	Input offset voltage	V _{IC} = 0, R _S = 50 Ω		25°C	0.6 2.4			0.5 1.5			mV
	Full range			4			3.2				
α _{VIO}	Temperature coefficient of input offset voltage			Full range	1.7			1.7			μV/°C
I _{IO}	Input offset current			25°C	7 100			7 100			
				Full range	250			250			
I _{IB}	Input bias current			25°C	-0.7 -1.5			-0.7 -1.5			μA
		Full range	-1.8			-1.8					
V _{ICR}	Common-mode input voltage range	R _S = 50 Ω		25°C	-15 -15.3 to to 13 13.2			-15 -15.3 to to 13 13.2			V
				Full range	-15 -15.3 to to 12.7 12.9			-15 -15.3 to to 12.7 12.9			
V _{OM+}	Maximum positive peak output voltage swing			25°C	13.8 14.1			13.8 14.1			V
					13.7 14			13.7 14			
					13.1 13.7			13.1 13.7			
				Full range	13.7			13.7			
					13.6			13.6			
					13.1			13.1			
V _{OM-}	Maximum negative peak output voltage swing			25°C	-14.7 -14.9			-14.7 -14.9			V
					-14.5 -14.8			-14.5 -14.8			
					-13.4 -13.8			-13.4 -13.8			
				Full range	-14.6			-14.6			
					-14.5			-14.5			
					-13.4			-13.4			
A _{VD}	Large-signal differential voltage amplification	V _O = ±10 V, R _L = 2 kΩ		25°C	100 170			100 170			V/mV
			Full range	20			20				
r _i	Input resistance			25°C	65			65			MΩ
c _i	Input capacitance			25°C	2.5			2.5			pF
z _o	Open-loop output impedance	f = 1 MHz		25°C	30			30			Ω
CMRR	Common-mode rejection ratio	V _{IC} = V _{ICRmin} , R _S = 50 Ω		25°C	85 108			85 108			dB
				Full range	80			80			
k _{SVR}	Supply-voltage rejection ratio (ΔV _{CC±} / ΔV _{IO})	V _{CC±} = ±2.5 V to ±15 V, R _S = 50 Ω		25°C	90 106			90 106			dB
				Full range	85			85			
I _{OS}	Short-circuit output current	V _O = 0	V _{ID} = 1 V	25°C	-25 -50			-25 -50			mA
			V _{ID} = -1 V		20 31			20 31			
I _{CC}	Supply current	V _O = 0, V _{IC} = 2.5 V	No load,	25°C	13.8 18			13.8 18			mA
				Full range	18.8			18.8			

† Full range is -55°C to 125°C

8961724 0107457 55T



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-329

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2144M operating characteristics, $V_{CC\pm} = \pm 15\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER	TEST CONDITIONS	TLE2144M			TLE2144AM			UNIT
		MIN	TYP	MAX	MIN	TYP	MAX	
SR+ Positive slew rate	$R_L = 2\text{ k}\Omega$ $C_L = 100\text{ pF}$ $A_{VD} = -1$,	27	45		27	45		V/ μs
SR– Negative slew rate		27	42		27	42		
t_s Settling time	$A_{VD} = -1$, 10-V step		0.34 .4			0.34 .4		μs
V_n Equivalent input noise voltage	$R_S = 20\text{ }\Omega$, $f = 10\text{ Hz}$		15			15		$\text{nV}/\sqrt{\text{Hz}}$
	$R_S = 20\text{ }\Omega$, $f = 1\text{ kHz}$		10.5			10.5		
$V_{N(PP)}$ Peak-to-peak equivalent input noise voltage	$f = 0.1\text{ Hz to }1\text{ Hz}$		0.48			0.48		μV
	$f = 0.1\text{ Hz to }10\text{ Hz}$		0.51			0.51		
I_n Equivalent input noise current	$f = 10\text{ Hz}$		1.89			1.89		$\text{pA}/\sqrt{\text{Hz}}$
	$f = 10\text{ kHz}$		0.47			0.47		
THD + N Total harmonic distortion plus noise	$V_O(PP) = 20\text{ V}$, $A_{VD} = 10$, $R_L = 2\text{ k}\Omega$, $f = 10\text{ kHz}$		0.01%			0.01%		
B_1 Unity-gain bandwidth	$R_L = 2\text{ k}\Omega$, $C_L = 100\text{ pF}$		6			6		MHz
Gain-bandwidth product	$R_L = 2\text{ k}\Omega$, $f = 100\text{ kHz}$		5.9			5.9		MHz
B_{OM} Maximum output-swing bandwidth	$V_O(PP) = 20\text{ V}$, $A_{VD} = 1$, $R_L = 2\text{ k}\Omega$, $C_L = 100\text{ pF}$		668			668		kHz
ϕ_m Phase margin at unity gain	$R_L = 2\text{ k}\Omega$, $C_L = 100\text{ pF}$		58°			58°		

8961724 0107458 496



TEXAS
INSTRUMENTS

6–330

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2141Y electrical characteristics at specified free-air temperature, $V_{CC\pm} = \pm 15\text{ V}$, $T_A = 25^\circ\text{C}$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS	TLE2141Y			UNIT
		MIN	TYP	MAX	
V_{IO} Input offset voltage	$V_{IC} = 0$, $R_S = 50\ \Omega$, $V_O = 0$		200	1000	μV
I_{IO} Input offset current			7	100	nA
I_{IB} Input bias current			-0.7	-1.5	μA
V_{ICR} Common-mode input voltage range	$R_S = 50\ \Omega$	-15 to 13	-15.3 to 13.2		V
V_{OM+} Maximum positive peak output voltage swing	$I_O = -150\ \mu\text{A}$	13.8	14.1		V
	$I_O = -1.5\text{ mA}$	13.7	14		
	$I_O = -15\text{ mA}$	13.3	13.7		
V_{OM-} Maximum negative peak output voltage swing	$I_O = 150\ \mu\text{A}$	-14.7	-14.9		V
	$I_O = 1.5\text{ mA}$	-14.5	-14.8		
	$I_O = 15\text{ mA}$	-13.4	-13.8		
A_{VD} Large-signal differential voltage amplification	$V_O = \pm 10\text{ V}$, $R_L = 2\text{ k}\Omega$	100	450		V/mV
r_i Input resistance			65		M Ω
c_i Input capacitance			2.5		pF
z_o Open-loop output impedance	$f = 1\text{ MHz}$		30		Ω
CMRR Common-mode rejection ratio	$V_{IC} = V_{ICRmin}$, $R_S = 50\ \Omega$	80	108		dB
k_{SVR} Supply-voltage rejection ratio ($\Delta V_{CC\pm}/\Delta V_{IO}$)	$V_{CC\pm} = \pm 2.5\text{ V}$ to $\pm 15\text{ V}$, $R_S = 50\ \Omega$	85	106		dB
I_{OS} Short-circuit output current	$V_O = 0$	$V_{ID} = 1\text{ V}$	-25	-50	mA
		$V_{ID} = -1\text{ V}$	20	31	
I_{CC} Supply current	$V_O = 0$, No load		3.5	4.5	mA

8961724 0107459 322



**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-331

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TLE2142Y electrical characteristics at specified free-air temperature, $V_{CC\pm} = \pm 15\text{ V}$, $T_A = 25^\circ\text{C}$

PARAMETER	TEST CONDITIONS	TLE2142Y			UNIT
		MIN	TYP	MAX	
V_{IO} Input offset voltage	$V_{IC} = 0$, $R_S = 50\ \Omega$, $V_O = 0$	150	875		μV
I_{IO} Input offset current		7	100		nA
I_{IB} Input bias current		-0.7	-1.5		μA
V_{ICR} Common-mode input voltage range	$R_S = 50\ \Omega$	-15 to 13	-15.3 to 13.2		V
V_{OM+} Maximum positive peak output voltage swing	$I_O = -150\ \mu\text{A}$	13.8	14.1		V
	$I_O = -1.5\text{ mA}$	13.7	14		
	$I_O = -15\text{ mA}$	13.3	13.7		
V_{OM-} Maximum negative peak output voltage swing	$I_O = 150\ \mu\text{A}$	-14.7	-14.9		V
	$I_O = 1.5\text{ mA}$	-14.5	-14.8		
	$I_O = 15\text{ mA}$	-13.4	-13.8		
A_{VD} Large-signal differential voltage amplification	$V_O = \pm 10\text{ V}$, $R_L = 2\text{ k}\Omega$	100	450		V/mV
r_i Input resistance		65			M Ω
C_i Input capacitance		2.5			pF
Z_o Open-loop output impedance	$f = 1\text{ MHz}$	30			Ω
CMRR Common-mode rejection ratio	$V_{IC} = V_{ICRmin}$, $R_S = 50\ \Omega$	80	108		dB
k_{SVR} Supply-voltage rejection ratio ($\Delta V_{CC\pm} / \Delta V_{IO}$)	$V_{CC\pm} = \pm 2.5\text{ V to } \pm 15\text{ V}$, $R_S = 50\ \Omega$	85	106		dB
I_{OS} Short-circuit output current	$V_O = 0$	$V_{ID} = 1\text{ V}$	-25	-50	mA
		$V_{ID} = -1\text{ V}$	20	31	
I_{CC} Supply current	$V_O = 0$, No load	6.9	9		mA

8961724 0107460 044



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS
SLOS183 – FEBRUARY 1997

TLE2144Y electrical characteristics at $V_{CC\pm} = \pm 15$ V, $T_A = 25^\circ\text{C}$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS	TLE2144Y			UNIT
		MIN	TYP	MAX	
V_{IO} Input offset voltage	$V_{IC} = 0, \quad V_O = 0 \quad R_S = 50 \, \Omega,$		0.3	1.8	mV
I_{IO} Input offset current			7	100	nA
I_{IB} Input bias current			-0.7	-1.5	μA
V_{ICR} Common-mode input voltage range	$R_S = 50 \, \Omega$	-15 to 13	-15.3 to 13.2		V
V_{OM+} Maximum positive peak output voltage swing	$I_O = -150 \, \mu\text{A}$	13.8	14.1		V
	$I_O = -1.5 \, \text{mA}$	13.7	14		
	$I_O = -15 \, \text{mA}$	13.3	13.7		
V_{OM-} Maximum negative peak output voltage swing	$I_O = 150 \, \mu\text{A}$	-14.7	-14.9		V
	$I_O = 1.5 \, \text{mA}$	-14.5	-14.8		
	$I_O = 15 \, \text{mA}$	-13.4	-13.8		
A_{VD} Large-signal differential voltage amplification	$V_O = \pm 10 \, \text{V}, \quad R_L = 2 \, \text{k}\Omega$	100	450		V/mV
r_i Input resistance			65		$\text{M}\Omega$
c_i Input capacitance			2.5		pF
z_o Open-loop output impedance	$f = 1 \, \text{MHz}$		30		Ω
CMRR Common-mode rejection ratio	$V_{IC} = V_{ICRmin}, \quad R_S = 50 \, \Omega$	80	108		dB
ksvr Supply-voltage rejection ratio ($\Delta V_{CC\pm} / \Delta V_{IO}$)	$V_{CC\pm} = \pm 2.5 \, \text{V to } \pm 15 \, \text{V}, \quad R_S = 50 \, \Omega$	85	106		dB
I_{OS} Short-circuit output current	$V_O = 0$	$V_{ID} = 1 \, \text{V}$	-25	-50	mA
		$V_{ID} = -1 \, \text{V}$	20	31	
I_{CC} Supply current	$V_O = 0, \quad \text{No load}$		13.8	18	mA

8961724 0107461 T80



**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-333

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TYPICAL CHARACTERISTICS

Table of Graphs





			FIGURE
V_{IO}	Input offset voltage	Distribution	1, 2, 3
I_{IO}	Input offset current	vs Free-air temperature	4
I_{IB}	Input bias current	vs Common-mode input voltage	5
		vs Free-air temperature	6
V_{OM+}	Maximum positive peak output voltage	vs Supply voltage	7
		vs Free-air temperature	8
		vs Output current	9
		vs Settling time	11
V_{OM-}	Maximum negative peak output voltage	vs Supply voltage	7
		vs Free-air temperature	8
		vs Output current	10
		vs Settling time	11
$V_{O(PP)}$	Maximum peak-to-peak output voltage	vs Frequency	12
V_{OH}	High-level output voltage	vs Output current	13
V_{OL}	Low-level output voltage	vs Output current	14
A_{VD}	Large-signal differential voltage amplification	vs Frequency	15
		vs Free-air temperature	16
z_o	Closed loop output impedance	vs Frequency	17
I_{OS}	Short-circuit output current	vs Free-air temperature	18
$CMRR$	Common-mode rejection ratio	vs Frequency	19
		vs Free-air temperature	20
k_{SVR}	Supply-voltage rejection ratio	vs Frequency	21
		vs Free-air temperature	22
I_{CC}	Supply current	vs Supply voltage	23
		vs Free-air temperature	24
V_n	Equivalent input noise voltage	vs Frequency	25
V_n	Input noise voltage	Over a 10-second period	26
I_n	Noise current	vs Frequency	27
$THD + N$	Total harmonic distortion plus noise	vs Frequency	28
SR	Slew rate	vs Free-air temperature	29
		vs Load capacitance	30
Pulse response	Noninverting large signal	vs Time	31
	Inverting large signal	vs Time	32
	Small signal	vs Time	33
B_1	Unity-gain bandwidth	vs Load capacitance	34
	Gain margin	vs Load capacitance	35
ϕ_m	Phase margin	vs Load capacitance	36
	Phase shift	vs Frequency	15

8961724 0107462 917







POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TYPICAL CHARACTERISTICS



† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

TYPICAL CHARACTERISTICS







† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TYPICAL CHARACTERISTICS



† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.



**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-337

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TYPICAL CHARACTERISTICS

HIGH-LEVEL OUTPUT VOLTAGE†
vs
OUTPUT CURRENT




Figure 13

LOW-LEVEL OUTPUT VOLTAGE†
vs
OUTPUT CURRENT




Figure 14

LARGE-SIGNAL DIFFERENTIAL VOLTAGE
AMPLIFICATION AND PHASE SHIFT

vs
FREQUENCY




Figure 15

† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TYPICAL CHARACTERISTICS

LARGE-SIGNAL DIFFERENTIAL VOLTAGE AMPLIFICATION†




Figure 16

CLOSED-LOOP OUTPUT IMPEDANCE




Figure 17

SHORT-CIRCUIT OUTPUT CURRENT†




Figure 18

† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.

TLE214x, TLE214xA, TLE214xY
EXCALIBUR LOW-NOISE HIGH-SPEED
PRECISION OPERATIONAL AMPLIFIERS

SLOS183 – FEBRUARY 1997

TYPICAL CHARACTERISTICS

COMMON-MODE REJECTION RATIO
vs
FREQUENCY




Figure 19

COMMON-MODE REJECTION RATIO†
vs
FREE-AIR TEMPERATURE




Figure 20

SUPPLY-VOLTAGE REJECTION RATIO
vs
FREQUENCY




Figure 21

SUPPLY-VOLTAGE REJECTION RATIO†
vs
FREE-AIR TEMPERATURE




Figure 22

† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.





8961724 0107468 335



TEXAS
INSTRUMENTS

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

TYPICAL CHARACTERISTICS



† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.







**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-341

TYPICAL CHARACTERISTICS



† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.



**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

8961724 0107470 T93

TYPICAL CHARACTERISTICS




Figure 31




Figure 32




Figure 33




Figure 34

† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.



**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75285

6-343

TYPICAL CHARACTERISTICS




Figure 35




Figure 36

† Data at high and low temperatures are applicable only within the rated operating free-air temperature ranges of the various devices.



TEXAS
INSTRUMENTS

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

APPLICATION INFORMATION

input offset voltage nulling

The TLE2141 series offers external null pins that can be used to further reduce the input offset voltage. If this feature is desired, connect the circuit of Figure 37 as shown. If external nulling is not needed, the null pins may be left unconnected.




Figure 37. Input Offset Voltage Null Circuit

8961724 0107473 7T2



TEXAS
INSTRUMENTS

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

6-345