

MS Series

Microminiature Slide Switches













SPECIFICATIONS	FEATURES
Contact rating: 300 mA at 6 VDC Initial contact resistance: 70 milliohms max. Insulation resistance: 100 megohms max. at 500 VDC Dielectric strength: 500 volts RMS at sea level Electrical life: 10,000 cycles min. Operating temperature range: -10°C to +60°C Solder heat resistance: 260°C max. for 3 seconds Washing not recommended	● Low profile. ● Insert molded terminals. ● Stainless steel cover.
	MATERIALS
	Contacts & terminals: Silver plated Cover: Stainless steel Actuator: Thermoplastic Base: High temperature thermoplastic Terminal seal: Insert molded







MODEL NO. MS12	1P2T VERTICAL ACTUATOR	SCHEMATIC	P.C. BOARD LAYOUT
MODEL NO. MS13	1P3T VERTICAL ACTUATOR	SCHEMATIC	P.C. BOARD CUTOUT
MODEL NO. MS13S	1P3T VERTICAL ACTUATOR	SCHEMATIC	P.C. BOARD LAYOUT

MS Series

Microminiature Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

MODEL NO. MS22  VERTICAL ACTUATOR	2P2T  ● = COMMON  MECHANICAL OUTLINE  P.C. BOARD LAYOUT
MODEL NO. MS22R  RIGHT ANGLE ACTUATOR	2P2T  ● = COMMON  MECHANICAL OUTLINE  P.C. BOARD LAYOUT
MODEL NO. MS23  VERTICAL ACTUATOR	2P3T  ● = COMMON  MECHANICAL OUTLINE  P.C. BOARD LAYOUT
MODEL NO. MS23R  RIGHT ANGLE ACTUATOR	2P3T  ● = COMMON  MECHANICAL OUTLINE  P.C. BOARD LAYOUT

MODEL NO. MS23S  VERTICAL ACTUATOR	2P3T    SCHEMATIC MECHANICAL OUTLINE P.C. BOARD CUTOUT
MODEL NO. MS42R  RIGHT ANGLE ACTUATOR	4P2T    SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE