

DATE	DESCRIPTION	REV.
7.26.99	CHANGE AS PER ECN 99-053	A
6.7.05	CHANGE AS PER ECN 05-030	B

Notes:

Shell: Mat'l: Phosphor Bronze,
Finish: Tin Plate over
Nickel Plate.

Insulator: Mat'l: Thermoplastic
UL 94V-0

Contacts: Mat'l: Phosphor Bronze
Finish: Gold Plate over
Nickel Plate on
Contact Area.
Tin Plate over
Nickel Plate
on Solder Tail.

Electrical Specifications

Rated Voltage:
30V AC (rms)




Contact Current Rating:
1A Max.

Contact Resistance:
30 milliohms Max.

Insulation Resistance:
1000 Megohms Min.

Dielectric Withstanding:
750V AC

Operating Temperature:
32° [0°C] to 104° [40°C]



KEYSTONE ELECTRONICS CORP.			
ASTORIA, N.Y. 11105-2017			
PART NAME			
IEEE 1394 FIREWIRE SM HORIZONTAL SOCKET			
MATERIAL			
AS NOTED			
FINISH		DRN BY	DATE
AS NOTED		BOONE	5.22.98
TOLERANCES		APPD	SCALE
DECIMAL ± .010 [± 0.25]		LN	3X
ANGULAR ± 1°		DWG NO.	
UNLESS OTHERWISE SPECIFIED		C/M	
927			

THIS DOCUMENT IS THE PROPERTY OF
KEYSTONE ELECTRONICS CORP. AND
SHALL NOT BE REPRODUCED, DISTRIBUTED
OR USED AS A BASIS FOR MANUFACTURE
WITHOUT PRIOR WRITTEN PERMISSION
FROM KEYSTONE ELECTRONICS CORP.