

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

C

COPYRIGHT

By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

HB

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

D

REMOVED THE RIB ON THE BASE T O CASE ECO-15-011310

29Feb2016

HYS

CHL

PART A

B

B2

C

TE **US** **OSC**

OJE-SS-118HM18V

10A 250V ~ / 30V

LOT NO.





SEE NOTE 6 B2

OEG


C

PART B

C:MADE IN CHINA



CONNECTION FIGURE

FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING
(BOTTOM VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

H.SASAKI

CHK

Y.OIKAWA

APVD

A.NAGAI

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

±

±

±

±

±

±

±

MATERIAL

FINISH

NAME

H.SASAKI

Y.OIKAWA

A.NAGAI

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

NAME

-

OJE-SH-HM CUSTOMER DRAWING

SIZE

A3

CAGE CODE

00779

DRAWING NO

1461402

RESTRICTED TO

-

SCALE 5:1

SHEET 1 OF 2

REV D

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

C

COPYRIGHT

By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

HB

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

-

SEE SHEET 1

-

-



-

B2	1461402-1	OJE-SH-148HM	107-79010	48V	OJE-SH-148HM	g
	1461402-2	OJE-SH-124HM	107-79010	24V	OJE-SH-124HM	f
	1461402-6	OJE-SH-112HM	107-79010	12V	OJE-SH-112HM	e
B2	1461402-3	OJE-SH-109HM	107-79010	9V	OJE-SH-109HM	d
B2	1461402-5	OJE-SH-106HM	107-79010	6V	OJE-SH-106HM	c
	1461402-4	OJE-SH-105HM	107-79010	5V	OJE-SH-105HM	b
B2	1461402-7	OJE-SH-103HM	107-79010	3V	OJE-SH-103HM	a
	TE CONNECTIVITY PART NO	TE CONNECTIVITY TYPE NAME	PACKAGE SPEC.	PART B	PART A	TYPE

RELAY TYPE

B A NOTES:

1.LOT NO. SYSTEM AS FOLLOWING: B2 5.ADD LOT NO. SYSTEM AS FOLLOWING;



I, DIGITS FOR DAY OF THE WEEK

1...MONDAY IN THIS WEEK;

2...TUESDAY IN THIS WEEK;

.....

7...SUNDAY IN THIS WEEK

II, DIGITS FOR SHIFT OF THE DAY

1...DAY SHIFT IN THIS DAY;

2...NIGHT SHIFT IN THIS DAY;

III, ONE CHARACTER DISTINGUISH THE LINE IDENTITY,
SUCH AS: A,B.....Z

B2 2.TERMINAL DIMENSION IS BEFORE SOLDER DIP;

B2 3.FOR THE TIN-PLATING OF THE PINS:

+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.

+0.5mm FOR LENGTH.

C B2 4.MARKING FROM INK TO LASER AND USING WELDED CONTACT

		UV RESIN	SEAL (VENT HOLE)	16
		EPOXY RESIN	SEAL (BASE & BOBBIN)	15
		3UEW	MAGNETIC WIRE	14
94V-0		P.B.T	CASE	13
94V-0		P.B.T	BASE	12
94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		P.P.S	CARD	9
		Ag ALLOY	MOVABLE CONTACT	8
		Ag	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	PBP	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

H.SASAKI

CHK

Y.OIKAWA

APVD

A.NAGAI

PRODUCT SPEC

SEE PRODUCT SPEC

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

OJE-SH-HM CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C= 1461402

SCALE 5:1

SHEET 2 OF 2

REV D