




1. MATERIALS AND FINISHES (IN MICRO-INCHES)
BODY = BRASS, NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
CONTACT PIN= BERYLLIUM COPPER, GOLD PL. 30 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
LOCK COVER = NYLON66 (WITH 30% GLASS FIBER), COLOR: REFER TO TABLE BELOW FOR KEY CODE
INSULATOR = PTFE PER, NATURAL
FERRULE = COPPER, NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
BARREL = BRASS, NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM (NOMINAL)
B. FREQUENCY RANGE: DC - 6 GHz, (OPTIMIZED FOR DC-4GHz)
C. VSWR (RETURN LOSS): 1.4 (-15.6 dB), MAX. (DC-2GHz)
MATED PAIR 1.5 (-13.9 dB), MAX. (2-3GHz)
D. DIELECTRIC WITHSTANDING VOLTAGE: 800 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY: 100 CYCLES MIN.
B. TEMPERATURE RANGE: -40° C TO 100° C
4. PACKAGING:
A. QUANTITY: TRAY PACK
B. MARKING: TRAY TO BE MARKED
"AMPHENOL, FAI-NXRJ-C01-0,
AND DATE CODE"
5. CRIMPED FERRULE:
HEX. CRIMP SIZE .128"
6. CONTACT PIN TO SOLDER







The diagram shows a side profile of a semi-circular component, likely a connector or ferrule. A vertical centerline is indicated. A dimension line on the right shows a diameter of 5.5. Another dimension line at the bottom shows a length of 1.1. The component has a flat top surface and a curved bottom surface.

TABLE


<u>CODING</u>	<u>PART NO.</u>	<u>DRAWING NO.</u>	<u>COLOR</u>	<u>RAL NO.</u>
A	FAI-NARJ-C01-0	FK6112AW-007-NT30G-50	JET BLACK	9005
B	FAI-NBRJ-C01-0	FK6112BW-007-NT30G-50	CREAM	9001
C	FAI-NCRJ-C01-0	FK6112CW-007-NT30G-50	SIGNAL BLUE	5005
D	FAI-NDRJ-C01-0	FK6112DW-007-NT30G-50	CLARET VIOLET	4004
E	FAI-NERJ-C01-0	FK6112EW-007-NT30G-50	LEAF GREEN	6002
F	FAI-NFRJ-C01-0	FK6112FW-007-NT30G-50	NUT BROWN	8011
G	FAI-NGRJ-C01-0	FK6112GW-007-NT30G-50	BLUE GREY	7031
H	FAI-NHRJ-C01-0	FK6112HW-007-NT30G-50	HEATHER VIOLET	4003
I	FAI-NIRJ-C01-0	FK6112IW-007-NT30G-50	BEIGE	1001
K	FAI-NKRJ-C01-0	FK6112KW-007-NT30G-50	CURRY	1027
L	FAI-NLRJ-C01-0	FK6112LW-007-NT30G-50	CARMINE RED	3002
M	FAI-NMRJ-C01-0	FK6112MW-007-NT30G-50	PASTEL ORANGE	2003
N	FAI-NNRJ-C01-0	FK6112NW-007-NT30G-50	PASTEL GREEN	6019
Z	FAI-NZRJ-C01-0	FK6112ZW-007-NT30G-50	WATER BLUE	5021



SCALE 2.000



RECOMMENDED
CABLE STRIPPING DIM'S I

RECOMMENDED
CABLE STRIPPING DIM'S 2

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp., (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp., the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL	DRAWN EDWARD	DATE 15-May-09	TITLE FAKRA R/A JACK (FOR RG-174/U, 188A/U, 316/U)			Amphenol RF Danbury CT USA, Taiwan, Taiwan, Shenzhen, China www.amphenolrf.com	
		ENGINEER JERRY	DATE 02-May-08				DRAWING NO.	FK6112XX-007-NT30G-50
	REFERENCE	APPROVED SCOTT	DATE 15-May-09				ITEM NO.	FK6112AAX36NC5F
		CAD FILE		SCALE: 5.0:1.0	SHEET 2 OF 2		PART NO.	FAI-NXRJ-C01-0
	FINISH	I:\FAKRA\FK6112XX-007-NT30G-50		DWG SIZE B	CODE ID 74868	REV J		