



LOC	DIST	REVISIONS					
AI	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			D	CONTACT BEND ANGLE CHANGE TO 32°	11DEC2012	KJK	RP



NOTES:

- 1 DIRECTION OF THE TOP OF THE REEL
- 2 COVER TAPE WITH BLISTER BELT WELDED
- 3 PACKING: 1100 CONNECTORS PER REEL
13.8m BLISTER PER REEL
13.8m COVER TAPE PER REEL
- 4 SOLDERLEGS 1. POS. OF EACH CONNECTOR AS SHOWN
IN SHEET 2
- 5 PACKING ACCORDING TO DIN/IEC 286 RESPECTIVELY EIA 481
INCLUDING DECLARATIONS OF THE FIRST AND LAST RUNNING
(DIN/IEC 286 PART 3)
- 6 SEE SHEET 2


BEMERKUNGEN:


- 1 ABWICKELRICHTUNG
- 2 ABDECKBAND MIT BLISTERGURT VERSCHWEIßT
- 3 VERPACKUNG: 1100 BUCHSENSTECKER PRO SPULE
13.8m BLISTERGURT PRO SPULE
13.8m ABDECKBAND PRO SPULE
- 4 LÖTBEINCHEN 1. POS. BEI JEDEM STECKER WIE GEZEICHNET
AUF SHEET 2
- 5 VERPACKUNG ENTSPRECHEND DIN/IEC 286 BZW. EIA 481
INKLUSIVE DER ANGABEN ÜBER DEN VOR- UND NACHLAUF
(DIN/IEC 286 TEIL 3)
- 6 SIEHE SHEET 2

Das mit dieser Zeichnung vorgestellte Produkt wird hiermit zur Fertigung der notwendigen Produktionswerkzeuge freigegeben. Nachträgliche Änderungswünsche gehen zu Lasten des Auftraggebers.

.....
Datum, Firmenstempel und Unter-
schrift des Auftraggebers

	3		HV100 CONNECTOR, SMD, 4 POS.	6	6	4
	3		COVER TAPE B=21.4mm	TRANSPARENT	PET	3
	3		BLISTER BELT A=24mm	BLACK	PS	2
	3		REEL Ø380mm, C = 30.4mm	BLACK	PS	1
	0-1987001-4		DESCRIPTION	SURFACE COLOUR	MATERIAL	ITEM NO
ORDER NO						

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 27MAR2007 G. ACKERMANN CHK 27MAR2007 N. GEISTER APVD 29MAR2007 M. SCHAARSCHMIDT		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±° FINISH		NAME HV100 RECEPTACLE CONNECTOR SINGLE ROW, SMD, PACKED IN BLISTER GOLD VERSION	
		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A2	
MATERIAL SEE TABLE		SEE TABLE		CAGE CODE 00779	
		Customer Drawing		DRAWING NO C-1987001	
				RESTRICTED TO -	
				SCALE 9.1 SHEET 1 OF 2 REV D	



NOTE

7. CONTACT RANGE: 0.8 µm GOLD OVER 1.3 µm Ni
SOLDERING RANGE: 2.5 µm TIN OVER 1.3 µm Ni

8. CAN BE PLUGGED IN WITH MODU II PINS
Ø0.63 OR □0.63 TOP OR BOTTOM ENTRY

9. ONLY WITH THE BOTTOM ENTRY

A	THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN G. ACKERMANN 27MAR2007 CHK N. GEISTER 27MAR2007 APVD M. SCHAARSTHIMMEL 29MAR2007		TE Connectivity				
	DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		NAME HV100 RECEPTACLE CONNECTOR SINGLE ROW, SMD, PACKED IN BLISTER GOLD VERSION				
			0 PLC ±0.20 1 PLC ±0.20 2 PLC ±0.20 3 PLC ±0.20 4 PLC ±0.20 ANGLES ± 5°		APPLICATION SPEC		SIZE A2		CAGE CODE 00779	DRAWING NO. C-1987001	RESTRICTED TO -
	SEE TABLE		SEE TABLE		WEIGHT -		Customer Drawing		SCALE 9:1		SHEET 2 OF 2