

5 Watts

AA05E

Total Power: 5 Watts
Input Voltages: 12V, 24V or 48V
No. of Outputs: Single, Dual



Electrical Specs

Input

Input Range	9-18 Vdc; 18-36 Vdc; 36-72 Vdc
Input Capacitance	2.5 μ F (typ)
Input reverse voltage protection	Fuse recommended
Input Filter	Pi
Efficiency	85% typ

Output

Voltage Tolerance	Output 1 and 2 - $\pm 1\%$
Line Regulation	Output 1 and 2 - $\pm 0.5\%$
Load Regulation	$\pm 1\%$
Noise/Ripple	1 % mV P-P (see note 1)
Short Circuit Protection	Continuous Current Limit
Overvoltage Protection	Zener Clamp
Transient Response	500 μ sec max (50% step load change to within 1%Vo)
Switching Frequency	200kHz
Temperature Coefficient	$\pm 0.02\%/^{\circ}$ C

Isolation

I/O isolation	1500Vdc
Isolation resistance	1 x 10 ⁹ ohms

Special Features

- 2:1 Input range
- 1.25 x 0.80 x 0.40 Case size
- 1500Vdc Isolation

Environmental

Operating ambient temperature
 -40°C to +85°C (full load, no derating)
 Baseplate: 100°C max
 Storage temperature: -40°C to +125°C
 Humidity: 5% to 95%(non-condensing)
 Cooling method: Convection
 MTBF: >1,000,000 hours (MIL-HDBK-217F)
 Conducted EMI: EN55022, Class B
 UL, CSA, EN60950 Certified

AMERICAS

5810 Van Allen Way
Carlsbad, CA 92008
Telephone: 760-930-4600
Facsimile: 760-930-0698

EUROPE

Astec House, Waterfront Business Park
Merry Hill, Dudley
West Midlands, DY5 1LX, UK
Telephone: 44 (1384) 842-211
Facsimile: 44 (1384) 843-355

ASIA

Units 2111-2116, Level 21
Tower1, Metroplaza
223, Hing Fong Road
Fwai Fong, New Territories
Hong Kong
Telephone: 852-2437-9662
Facsimile: 852-2402-4426



Ordering Information

Input Voltage	Output 1 Voltage	Output 2 Voltage	Maximum Power	Model Number
9-18VDC	3.3V @ 1.0A		3.3W	AA05E-012L-033S
9-18VDC	5V @ 1.0A		5W	AA05E-012L-050S
9-18VDC	12V @ 0.41A		5W	AA05E-012L-120S
9-18VDC	15V @ 0.33A		5W	AA05E-012L-150S
9-18VDC	+12V @ 0.20A	-12V @ 0.20A	4.8W	AA05E-012L-120D
9-18VDC	+15V @ 0.16A	-15V @ 0.16A	4.8W	AA05E-012L-150D
18-36VDC	3.3V @ 1.0A		3.3W	AA05E-024L-033S
18-36VDC	5V @ 1.0A		5W	AA05E-024L-050S
18-36VDC	12V @ 0.41A		5W	AA05E-024L-120S
18-36VDC	15V @ 0.33A		5W	AA05E-024L-150S
18-36VDC	+12V @ 0.20A	-12V @ 0.20A	4.8W	AA05E-024L-120D
18-36VDC	+15V @ 0.16A	-15V @ 0.16A	4.8W	AA05E-024L-150D
36-72VDC	3.3V @ 1.0A		3.3W	AA05E-048L-033S
36-72VDC	5V @ 1.0A		5W	AA05E-048L-050S
36-72VDC	12V @ 0.41A		5W	AA05E-048L-120S
36-72VDC	15V @ 0.33A		5W	AA05E-048L-150S
36-72VDC	+12V @ 0.20A	-12V @ 0.20A	4.8W	AA05E-048L-120D
36-72VDC	+15V @ 0.16A	-15V @ 0.16A	4.8W	AA05E-048L-150D



Pin Assignments

Single Output

2 & 3: -Vin
22 & 23: +Vin
14: +Vout
16: Comm
Remaining Pins NC

Dual Output

2 & 3: -Vin
22 & 23: +Vin
14: Output 1
9 & 16: Comm
11: Output 2
Remaining Pins NC



Notes:

- 20 MHz bandwidth. An external 0.1uF ceramic capacitor is recommended to be placed from Vout to Comm.
- All specifications are typical at nominal line, full load, and 25° C unless otherwise noted.
- All specifications subject to change without notice.
- Mechanical drawings are for reference only.
- Warranty: 1 yr

Case Material: Metal (5 sides)
Weight: 0.5Oz/15Grams

AA05E

Astec Conventional