


Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 838495



- | | |
|----|--|
| 8 | OBsolete PART NUMBER. |
| 9 | 2.54 μm -7.62 μm [.000100-.000300] TIN-NICKEL OVER 3.81 μm -5.08 μm [.000150-.000200] NICKEL OVER 2.54 μm [.000100] MIN COPPER. |
| 10 | 5.08 μm -10.16 μm [.000200-.000400] TIN-LEAD OVER 1.27 μm -2.54 μm [.000050-.000100] COPPER. LUBRICATED AFTER PLATING. |
| 11 | 0.76 μm [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA, 3.00 μm [.000100] MIN TIN IN TERMINATION AREA, ALL OVER 1.27 μm [.000050] MIN NICKEL. |

OBSELETE	7.44 [.293]	21.06 [.829]	15.80 [.622]	11.43 [.450]	9			20	749621-1
	E	D	C	B	A	SHELL FINISH	CONTACT FINISH	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: 03/31/89 M.F. SHIRK		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
CHG: 04/03/89 JOHN A. ROOT		APD		NAME	
DIMENSIONS: INCHES 		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 P.L.C. ± 1 P.L.C. ± 2 P.L.C. ± 0.38 [015] 3 P.L.C. ± 4 P.L.C. ± ANGLES ± FINISH		PRODUCT SPEC 108-1228  APPLICATION SPEC 114-40029 WEIGHT —	
MATERIAL 		SHELL: SEE TABLE		KIT, PLUG ASSEMBLY, AMPLIMITE .050 Series SIZE CASE CODE DRAWING NO A1 00779 C 749621 RESTRICTED TO —	
		CUSTOMER DRAWING		SCALE 5:1 SHEET 1 of 1 REV U	