Dialight

556 Series **N**

High Intensity LED Panel Mount Indicators for 1" Mounting Hole for 37.5, 72 and 125 VDC

Watertight - NEMA4X IP66



FEATURES / BENEFITS

- Daylight viewable
- ▲ Safety standards UL and NEMA
- ▲ Tamperproof / Designed for high durability
- ▲ Long life, lasting up to 100k hours
- ▲ Uniform illumination multi-LED construction
- ▲ Lens options:
 - Low profile flat
 - Wide angle domed

APPLICATIONS

The 556 Series LED Panel Mount Indicators incorporate both InGaN and AllnGaP technologies to offer higher intensities. This is a highly durable package, designed to withstand outdoor applications susceptible to rain, dust and sunlight.


- Instrument panels
- Lane control
- Safety applications
- Display lighting
- Vending, gaming
- Transportation rail, bus, airline
- ... and many more!

SPECIFICATIONS

- Available in red, yellow and green
- ▲ Voltage range of 37.5, 72 and 125 VDC
- ▲ Watertight seal from front of panel meets NEMA 4X IP66 Maximum Mounting Torque 40 in./lb.
- ▲ Housing material: Nickel plated brass
- ▲ Lens material: Polycarbonate 94 VO

- ▲ UL recognized File #E156890
- ▲ Front mounting in 1" clearance hole
- ▲ Operating temperature: -30°C to +85°C
- ▲ Storage temperature: -40°C to +100°C

Dimensions in inches [mm]
All measurements are typical



Please see back of page for part numbers and additional specifications.

Dialight reserves the right to make changes at any time in order to supply the best product possible.

Dialight Corporation

1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com










556 Series **%**


High Intensity LED Panel Mount Indicators for 1" Mounting Hole for 37.5, 72 and 125 VDC

Watertight - NEMA4X IP66

FLAT LENS - 37.5, 72 & 125 VDC



DOME LENS - 37.5, 72 & 125 VDC



| PART NUMBER | COLOR | VOLTAGE (VDC) | TYPICAL CURRENT (mA) | TYPICAL LUMINANCE (fL) |
|----------------|--------|------------------|----------------------------|------------------------------|
| 556-1508-304F | Red | 37.5 | 20 | 2600 |
| 556-1608-304F | Green | 37.5 | 16 | 4000 |
| 556-1708-304F | Yellow | 37.5 | 20 | 2600 |
| 556-1506-304F | Red | 72 | 18.5 | 1800 |
| 556-1606-304F | Green | 72 | 16 | 1800 |
| 556-1706-304F | Yellow | 72 | 20 | 1000 |
| 556-1507-304F | Red | 125 | 10 | 700 |
| 556-1607-304F | Green | 125 | 10 | 1000 |
| 556-1707-304F | Yellow | 125 | 10 | 700 |

| PART NUMBER | COLOR | VOLTAGE (VDC) | TYPICAL CURRENT (mA) | TYPICAL LUMINANCE (fL) |
|----------------|--------|------------------|----------------------------|------------------------------|
| 556-3508-304F | Red | 37.5 | 20 | 1000 |
| 556-3608-304F | Green | 37.5 | 16 | 1800 |
| 556-3708-304F | Yellow | 37.5 | 20 | 1000 |
| 556-3506-304F | Red | 72 | 20 | 1000 |
| 556-3606-304F | Green | 72 | 16 | 1800 |
| 556-3706-304F | Yellow | 72 | 20 | 1000 |
| 556-3507-304F | Red | 125 | 10 | 700 |
| 556-3607-304F | Green | 125 | 10 | 1000 |
| 556-3707-304F | Yellow | 125 | 10 | 700 |

Other voltages and colors are available. Please contact our factory for more information.

Dialight reserves the right to make changes at any time in order to supply the best product possible.



1501 Route 34 South • Farmingdale, NJ 07727 USA Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com





