


REVISIONS			
LTR	DESCRIPTION	DATE (YR-MO-DA)	APPROVED
A	Change vendor part number from 54F148/B2C to 54F148/B2A. Table I I _{IL} column delete I _E and substitute I _E . Table I t _{PHL6} maximum limits column delete 11 and substitute 13. Add figure 4 to document. Editorial changes throughout. -ljs	88-12-13	M. A. Frye
B	Revise for "QD" certification. New boilerplate. -ljs	99-11-08	Raymond Monnin
C	Update to current requirements. Editorial changes throughout. - gap	06-01-04	Raymond Monnin

The original first page of this drawing has been replaced.

1. SCOPE

1.1 Scope. This drawing describes device requirements for MIL-STD-883 compliant, non-JAN class level B microcircuits in accordance with MIL-PRF-38535, appendix A.

1.2 Part or Identifying Number (PIN). The complete PIN is as shown in the following example:



1.2.1 Device type(s). The device type(s) identify the circuit function as follows:

<u>Device type</u>	<u>Generic number</u>	<u>Circuit function</u>
01	54F148	8-line to 3-line priority encoder

1.2.2 Case outline(s). The case outline(s) are as designated in MIL-STD-1835 and as follows:

<u>Outline letter</u>	<u>Descriptive designator</u>	<u>Terminals</u>	<u>Package style</u>
E	GDIP1T-16 or CDIP2-T16	16	dual-in-line
F	GDFP2-F16 or GDFP3-F16	16	flat package
2	CQCC1-N20	20	square chip carrier

1.2.3 Lead finish. The lead finish is as specified in MIL-PRF-38535, appendix A.

1.3 Absolute maximum ratings.

Supply voltage range	-0.5 V dc minimum to +7.0 V dc maximum
Input voltage range	-1.5 V at -18 mA to +7.0 V dc
Storage temperature range	-65°C to +150°C
Maximum power dissipation (P_D) ^{1/}	193 mW
Lead temperature (soldering, 10 seconds)	+300°C
Thermal resistance, junction-to-case (θ_{JC})	See MIL-STD-1835
Junction temperature (T_J)	+175°C

1.4 Recommended operating conditions.

Supply voltage range (V_{CC})	4.5 V minimum to 5.5 V maximum
Minimum high level input voltage (V_{IH})	2.0 V dc
Maximum low level input voltage (V_{IL})	0.8 V dc
Case operating temperature (T_C)	-55°C to +125°C

^{1/} Maximum power dissipation is defined as $V_{CC} \times I_{CC}$, and must withstand the added P_D due to short circuit test, e.g. I_{OS}

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE	5962-86070
	REVISION LEVEL	

2. APPLICABLE DOCUMENTS

2.1 Government specification, standards, and handbooks. The following specification, standards, and handbooks form a part of this drawing to the extent specified herein. Unless otherwise specified, the issues of these documents are those cited in the solicitation or contract.

DEPARTMENT OF DEFENSE SPECIFICATION

MIL-PRF-38535 - Integrated Circuits, Manufacturing, General Specification for.

DEPARTMENT OF DEFENSE STANDARDS

MIL-STD-883 - Test Method Standard Microcircuits.

MIL-STD-1835 - Interface Standard Electronic Component Case Outlines.

DEPARTMENT OF DEFENSE HANDBOOKS

MIL-HDBK-103 - List of Standard Microcircuit Drawings.

MIL-HDBK-780 - Standard Microcircuit Drawings.

(Copies of these documents are available online at <http://assist.daps.dla.mil/quicksearch/> or www.dodssp.daps.mil or from the Standardization Document Order Desk, 700 Robbins Avenue, Building 4D, Philadelphia, PA 19111-5094.)

2.2 Order of precedence. In the event of a conflict between the text of this drawing and the references cited herein, the text of this drawing takes precedence. Nothing in this document, however, supersedes applicable laws and regulations unless a specific exemption has been obtained.

3. REQUIREMENTS

3.1 Item requirements. The individual item requirements shall be in accordance with MIL-PRF-38535, appendix A for non-JAN class level B devices and as specified herein. Product built to this drawing that is produced by a Qualified Manufacturer Listing (QML) certified and qualified manufacturer or a manufacturer who has been granted transitional certification to MIL-PRF-38535 may be processed as QML product in accordance with the manufacturers approved program plan and qualifying activity approval in accordance with MIL-PRF-38535. This QML flow as documented in the Quality Management (QM) plan may make modifications to the requirements herein. These modifications shall not affect form, fit, or function of the device. These modifications shall not affect the PIN as described herein. A "Q" or "QML" certification mark in accordance with MIL-PRF-38535 is required to identify when the QML flow option is used. This drawing has been modified to allow the manufacturer to use the alternate die/fabrication requirements of paragraph A.3.2.2 of MIL-PRF-38535 or other alternative approved by the qualifying activity.

3.2 Design, construction, and physical dimensions. The design, construction, and physical dimensions shall be as specified in MIL-PRF-38535, appendix A and herein.

3.2.1 Case outline(s). The case outline(s) shall be in accordance with 1.2.2 herein.

3.2.2 Terminal connections. The terminal connections shall be as specified on figure 1.

3.2.3 Truth table. The truth table shall be as specified on figure 2.

3.2.4 Logic diagram. The logic diagram shall be as specified on figure 3.

3.2.5 Test circuit and switching waveforms. The test circuit and switching waveforms shall be as specified on figure 4.

3.3 Electrical performance characteristics. Unless otherwise specified herein, the electrical performance characteristics are as specified in table I and shall apply over the full case operating temperature range.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE	5962-86070
	REVISION LEVEL C	

3.4 Electrical test requirements. The electrical test requirements shall be the subgroups specified in table II. The electrical tests for each subgroup are described in table I.

3.5 Marking. Marking shall be in accordance with MIL-PRF-38535, appendix A. The part shall be marked with the PIN listed in 1.2 herein. In addition, the manufacturer's PIN may also be marked. For packages where marking of the entire SMD PIN number is not feasible due to space limitations, the manufacturer has the option of not marking the "5962-" on the device.

3.5.1 Certification/compliance mark. A compliance indicator "C" shall be marked on all non-JAN devices built in compliance to MIL-PRF-38535, appendix A. The compliance indicator "C" shall be replaced with a "Q" or "QML" certification mark in accordance with MIL-PRF-38535 to identify when the QML flow option is used. For product built in accordance with A.3.2.2 of MIL-PRF-38535, or as modified in the manufacturer's QM plan, the "QD" certification mark shall be used in place of the "Q" or "QML" certification mark.

3.6 Certificate of compliance. A certificate of compliance shall be required from a manufacturer in order to be listed as an approved source of supply in MIL-HDBK-103 (see 6.6 herein). The certificate of compliance submitted to DSCC-VA prior to listing as an approved source of supply shall affirm that the manufacturer's product meets the requirements of MIL-PRF-38535, appendix A and the requirements herein.

3.7 Certificate of conformance. A certificate of conformance as required in MIL-PRF-38535, appendix A shall be provided with each lot of microcircuits delivered to this drawing.

3.8 Notification of change. Notification of change to DSCC-VA shall be required for any change that affects this drawing.

3.9 Verification and review. DSCC, DSCC's agent, and the acquiring activity retain the option to review the manufacturer's facility and applicable required documentation. Offshore documentation shall be made available onshore at the option of the reviewer.

4. VERIFICATION

4.1 Sampling and inspection. Sampling and inspection procedures shall be in accordance with MIL-PRF-38535, appendix A.

4.2 Screening. Screening shall be in accordance with method 5004 of MIL-STD-883, and shall be conducted on all devices prior to quality conformance inspection. The following additional criteria shall apply:

a. Burn-in test, method 1015 of MIL-STD-883.

(1) Test condition A, B, C or D. The test circuit shall be maintained by the manufacturer under document revision level control and shall be made available to the preparing or acquiring activity upon request. The test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in method 1015 of MIL-STD-883.

(2) $T_A = +125^\circ\text{C}$, minimum.

b. Interim and final electrical test parameters shall be as specified in table II herein, except interim electrical parameter tests prior to burn-in are optional at the discretion of the manufacturer.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A	5962-86070
		REVISION LEVEL C

TABLE I. Electrical performance characteristics.

Test	Symbol	Conditions $-55^{\circ}\text{C} \leq T_{\text{C}} \leq +125^{\circ}\text{C}$ unless otherwise specified	Group A subgroups	Limits		Unit	
				Min	Max		
High level output voltage	V_{OH}	$V_{\text{CC}} = 4.5 \text{ V}$, $I_{\text{OH}} = -1 \text{ mA}$, $V_{\text{IL}} = 0.8 \text{ V}$ $V_{\text{IH}} = 2.0 \text{ V}$	1, 2, 3	2.5		V	
Low level output voltage	V_{OL}	$V_{\text{CC}} = 4.5 \text{ V}$, $I_{\text{OL}} = 20 \text{ mA}$, $V_{\text{IL}} = 0.8 \text{ V}$ $V_{\text{IH}} = 2.0 \text{ V}$	1, 2, 3		0.5	V	
Input clamp voltage	V_{IC}	$V_{\text{CC}} = 4.5 \text{ V}$, $I_{\text{IN}} = -18 \text{ mA}$	1, 2, 3		-1.2	V	
High level input current	I_{IH1}	$V_{\text{CC}} = 5.5 \text{ V}$, $V_{\text{IN}} = 7.0 \text{ V}$	1, 2, 3		100	μA	
	I_{IH2}	$V_{\text{CC}} = 5.5 \text{ V}$, $V_{\text{IN}} = 2.7 \text{ V}$	1, 2, 3		20	μA	
Low level input current	I_{IL}	$V_{\text{CC}} = 5.5 \text{ V}$	$\bar{I}_{\text{o}}, \bar{E}\bar{I}$	1, 2, 3	-0.6	mA	
		$V_{\text{IN}} = 0.5 \text{ V}$	$\bar{I}_{\text{h}}, \bar{I}_{\text{r}}$	1, 2, 3	-1.2	mA	
Short circuit output current	I_{os}	$V_{\text{CC}} = 4.5 \text{ V}$, $V_{\text{OUT}} = 0.0 \text{ V}$	1/	1, 2, 3	-60	-150	mA
Supply current	I_{CC}	$V_{\text{CC}} = 5.5 \text{ V}$		1, 2, 3		35	mA
Functional tests		See 4.3.1c		7, 8			
Propagation delay time, \bar{I}_{n} to \bar{A}_{n}	t_{PLH1}	$V_{\text{CC}} = 5.0 \text{ V}$ $R_{\text{L}} = 500\Omega$ $C_{\text{L}} = 50 \text{ pF}$	9		9	ns	
			10, 11		12		
	t_{PHL1}		9		11		
			10, 11		15		
Propagation delay time, \bar{I}_{n} to $\bar{E}\bar{O}$	t_{PLH2}		9		7	ns	
			10, 11		9		
	t_{PHL2}		9		8		
			10, 11		11		
Propagation delay time, \bar{I}_{n} to $\bar{G}\bar{S}$	t_{PLH3}		9		11	ns	
			10, 11		15		
	t_{PHL3}		9		11		
			10, 11		15		
Propagation delay time, $\bar{E}\bar{I}$ to \bar{A}_{n}	t_{PLH4}		9		9	ns	
			10, 11		12		
	t_{PHL4}		9		8		
			10, 11		11		
Propagation delay time, $\bar{E}\bar{I}$ to $\bar{G}\bar{S}$	t_{PLH5}		9		7	ns	
			10, 11		9		
	t_{PHL5}		9		11		
			10, 11		15		
Propagation delay time, $\bar{E}\bar{I}$ to $\bar{E}\bar{O}$	t_{PLH6}		9		7	ns	
			10, 11		9		
	t_{PHL6}		9		11		
			10, 11		13		

1/ Not more than one output should be shorted at a time, and the duration of the short circuit condition should not exceed 1 second.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE	5962-86070
	A	
	REVISION LEVEL C	SHEET 5

Case outlines	E and F	2
Terminal number	Terminal symbol	
1	\bar{l}_4	NC
2	\bar{l}_5	\bar{l}_4
3	\bar{l}_6	\bar{l}_5
4	\bar{l}_7	\bar{l}_6
5	$\bar{E}l$	\bar{l}_7
6	\bar{A}_2	NC
7	\bar{A}_1	$\bar{\bar{E}}l$
8	GND	\bar{A}_2
9	\bar{A}_0	\bar{A}_1
10	\bar{l}_0	GND
11	\bar{l}_1	NC
12	\bar{l}_2	\bar{A}_0
13	\bar{l}_3	\bar{l}_0
14	$\bar{\bar{G}}S$	\bar{l}_1
15	$\bar{\bar{E}}O$	\bar{l}_2
16	V_{CC}	NC
17	---	\bar{l}_3
18	---	$\bar{\bar{G}}S$
19	---	$\bar{\bar{E}}O$
20	---	V_{CC}

NC = No connection

FIGURE 1. Terminal connections.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE		5962-86070
	A		
		REVISION LEVEL C	SHEET 6

Inputs								Outputs					
\overline{EO}	$\overline{I_0}$	$\overline{I_1}$	$\overline{I_2}$	$\overline{I_3}$	$\overline{I_4}$	$\overline{I_5}$	$\overline{I_6}$	$\overline{I_7}$	\overline{GS}	$\overline{A_0}$	$\overline{A_1}$	$\overline{A_2}$	\overline{EO}
H	X	X	X	X	X	X	X	X	H	H	H	H	H
L	H	H	H	H	H	H	H	H	H	H	H	H	L
L	X	X	X	X	X	X	X	L	L	L	L	L	H
L	X	X	X	X	X	X	L	H	L	H	L	L	H
L	X	X	X	X	X	L	H	H	L	L	H	L	H
L	X	X	X	X	L	H	H	H	L	H	H	L	H
L	X	X	X	L	H	H	H	H	L	L	L	H	H
L	X	X	L	H	H	H	H	H	L	H	L	H	H
L	X	L	H	H	H	H	H	H	L	L	H	H	H
L	L	H	H	H	H	H	H	H	L	H	H	H	H

H -- High voltage level

L = Low voltage level

X = Irrelevant

FIGURE 2. Truth table.







FIGURE 3. Logic diagram.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		5962-86070
		REVISION LEVEL C	SHEET 7



NOTES:

1. C_L includes probe and jig capacitance
2. Input pulse requirements: PRR = 1 MHz, $t_{TLH} = t_{THL} = 2.5$ ns, duty cycle = 50%.
3. R_T = termination resistance is \cong to Z_{OUT} of pulse generator.

FIGURE 4. Test circuit and switching waveforms.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A	5962-86070
	REVISION LEVEL C	

TABLE II. Electrical test requirements.

MIL-STD-883 test requirements	Subgroups (in accordance with MIL-STD-883, method 5005, table I)
Interim electrical parameters (method 5004)	---
Final electrical test parameters (method 5004)	1*, 2, 3, 7, 8, 9
Group A test requirements (method 5005)	1, 2, 3, 7, 8, 9, 10, 11
Groups C and D end-point electrical parameters (method 5005)	1, 2, 3

* PDA applies to subgroup 1.

4.3 Quality conformance inspection. Quality conformance inspection shall be in accordance with method 5005 of MIL-STD-883 including groups A, B, C, and D inspections. The following additional criteria shall apply.

4.3.1 Group A inspection.

- a. Tests shall be as specified in table II herein.
- b. Subgroups 4, 5 and 6 in table I, method 5005 of MIL-STD-883 shall be omitted.
- c. Subgroups 7 and 8 shall include verification of the truth table.

4.3.2 Groups C and D inspections.

- a. End-point electrical parameters shall be as specified in table II herein.
- b. Steady-state life test conditions, method 1005 of MIL-STD-883.
 - (1) Test condition A, B, C or D. The test circuit shall be maintained by the manufacturer under document revision level control and shall be made available to the preparing or acquiring activity upon request. The test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in method 1005 of MIL-STD-883.
 - (2) $T_A = +125^\circ\text{C}$, minimum.
 - (3) Test duration: 1,000 hours, except as permitted by method 1005 of MIL-STD-883.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE		5962-86070
		REVISION LEVEL C	SHEET 9

5. PACKAGING

5.1 Packaging requirements. The requirements for packaging shall be in accordance with MIL-PRF-38535, appendix A.

6. NOTES

6.1 Intended use. Microcircuits conforming to this drawing are intended for use for Government microcircuit applications (original equipment), design applications, and logistics purposes.

6.2 Replaceability. Microcircuits covered by this drawing will replace the same generic device covered by a contractor-prepared specification or drawing.

6.3 Configuration control of SMD's. All proposed changes to existing SMD's will be coordinated with the users of record for the individual documents. This coordination will be accomplished using DD Form 1692, Engineering Change Proposal.

6.4 Record of users. Military and industrial users shall inform Defense Supply Center Columbus (DSCC) when a system application requires configuration control and the applicable SMD. DSCC will maintain a record of users and this list will be used for coordination and distribution of changes to the drawings. Users of drawings covering microelectronics devices (FSC 5962) should contact DSCC-VA, telephone (614) 692-0544.

6.5 Comments. Comments on this drawing should be directed to DSCC-VA, Columbus, Ohio 43218-3990, or telephone (614) 692-0547.

6.6 Approved sources of supply. Approved sources of supply are listed in MIL-HDBK-103. The vendors listed in MIL-HDBK-103 have agreed to this drawing and a certificate of compliance (see 3.6 herein) has been submitted to and accepted by DSCC-VA.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE	5962-86070
	A	
	REVISION LEVEL C	SHEET 10

STANDARD MICROCIRCUIT DRAWING BULLETIN

DATE: 06-01-04

Approved sources of supply for SMD 5962-86070 are listed below for immediate acquisition information only and shall be added to MIL-HDBK-103 and QML 38535 during the next revision. MIL-HDBK-103 and QML 38535 will be revised to include the addition or deletion of sources. The vendors listed below have agreed to this drawing and a certificate of compliance has been submitted to and accepted by DSCC-VA. This bulletin is superseded by the next dated revision of MIL-HDBK-103 and QML 38535.

Standard microcircuit drawing PIN <u>1</u> /	Vendor CAGE number	Vendor similar PIN <u>2</u> /
5962-8607001EA	0C7V7	54F148/BEA
5962-8607001FA	<u>3</u> /	54F148/BFA
5962-86070012A	<u>3</u> /	54F148/B2A

- 1/ The lead finish shown for each PIN representing a hermetic package is the most readily available from the manufacturer listed for that part. If the desired lead finish is not listed contact the vendor to determine its availability.
- 2/ Caution. Do not use this number for item acquisition. Items acquired to this number may not satisfy the performance requirements of this drawing.
- 3/ Not available from an approved source.

Vendor CAGE
number

0C7V7

Vendor name
and address

QP Semiconductor
2945 Oakmead Village Court
Santa Clara, CA 95051

The information contained herein is disseminated for convenience only and the Government assumes no liability whatsoever for any inaccuracies in the information bulletin.