



Fittings for metallic conduits

- **SC-SM Swivel External Thread**

Swivel external thread, nickel plated brass.

Features and Benefits

- Two-part fitting of shell and body with external thread
- External thread swives about main body
- Provides tight, reliable hold of conduit
- Can be secured with locknut



HelaGuard SC-SM Swivel External Thread.

MATERIAL	Nickel Plated Brass (NPB)
Operating Temperature	-100 °C to +300 °C



TYPE	Nominal Ø	Thread Size (metric)	Thread Size (PG)	Min. Bore Size	Length (L)	A/F Body	A/F Thread	Thread Length	Pack Cont.	Colour	Article-No.
SC10-SM-PG7	10	-	PG7	5.6	30.2	13	13	8.0	10 pcs.	Metal (ML)	166-30410
SC10-SM-M12	10	M12	-	5.6	30.2	13	13	8.0	10 pcs.	Metal (ML)	166-30400
SC12-SM-PG9	12	-	PG9	8.5	32.2	17	17	8.0	10 pcs.	Metal (ML)	166-30411
SC12-SM-M16	12	M16	-	8.5	32.2	17	17	8.0	10 pcs.	Metal (ML)	166-30401
SC16-SM-PG11	16	-	PG11	11.5	34.2	20	22	10.0	10 pcs.	Metal (ML)	166-30412
SC16-SM-M16	16	M16	-	11.5	34.2	20	20	10.0	10 pcs.	Metal (ML)	166-30402
SC16-SM-M20	16	M20	-	11.5	34.2	20	22	10.0	10 pcs.	Metal (ML)	166-30403
SC20-SM-PG13	20	-	PG13.5	15.3	35.5	24	24	10.0	10 pcs.	Metal (ML)	166-30413
SC20-SM-PG16	20	-	PG16	15.3	35.5	24	24	10.0	10 pcs.	Metal (ML)	166-30414
SC20-SM-M20	20	M20	-	15.3	35.5	24	24	10.0	10 pcs.	Metal (ML)	166-30404
SC25-SM-PG21	25	-	PG21	19.1	43.7	29	29	12.0	10 pcs.	Metal (ML)	166-30415
SC25-SM-M25	25	M25	-	19.1	43.7	29	29	12.0	10 pcs.	Metal (ML)	166-30405
SC32-SM-PG29	32	-	PG29	26.2	48.0	38	38	13.0	2 pcs.	Metal (ML)	166-30416
SC32-SM-M32	32	M32	-	26.2	48.0	38	38	13.0	2 pcs.	Metal (ML)	166-30406
SC40-SM-PG36	40	-	PG36	34.2	51.2	48	48	14.0	2 pcs.	Metal (ML)	166-30417
SC40-SM-M40	40	M40	-	34.2	51.2	48	48	14.0	2 pcs.	Metal (ML)	166-30407
SC50-SM-PG42	50	-	PG42	44.8	54.2	58	58	15.0	1 EA	Metal (ML)	166-30418
SC50-SM-M50	50	M50	-	44.8	54.2	58	58	15.0	1 EA	Metal (ML)	166-30408
SC63-SM-M63	63	M63	-	54.5	63.2	70	70	18.0	1 EA	Metal (ML)	166-30409

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content.