



Main

|                           |                   |
|---------------------------|-------------------|
| Range of product          | TeSys U           |
| Device short name         | LUA1              |
| Product or component type | Auxiliary contact |

Complementary

|   |  |
|---|--|
| Auxiliary contact composition               | 1 NO + 1 NC  |
| Signalling function                         | Fault signalling<br>Indicating rotary knob in ready position                           |
| [Ue] rated operational voltage              | <= 250 V AC<br><= 250 V DC   |
| [Ui] rated insulation voltage               | 250 V conforming to CSA<br>250 V conforming to IEC 60947-5-1<br>250 V conforming to UL |
| [Ith] conventional free air thermal current | 5 A  |
| Minimum switching voltage                   | 17 V   |
| Minimum switching current                   | 5 mA   |
| Product weight                              | 0.03 kg  |
| Connections - terminals                     | Screw clamp terminals  |