

SMD Choke Coils

Singapore

Series: **M**

Type: **ELL4□M**



Type ELL4□M

■ Features

- Magnetic shielded structure
- Low DC resistance and capable of corresponding
- Structure for withstanding fall shock
- Available on tape and reel for automatic insertion


■ Recommended Applications

- DC/DC converter circuit for Computer peripheral, Hand phone.
- Choke coils for Chopper circuit decoupling choked in DC/DC converter circuit


■ Standard Packing Quantity

- 4GM : 2000 pcs./Reel, 4LM : 3000 pcs./Reel


■ Explanation of Part Numbers



■ Dimensions in mm (not to scale)



■ Recommended land patterns in mm (not to scale)



Examples

Part Number	Inductance (100kHz)		DCR (at 20 °C)		* Rated Current (mA max.)	Marking
	(μH)	Tol.	(mΩ)	Tol.		
ELL4GM2R4N	2.4	±30 %	66	±20 %	1150	12
ELL4GM3R6N	3.6		100		950	17
ELL4GM4R7N	4.7		120		800	21
ELL4GM5R6N	5.6		130		750	23
ELL4GM6R8N	6.8		180		640	26
ELL4GM8R2N	8.2	±20%	220	±20 %	580	29
ELL4GM100M	10.0		260		540	31
ELL4GM180M	18.0		490		400	35
ELL4GM220M	22.0		560		350	36
ELL4GM270M	27.0		640		330	37
ELL4GM330M	33.0	±30%	700	±20%	300	39
ELL4LM1R0N	1.0		26		2000	01
ELL4LM1R5N	1.5		31		1600	06
ELL4LM2R0N	2.0		43		1350	10
ELL4LM2R7N	2.7		56		1250	13
ELL4LM3R3N	3.3		62		1100	16
ELL4LM4R7N	4.7		90		900	21
ELL4LM6R2N	6.2		140		800	25
ELL4LM7R5N	7.5		150		720	27
ELL4LM100M	10.0		180		690	31
ELL4LM120M	12.0	±20%	200	±20%	530	32
ELL4LM150M	15.0		300		500	33
ELL4LM180M	18.0		320		460	35
ELL4LM220M	22.0		380		430	36
ELL4LM270M	27.0		420		370	37

* Current: This indicates the value of current when the inductance is 70% more than nominal value and temperature rising $\Delta t=45^{\circ}\text{C}$ lower at D.C superposition.(at 20°C)

Embossed Carrier Tape Dimensions in mm (not to scale)

● 4GM, 4LM

