





MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING


Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



MOUNTING HARDWARE



LOCK WASHER



HEX NUT

NOTES:

1. TUSONIX STANDARD PART NUMBER: 4208-000.
TUSONIX RoHS COMPLIANT PART NUMBER: 4208-000 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER
WHEN ORDERING.
2. SUPPLIED WITH SILVER PLATED LOCK WASHER AND NUT.
3. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.

MIN. Cx.	WORKING VOLTAGE		DWV (VDC)	CURRENT IDC	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220			
	85° C	125° C			10MHz	100MHz	1GHz	10 GHz
1500 pF	2500	2000	5 KV	25A	5	50	50	50

X-2015 Rev-0	REVISION RECORD						--TOLERANCES-- Unless Otherwise Specified		Title HI-VOLTAGE EMI FILTER	
	0	Original Release C.O.	1	1	2	3				
	5183	WAS SK 6959-000. KLJ 5-1-90	5183	2	3	4	DECIMAL ± .031 [0.79]		Drawn S.M. 05-28-02	
	5183	REISSUE -375 DIM. WAS .347. KLJ. 5-4-90	5183	3	4	5	ANGLES ±		Scale 2 X	
	5183	ADDED COLUMN (IDC) & HARDWARE. E.C. 07-03-90	5183	4	5	6	TUSONIX TUCSON, ARIZONA		Approved J.Mc. 05-28-02	
		20020523-4-10			20050718-5-02			A		4208-000