


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	—		C	CONTACT PIN MATERIAL & PLATING CHANGE	26JUN2014	PS	JK

POS.	L±0.5	PART NO.
—	—	—
2	5.08	966245-2
3	7.62	—
4	10.16	—
5	12.70	—
6	15.24	—
7	17.78	—
8	20.32	—
9	22.86	—
10	25.40	1—
11	27.94	1—
12	30.48	1—
13	33.02	1—
14	35.56	1—
15	38.10	1—
16	40.64	1—
17	43.18	1—
18	45.72	1—
19	48.26	1—
20	50.80	2—
21	53.34	2—
22	55.88	2—
23	58.42	2—
24	60.96	2—
25	63.50	2—
26	66.04	2—
27	68.58	2—
28	71.12	2—
29	73.66	2—
30	76.20	3—
31	78.74	3—
32	81.28	3—
33	83.82	3—
34	86.36	3—
35	88.90	3—
36	91.44	3—
37	93.98	3—
38	96.52	3—
39	99.06	3—
40	101.60	4—
41	104.14	4—
42	106.68	4—
43	109.22	4—
44	111.76	4—
45	114.30	4—
46	116.84	4—
47	119.38	4—
48	121.92	4—
49	124.46	4—
50	127.00	5— 966245-0

CONTACT PIN	CuZn	1
HOUSING	PBT	GREEN
DESCRIPTION	MATERIAL	FINISH / COLOR



- 1 MATING SIDE: MIN 0.7μm PdNi+ MIN 0.1μm GOLD FLASH IN ZONE "F" OVER 1.27μm NICKEL
SOLDER SIDE: 3.0 TO 5.0μm TIN OVER 1.27μm NICKEL.
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 3 OBSOLETE

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

By -
COPYRIGHT -

DIMENSIONS:		DWN	25.03.93	MATERIAL	SEE TABLE	FINISH	SEE TABLE
mm		CHK	A.HO	 TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	M.SCHAARSCHMIDT				
±0.2 mm		PRODUCT SPEC	108-18012	NAME			
0 PLC ± -		APPLICATION SPEC	—	SPEC. AMPMODU II PIN HEADER, SINGLE ROW			
1 PLC ± -		WEIGHT	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
2 PLC ± -		A4 00779 C-966245			—		
3 PLC ± -		CUSTOMER DRAWING			SCALE	SHEET	REV
4 PLC ± -					4:1	1 OF 1	C
ANGLES ± -							

