

DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC
G

DIST
14

P
F

ZONE

LTR

E

REVISIONS

DESCRIPTION

DATE

APPD

EC 0720-0279-93

6-21-93

SP BB


AMP
WIRE RANGE

2 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]

1. TONGUE MATERIAL THK 1.45 ± 0.08 [$.057 \pm .003$]
FOR 11.89 [$.468$] MAX WIRE INS DIA



**AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS**

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

MAX RECOMMENDED OPERATING
TEMPERATURE:

105°C

VOLTAGE RATING:

-

CIRCULAR MIL AREA:

26.7-42.4mm² [52,600-83,700]
STRANDED

MS25036-127
CLASS 2

MILITARY P/N & CLASS

QTY

LOOSE PC

324054

PACKAGE TYPE

PART NO

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm - ENGLISH
TOLERANCES ON:
2 PLC DEC ± 0.20 (.008)
3 PLC DEC ± -
ANGLES ± -

MATERIAL
COPPER PER ASTM B-152
NYLON (MIL-H-20693) TYPE I
COLOR: RED

FINISH
TIN PLATE PER MIL-T-10727

OR 6-21-93
S.S. GULDEN
CHK 6-21-93
R. HERSEY
APPD 6-21-93
B. BARE
APPD 6-21-93
H. ELLIS
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

AMP AMP Incorporated
Harrisburg, PA 17105-3608

NAME
TERMINAL, RING TONGUE, TERMINYL
WIRE SIZE: 2 AWG

SIZE
B 00779 C-324054

SCALE
NTS

SHEET
1 OF 1

AMP 1470-15 REV 3-92

21 JUN 1993

09:06:35

AMPT1122

<UUI28A>DEPT1132>AMPT1122>U.CUSTOMER NYL

CUSTOMER DRAWING