

## Aluminum Electrolytic Capacitors Axial Miniature High Voltage for E.L.B.





Fig. 1

QUICK REFERENCE DATA	
DESCRIPTION	VALUE
Nominal case sizes ( $\varnothing$ D x L in mm)	12.5 x 30 to 18 x 38
Rated capacitance range, $C_R$	6.8 $\mu$ F to 33 $\mu$ F
Tolerance on $C_R$	-10 % to +50 %
Rated voltage, $U_R$	450 V
Category temperature range	-25 °C to +85 °C
Endurance test at 85 °C	8000 h
Useful life at 85 °C	20 000 h
Useful life at 70 °C, $I_R$ applied	100 000 h
Shelf life at 0 V, 85 °C	500 h
Based on sectional specification	IEC 60384-4 / EN 130300
Climatic category IEC 60068	25 / 085 / 56

### FEATURES

- Useful life: 20 000 h at +85 °C
- Stable under overvoltage conditions: 550 V for 24 h at 85 °C
- High ripple current capability
- Smallest dimensions
- Taped versions up to case  $\varnothing$  15 mm x 30 mm available for automatic insertion
- Polarized aluminum electrolytic capacitors, non-solid electrolyte
- Axial leads, cylindrical aluminum case, insulated with a blue sleeve
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



RoHS  
COMPLIANT

### APPLICATIONS


- Electronic lighting ballast, power supply
- Smoothing, filtering, buffering at high voltages
- Boards with restricted mounting height, vibration, and shock resistant

### MARKING

The capacitors are marked (where possible) with the following information:

- Rated capacitance (in  $\mu$ F)
- Tolerance on rated capacitance, code letter in accordance with IEC 60062 (T for -10 % to +50 %)
- Rated voltage (in V)
- Upper category temperature (85 °C)
- Date code in accordance with IEC 60062
- Code for factory of origin
- Name of manufacturer
- Negative terminal identification
- Series number (042 or 043)


### DIMENSIONS in millimeters AND AVAILABLE FORMS



Form BR: Taped on reel

Case Ø D x L = 6.5 mm x 18 mm to 15 mm x 30 mm

Fig. 2 - Form BR



Form AA: Axial in box

Case Ø D x L = 10 mm x 30 mm to 21 mm x 38 mm

Fig. 3 - Form AA

**Table 1**

<b>AXIAL; DIMENSIONS</b> in millimeters, <b>MASS AND PACKAGING QUANTITIES</b>								
<b>NOMINAL CASE SIZE</b> $\varnothing$ D x L (mm)	<b>CASE CODE</b>	<b>AXIAL: FORM AA AND BR</b>				<b>MASS</b> (g)	<b>PACKAGING QUANTITIES</b>	
		$\varnothing$ d	I	$\varnothing$ D <sub>max.</sub>	L <sub>max.</sub>		<b>FORM AA</b>	<b>FORM BR</b>
12.5 x 30	01	0.8	55 ± 1	13.0	30.5	35	≈ 6.1	260
15 x 30	02	0.8	55 ± 1	15.5	30.5	35	≈ 8.3	200
18 x 30	03	0.8	55 ± 1	18.5	30.5	35	≈ 11.6	120
18 x 38	04	0.8	34 ± 1	18.5	39.5	44	≈ 16.0	125

**Note**

- For detailed tape dimensions please refer to packaging information: [www.vishay.com/doc?28361](http://www.vishay.com/doc?28361)

<b>ELECTRICAL DATA</b>	
<b>SYMBOL</b>	<b>DESCRIPTION</b>
C <sub>R</sub>	Rated capacitance at 100 Hz, tolerance -10 % to +50 %
I <sub>R</sub>	Rated RMS ripple current at 10 kHz, 85 °C
I <sub>L5</sub>	Max. leakage current after 5 min at U <sub>R</sub>
ESR	Typ. / max. equivalent series resistance at 100 Hz
Z	Typ. / max. impedance at 10 kHz

**ORDERING EXAMPLE**

Electrolytic capacitor 042 series

10 µF / 450 V; -10 % / +50 %

Nominal case size: Ø 12.5 mm x 30 mm; Form BR

Ordering code: MAL204282109E3

Former 12NC: 2222 042 82109

**Note**

- Unless otherwise specified, all electrical values in Table 2 apply at T<sub>amb</sub> = 20 °C, P = 86 kPa to 106 kPa, RH = 45 % to 75 %.


**Table 2**

<b>ELECTRICAL DATA AND ORDERING INFORMATION</b>										
U <sub>R</sub> (V)	C <sub>R</sub> 100 Hz (µF)	NOMINAL CASE SIZE	I <sub>R</sub> 10 kHz 85 °C (mA)	I <sub>L5</sub> 5 min (µA)	ESR TYP. 100 Hz (Ω)	ESR MAX. 100 Hz (Ω)	Z TYP. 10 kHz (Ω)	Z MAX. 10 kHz (Ω)	ORDERING CODE MAL2.....	
									AXIAL	
450	6.8	12.5 x 30	540	106	3.8	8.3	2.8	4.8	04281688E3	04282688E3
	10	12.5 x 30	710	110	2.6	5.6	1.8	3.1	04281109E3	04282109E3
	15	15 x 30	910	115	1.7	3.7	1.2	2.1	04281159E3	04282159E3
	22	18 x 30	1190	120	1.1	2.4	0.9	1.4	04281229E3	-
	33	18 x 38	1610	130	0.8	1.7	0.6	1.0	04381339E3	-

<b>ADDITIONAL ELECTRICAL DATA</b>			
PARAMETER	CONDITIONS		VALUE
<b>Voltage</b>		U <sub>R</sub> = 450 V	U <sub>S</sub> ≤ 550 V
Surge voltage		24 h at 85 °C	550 V <sup>(1)</sup>
Overvoltage test			U <sub>rev</sub> ≤ 1 V
Reverse voltage			
<b>Current</b>			
Leakage current		After 1 min	I <sub>L1</sub> ≤ 0.009 x C <sub>R</sub> x U <sub>R</sub> + 200 µA
		After 5 min	I <sub>L5</sub> ≤ 0.002 x C <sub>R</sub> x U <sub>R</sub> + 100 µA
<b>Inductance</b>		Case Ø D x L in mm:	
Equivalent series inductance		12.5 x 30	Typ. 46 nH
		15 x 30	Typ. 48 nH
		18 x 30	Typ. 50 nH
		18 x 38	Typ. 54 nH


**Note**

- (1) Test conditions on request.

**CAPACITANCE (C)**



$C_0$  = Capacitance at 20 °C, 100 Hz       $T_{amb} = 20$  °C

Fig. 4 - Typical multiplier of capacitance as a function of ambient temperature

**EQUIVALENT SERIES RESISTANCE (ESR)**



$ESR_0$  = Typical at 20 °C, 100 Hz

Fig. 5 - Typical multiplier of ESR as a function of frequency at different ambient temperatures



$ESR_0$  = Typical at 20 °C, 100 Hz       $T_{amb}$  (°C)


Fig. 6 - Typical multiplier of ESR as a function of ambient temperature at different frequencies

**IMPEDANCE (Z)**


$Z_0$  = Impedance at 20 °C, 10 Hz

$T_{amb}$  (°C)

Fig. 7 - Typical multiplier of impedance as a function of ambient temperature



$T_{amb} = 20$  °C

Fig. 8 - Typical impedance as a function of frequency

**RIPPLE CURRENT AND USEFUL LIFE**
**Table 3**

<b>ENDURANCE TEST DURATION AND USEFUL LIFE</b>	
<b>ENDURANCE AT 105 °C (h)</b>	<b>USEFUL LIFE AT 105 °C (h)</b>
8000	20 000

**Note**

- Multiplier of useful life code: CCB886




Fig. 9 - Multiplier of useful life as a function of ambient temperature and ripple current load

**Table 4**

<b>MULTIPLIER OF RIPPLE CURRENT (<math>I_R</math>) AS A FUNCTION OF FREQUENCY</b>					
<b>FREQUENCY (Hz)</b>					
50	100	300	1000	3000	$\geq 10\,000$
<b><math>I_R</math> MULTIPLIER</b>					
0.22	0.30	0.49	0.72	0.89	1.00

**Note**

- Formula (1) should be used to calculate the actual ripple current at 10 kHz (see Fig. 9) when multiple frequencies are present. For an example of the values 100 Hz and 50 kHz:

$$I_A = \sqrt{\left(\frac{I(100 \text{ Hz})}{0.30}\right)^2 + \left(\frac{I(50 \text{ kHz})}{1.0}\right)^2} \quad (1)$$

**Table 5**

<b>TEST PROCEDURES AND REQUIREMENTS</b>			
<b>TEST</b>		<b>PROCEDURE</b> (quick reference)	<b>REQUIREMENTS</b>
<b>NAME OF TEST</b>	<b>REFERENCE</b>		
Endurance	IEC 60384-4 / EN 130300 subclause 4.13	$T_{amb} = 85^{\circ}C$ ; $U_R$ applied; 8000 h	$\Delta C/C: \pm 10\%$ $\tan \delta \leq 1.3 \times \text{spec. limit}$ $Z \leq 2 \times \text{spec. limit}$ $I_{L5} \leq \text{spec. limit}$
Useful life	CECC 30301 subclause 1.8.1	$T_{amb} = 85^{\circ}C$ ; $U_R$ and $I_R$ applied; 20 000 h	$\Delta C/C: \pm 30\%$ $\tan \delta \leq 3 \times \text{spec. limit}$ $Z \leq 3 \times \text{spec. limit}$ $I_{L5} \leq \text{spec. limit}$ No short or open circuit Total failure percentage: $\leq 3\%$
Shelf life (storage at high temperature)	IEC 60384-4 / EN 130300 subclause 4.17	$T_{amb} = 85^{\circ}C$ ; no voltage applied; 500 h  After test: $U_R$ to be applied for 30 min, 24 h to 48 h before measurement	$\Delta C/C, \tan \delta, Z$ : for requirements see "Endurance test" above $I_{L5} \leq 2 \times \text{spec. limit}$

Statements about product lifetime are based on calculations and internal testing. They should only be interpreted as estimations. Also due to external factors, the lifetime in the field application may deviate from the calculated lifetime. In general, nothing stated herein shall be construed as a guarantee of durability.

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.