





RECOMENDED HOLE LAYOUT
FOR BOTTOM ENTRY OR PASS
THROUGH APPLICATIONS


- 1 TE CONNECTIVITY LOGO AND CSA LOGO ARE MOLDED INTO THE HOUSING.
- 2 TOLERANCE NON-CUMULATIVE.
- 3 DUPLEX PLATED: 0.00076 (.000030) GOLD IN CONTACT AREA, .00381-.00762 (.000150-.000300) BRIGHT TIN-LEAD ON LEADS, ALL OVER 0.00127 (.000050) MIN NICKEL.
- 4 THESE DIMENSIONS PERTAIN TO CAVITY C/L'S ONLY, NOT TO CONTACT LOCATIONS.
- 5 NO PART NUMBER MARKING REQUIRED ON THIS PART NUMBER.
- 6 HOUSING: FLAME RETARDANT GLASS FILLED POLYESTER - BLACK.
CONTACTS: PHOS. BRONZE.
- 7 POINT OF CONTACT DIMENSION.
- 8 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE CONTACT BEAMS).
- 9 DUPLEX PLATED: 0.00076 (.000030) GOLD DUPLEX IN CONTACT AREA, 0.00381-0.00762 (.000150-.000300) MATTE TIN ON LEADS, ALL OVER 0.00127 (.000050) MIN NICKEL.
- 10 ROHS 2002/95/EC COMPLIANT
- 11 PART NUMBER AND DATE CODE ARE MARKED IN APPROXIMATE LOCATION SHOWN.
- 12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT - By -	ALL RIGHTS RESERVED.	

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

5	OBSOLETE	$\triangle_9$	1.300	1.200	26	$\triangle_{10}$	9-534236-1
	OBSOLETE	$\triangle_9$	4.000	3.900	80	$\triangle_{10}$	9-534236-0
		$\triangle_9$	3.900	3.800	78	$\triangle_{10}$	8-534236-9
		$\triangle_9$	3.800	3.700	76	$\triangle_{10}$	8-534236-8
		$\triangle_9$	3.700	3.600	74	$\triangle_{10}$	8-534236-7
		$\triangle_9$	3.600	3.500	72	$\triangle_{10}$	8-534236-6
		$\triangle_9$	3.500	3.400	70	$\triangle_{10}$	8-534236-5
		$\triangle_9$	3.400	3.300	68	$\triangle_{10}$	8-534236-4
		$\triangle_9$	3.300	3.200	66	$\triangle_{10}$	8-534236-3
		$\triangle_9$	3.200	3.100	64	$\triangle_{10}$	8-534236-2
		$\triangle_9$	3.100	3.000	62	$\triangle_{10}$	8-534236-1
		$\triangle_9$	3.000	2.900	60	$\triangle_{10}$	8-534236-0
		$\triangle_9$	2.900	2.800	58	$\triangle_{10}$	7-534236-9
		$\triangle_9$	2.800	2.700	56	$\triangle_{10}$	7-534236-8
		$\triangle_9$	2.700	2.600	54	$\triangle_{10}$	7-534236-7
		$\triangle_9$	2.600	2.500	52	$\triangle_{10}$	7-534236-6
		$\triangle_9$	2.500	2.400	50	$\triangle_{10}$	7-534236-5
		$\triangle_9$	2.400	2.300	48	$\triangle_{10}$	7-534236-4
		$\triangle_9$	2.300	2.200	46	$\triangle_{10}$	7-534236-3
		$\triangle_9$	2.200	2.100	44	$\triangle_{10}$	7-534236-2
		$\triangle_9$	2.100	2.000	42	$\triangle_{10}$	7-534236-1
		$\triangle_9$	2.000	1.900	40	$\triangle_{10}$	7-534236-0
		$\triangle_9$	1.900	1.800	38	$\triangle_{10}$	6-534236-9
		OBSOLETE	$\triangle_9$	1.800	1.700	36	$\triangle_{10}$
	$\triangle_9$	1.700	1.600	34	$\triangle_{10}$	6-534236-7	
	OBSOLETE	$\triangle_9$	1.600	1.500	32	$\triangle_{10}$	6-534236-6
	$\triangle_9$	1.500	1.400	30	$\triangle_{10}$	6-534236-5	
	OBSOLETE	$\triangle_9$	1.400	1.300	28	$\triangle_{10}$	6-534236-4
$\triangle_9$		1.300	1.200	26	$\triangle_{10}$	6-534236-3	
	$\triangle_9$	1.200	1.100	24	$\triangle_{10}$	6-534236-2	
	OBSOLETE	$\triangle_9$	1.100	1.000	22	$\triangle_{10}$	6-534236-1
	$\triangle_9$	1.000	.900	20	$\triangle_{10}$	6-534236-0	
	OBSOLETE	$\triangle_9$	.900	.800	18	$\triangle_{10}$	5-534236-9
$\triangle_9$		.800	.700	16	$\triangle_{10}$	5-534236-8	
$\triangle_9$		.700	.600	14	$\triangle_{10}$	5-534236-7	
$\triangle_9$		.600	.500	12	$\triangle_{10}$	5-534236-6	
	$\triangle_5$	$\triangle_9$	.500	.400	10	$\triangle_{10}$	5-534236-5
$\triangle_5$	OBSOLETE	$\triangle_9$	.400	.300	8	$\triangle_{10}$	5-534236-4
$\triangle_5$	OBSOLETE	$\triangle_9$	.300	.200	6	$\triangle_{10}$	5-534236-3
$\triangle_5$	OBSOLETE	$\triangle_9$	.200	.100	4	$\triangle_{10}$	5-534236-2
$\triangle_5$	OBSOLETE	$\triangle_9$	.100	-	2	$\triangle_{10}$	5-534236-1
		FINISH	A	B	NO OF POSN	PART NO.	

5	12	OBSOLETE		1.300	1.200	26	4-534236-1
		 OBSOLETE		4.000	3.900	80	4-534236-0
				3.900	3.800	78	3-534236-9
				3.800	3.700	76	3-534236-8
				3.700	3.600	74	3-534236-7
				3.600	3.500	72	3-534236-6
				3.500	3.400	70	3-534236-5
				3.400	3.300	68	3-534236-4
				3.300	3.200	66	3-534236-3
				3.200	3.100	64	3-534236-2
12	OBSOLETE			3.100	3.000	62	3-534236-1
				3.000	2.900	60	3-534236-0
	 OBSOLETE			2.900	2.800	58	2-534236-9
				2.800	2.700	56	2-534236-8
				2.700	2.600	54	2-534236-7
12	OBSOLETE			2.600	2.500	52	2-534236-6
				2.500	2.400	50	2-534236-5
				2.400	2.300	48	2-534236-4
12	OBSOLETE			2.300	2.200	46	2-534236-3
				2.200	2.100	44	2-534236-2
12	OBSOLETE			2.100	2.000	42	2-534236-1
				2.000	1.900	40	2-534236-0
				1.900	1.800	38	1-534236-9
12	OBSOLETE			1.800	1.700	36	1-534236-8
				1.700	1.600	34	1-534236-7
				1.600	1.500	32	1-534236-6
				1.500	1.400	30	1-534236-5
				1.400	1.300	28	1-534236-4
				1.300	1.200	26	1-534236-3
				1.200	1.100	24	1-534236-2
12	OBSOLETE			1.100	1.000	22	1-534236-1
				1.000	.900	20	1-534236-0
				.900	.800	18	534236-9
				.800	.700	16	534236-8
				.700	.600	14	534236-7
				.600	.500	12	534236-6
				.500	.400	10	534236-5
				.400	.300	8	534236-4
	 OBSOLETE			.300	.200	6	534236-3
				.200	.100	4	534236-2
				.100	-	2	534236-1
		FINISH	A	B	NO OF POSN	PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. BOLES 19-11-92 CHK T. KINSEY 19-11-92 APVD —		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME ASSEMBLY, MOD II DOUBLE ROW, .100 X .100 C/L, VERTICAL MOUNTED, CLOSED ENTRY, SHORT PT. CONTACTS	
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —			
MATERIAL 		FINISH 			
		PRODUCT SPEC 108-25026 APPLICATION SPEC 114-25018 WEIGHT —		SIZE A2	CAGE CODE 00779
				DRAWING NO C=534236	
				RESTRICTED TO —	
CUSTOMER DRAWING				SCALE	4:1
				SHEET	2 of 2
				REV	V2