

FCI CONFIDENTIAL



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.


PRODUCT NO	DIM L	DIM M	PLATING	RECOMMENDED P.C BOARD THICKNESS	PRODUCT NO	PLATING				
10031077-001LF	2.70	3.41	NOTE 2	1.57mm (0.062") / 2.36mm (0.093")	10031077-001	NOTE 5	HOLE	A	B	REMARK
10031077-011LF	3.70	3.41		2.36mm (0.093")	10031077-011		HOLE DIAMETER AFTER PLATING	0.45 - 0.55 mm	0.35 - 0.45 mm	FOR -XXX & -XXXLF
					SEE NOTE 5		DRILLED HOLE	0.58 - 0.62 mm	0.50 - 0.51 mm	
							COPPER PLATING	25 - 50 μm	25 - 50 μm	
							Sn PLATING	5 - 15 μm	5 - 15 μm	
							Sn-Pd PLATING	5 - 15 μm	5 - 15 μm	

15.875

5.08

4.96±0.05

0.10




TOLERANCES UNLESS OTHERWISE SPECIFIED			tolerance std	material	-	dr	GL L00	2004-09-23	projection		MM	size	A3	scale	3:1
linear	X.	±-		ISO 406	mat code	-	eng	GL L00				2004-09-23	ecn no	S10-0228	
	0.X	±-	ISO 1101	heattreat	-	chr	GL L00	2010-10-28	rel level			-			
	0.XX	±0.20	surface	plating/finish	-	appr	JOEY NG	2010-10-28	product family			SAS			
	0.XXX	±-		spec ref	-	FCi			SAS RECEPTACLE			dwg no	10031077	rev	E
0.XXXX	±-	ISO 1302	model name	10031077	www.fci.com			VERTICAL PF TYPE ASSY			Product - Customer Drw			sheet 1 of 2	
angular	0°		±2°	model revision											

FCI CONFIDENTIAL




This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

PRODUCT NO	DIM L	DIM M	PLATING	RECOMMENDED P.C BOARD THICKNESS
10031077-003LF	2.70	2.10	NOTE 2	1.57mm (0.062") / 2.36mm(0.093")



NOTE:
ALL OTHER DIMENSIONS, REFER TO SHEET 1.



NOTES:

- MATERIAL :
1) HOUSING : HIGH TEMP. THERMOPLASTIC, UL 94V-0
COLOR : BLACK
2) TERMINAL : COPPER ALLOY
3) HOLD DOWN : COPPER ALLOY
- FINISH : FOR XXXXXXXX-XXXLF
1) TERMINAL : 30μ" Au PLATING (CONTACT POINT) OVER 50μ" MIN NICKEL
2) SOLDER TAIL : 20μ" MIN - 60μ" MAX TIN OVER 50μ" MIN NICKEL
3) HOLD DOWN : 50μ" MIN TIN OVER 50μ" MIN NICKEL
- TRUE POSITION NOTES APPLY AT (L= 2.70mm) TERMINAL TIP
- PER SFF REV 1.1 EXCEPT 0.8mm PITCH BUMP AREA.
- FINISH : FOR XXXXXXXX-XXX
1) TERMINAL : 30μ" Au PLATING (CONTACT POINT) OVER 50μ" MIN NICKEL
2) SOLDER TAIL : 20μ" MIN -60μ" MAX TIN-LEAD OVER 50μ" MIN NICKEL
3) HOLD DOWN : 50μ" MIN TIN-LEAD OVER 50μ" MIN NICKEL
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- PART NUMBERS ENDING IN "LF" MEANS FOR NOTE 7 LEAD FREE IDENTIFICATION.
- NOTE 7 AND 8 DO NOT APPLY TO TIN LEAD PLATING P/N XXXXXXXX-XXX IN TABLE.
- THE STD PACKAGING IS IN TRAY
- A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

TOLERANCES UNLESS OTHERWISE SPECIFIED			tolerance std	material	-	dr	GL L00	2004-09-23			size	A3	scale	3:1							
linear	X.	±-		ISO 406	mat code	-	eng	GL L00			2004-09-23	ecn no	S10-0228								
	0.X	±-		ISO 1101	heattreat	-	chr	GL L00			2010-10-28	rel level -									
	0.XX	±0.20	surface 	plating/finish	-	appr	JOEY NG	2010-10-28	product family		SAS										
	0.XXX	±-		spec ref		-				title		SAS RECEPTACLE VERTICAL PF TYPE ASSY		dwg no		10031077C		rev		E	
	0.XXXX	±-		model name		10031077															
angular	0°	±2°	ISO 1302	model revision		www.fci.com		cat. no.		-		Product - Customer Drw			sheet 2 of 2						