

PDM: Rev:W STATUS Released Printed: Jul 05, 2007

PDM: Rev:X STATUS Released Printed: Apr 12, 2011



PDM: Rev:W STATUS Released Printed: Jul 05, 2007

PDM: Rev:X STATUS Released Printed: Apr 12, 2011

PRODUCT NO	SIZE	DIM A	DIM B	DIM C	DIM D	DIM E	DIM J	TERM TYPE	TERM PLATING	STYLE
• 65692-001	2X5	24.1/.95	18.3/.72	10.16/.400	19.81/.780	17.78/.700	2.67/.105	RD	.76µ/30µ"Au OVER 1.27/50µ"Ni	A
-002							3.8/.15	RD		
-003							17.15/.675	SQ		
-004							2.67/.105	SQ	3.81µ/150µ" TIN	
-005							3.8/.15	SQ		
-006	2X5	24.1/.95	18.3/.72	10.16/.400	19.81/.780	17.78/.700	17.15/.675	SQ		A
-007	2X10	36.8/1.45	30.9/1.22	22.86/.900	32.51/1.280	30.48/1.200	2.67/.105	RD	.76µ/30µ"Au OVER 1.27/50µ"Ni	D
-008							3.8/.15	RD		
-009							17.15/.675	SQ		
-010							2.67/.105	SQ	3.81µ/150µ" TIN	
-011							3.8/.15	SQ		
-012	2X10	36.8/1.45	30.9/1.22	22.86/.900	32.51/1.280	30.48/1.200	17.15/.675	SQ		
-013	2X13	44.5/1.75	38.6/1.52	30.48/1.200	40.13/1.580	38.10/1.500	2.67/.105	RD	.76µ/30µ"Au OVER 1.27/50µ"Ni	
-014							3.8/.15	RD		
-015							17.15/.675	SQ		
-016							2.67/.105	SQ	3.81µ/150µ" TIN	
-017							3.8/.15	SQ		
-018	2X13	44.5/1.75	38.6/1.52	30.48/1.200	40.13/1.580	38.10/1.500	17.15/.675	SQ		
-019	2X17	54.6/2.15	48.8/1.92	40.64/1.600	50.29/1.980	48.26/1.900	2.67/.105	RD	.76µ/30µ"Au OVER 1.27/50µ"Ni	
-020							3.8/.15	RD		
-021							17.15/.675	SQ		
-022							2.67/.105	SQ	3.81µ/150µ" TIN	
-023							3.8/.15	SQ		
-024	2X17	54.6/2.15	48.8/1.92	40.64/1.600	50.29/1.980	48.26/1.900	17.15/.675	SQ		
-025	2X20	62.2/2.45	56.4/2.22	48.26/1.900	57.91/2.280	55.88/2.200	2.67/.105	RD	.76µ/30µ"Au OVER 1.27/50µ"Ni	
-026							3.8/.15	RD		
-027							17.15/.675	SQ		
-028							2.67/.105	SQ	3.81µ/150µ" TIN	
-029							3.8/.15	SQ		
65692-030	2X20	62.2/2.45	56.4/2.22	48.26/1.900	57.91/2.280	55.88/2.200	17.15/.675	SQ		D

REV	DESCRIPTION	BY	DATE
A1			

CUSTOMER COPY

DOC IDENT 22526

www.fciconnect.com

DO NOT SCALE DRAWING

XXXXX

XXXXX

TITLE: HEADER, QUICKIE SLIM LINE, VERTICAL

SIZE D | DWG NO 65692 | REV 3 | SHEET 1/1

PDM: Rev:W STATUS Released Printed: Jul 05, 2007

PDM: Rev:X STATUS Released Printed: Apr 12, 2011

PRODUCT NO	SIZE	DIM A	DIM B	DIM C	DIM D	DIM E	DIM J	TERM TYPE	TERM PLATING	STYLE
65692-031	2X25	74.9/2.95	69.1/2.72	60.96/2.400	70.61/2.780	68.58/2.700	2.67/.105	RD	.76µm/30µ"Au OVER 1.27µm/50µ"Ni	D
-032							3.8/.15	RD		
-033							17.15/.675	SQ		
-034							2.67/.105	SQ	3.81µ/150µ" TIN	
-035							3.8/.15	SQ		
-036	2X25	74.9/2.95	69.1/2.72	60.96/2.400	70.61/2.780	68.58/2.700	17.15/.675	SQ		D
-037	2X7	29.2/1.15	23.4/.92	15.24/.600	24.89/.980	22.86/.900	2.67/.105	RD	.76µm/30µ"Au OVER 1.27µm/50µ"Ni	C
-038							3.8/.15	RD		
-039							17.15/.675	SQ		
-040							2.67/.105	SQ	3.81µ/150µ" TIN	
-041							3.8/.15	SQ		
-042	2X7	29.2/1.15	23.4/.92	15.24/.600	24.89/.980	22.86/.900	17.15/.675	SQ		C
-043	2X8	31.8/1.25	25.9/1.02	17.78/.700	27.43/1.080	25.40/1.000	2.67/.105	RD	.76µm/30µ"Au OVER 1.27µm/50µ"Ni	D
-044							3.8/.15	RD		
-045							17.15/.675	SQ		
-046							2.67/.105	SQ	3.81µ/150µ" TIN	
-047							3.8/.15	SQ		
-048	2X8	31.8/1.25	25.9/1.02	17.78/.700	27.43/1.080	25.40/1.000	17.15/.675	SQ		D
-049	2X5	24.1/.95	18.3/.72	10.16/.400	19.81/.780	17.78/.700	3.8/.15	RD		A
-050	2X10	36.8/1.45	30.9/1.22	22.86/.900	32.51/1.280	30.48/1.200				D
-051	2X13	44.5/1.75	38.6/1.52	30.48/1.200	40.12/1.580	38.10/1.500				
-052	2X17	84.6/3.15	48.8/1.92	40.64/1.600	50.29/1.980	43.26/1.900				
-053	2X20	62.3/2.45	56.4/2.22	48.26/1.900	57.91/2.280	55.88/2.200			.76µm/30µ" GXT/GOLD FLASH	
-054	2X25	74.9/2.95	69.1/2.72	60.96/2.400	70.61/2.780	68.58/2.700				D
-055	2X7	29.2/1.15	23.4/.92	15.24/.600	24.89/.980	22.86/.900				C
-056	2X8	31.8/1.25	25.9/1.02	17.78/.700	27.43/1.080	25.40/1.000	3.8/.15	RD		D
-057	2X30	87.6/3.45	81.8/3.22	73.66/2.900	83.31/3.280	81.28/3.200	2.67/.105	RD	.76µm/30µ"Au OVER 1.27µm/50µ"Ni	
-058							3.8/.15	RD		
-059							17.15/.675	SQ		
-060							2.67/.105	SQ	3.81µ/150µ" TIN	
-061							3.8/.15	SQ		
-062							17.15/.675	SQ		
-063							2.67/.105	RD	.76µm/30µ" GXT/GOLD FLASH	
-064							3.8/.15	RD		
65692-065	2X30	87.6/3.45	81.8/3.22	73.66/2.900	83.31/3.280	81.28/3.200	17.15/.675	SQ		D

REVISIONS			
REV	DESCRIPTION	BY	DATE
A1			

CUSTOMER COPY

CODE IDENT 28520

www.fciconnect.com

DO NOT SCALE DRAWING

XXXX

TOLERANCES UNLESS OTHERWISE SPECIFIED: LINEAR 0.0±0.25/.00±.01; 0.00±0.13/.000±.005; 0.000±0.051/.0000±.002; ANGLES ±1°0'

XXXXXX

XXXXXX

D. SHAFFER 1/15/08

D. FROST 1/15/08

D. FROST 1/15/08

D. FROST 1/15/08

TITLE HEADER, QUICKIE SLIM LINE, VERTICAL

SIZE D

DWG NO 65692

REV A1

SHEET 4

THIS DRAWING IS THE PROPERTY OF AND CONTAINS PROPRIETARY DESIGNS OF THE FCI GROUP OF COMPANIES. NO PART OF THIS DRAWING SHALL BE USED FOR ANY USE WITHOUT THE EXPRESS CONSENT OF FCI GROUP OF COMPANIES, THE CONNECTOR, ITS

PDM: Rev:W STATUS Released Printed: Jul 05, 2007

PDM: Rev:X STATUS Released Printed: Apr 12, 2011

PRODUCT NO	SIZE	DIM A	DIM B	DIM C	DIM D	DIM E	DIM J	TERM TYPE	TERM PLATING	STYLE
65692-066	2X5	24.1/.95	18.3/.72	10.16/.400	19.81/.780	17.78/.700	2.67/.105	RD	.76µ/30µ" GXT/GOLD FLASH	A
-067	2X5	24.1/.95	18.3/.72	10.16/.400	19.81/.780	17.78/.700	17.15/.675	SQ		A
-068	2X7	29.2/1.15	23.4/.92	15.24/.600	24.89/.980	22.86/.900	2.67/.105	RD		C
-069	2X7	29.2/1.15	23.4/.92	15.24/.600	24.89/.980	22.86/.900	17.15/.675	SQ		C
-070	2X8	31.8/1.25	25.9/1.02	17.78/.700	27.43/1.080	25.40/1.000	2.67/.105	RD		D
-071	2X8	31.8/1.25	25.9/1.02	17.78/.700	27.43/1.080	25.40/1.000	17.15/.675	SQ		
-072	2X10	36.8/1.45	30.9/1.22	22.86/.900	32.51/1.280	30.48/1.200	2.67/.105	RD		
-073	2X10	36.8/1.45	30.9/1.22	22.86/.900	32.51/1.280	30.48/1.200	17.15/.675	SQ		
-074	2X13	44.5/1.75	38.6/1.52	30.48/1.200	40.12/1.580	38.10/1.500	2.67/.105	RD		
-075	2X13	44.5/1.75	38.6/1.52	30.48/1.200	40.12/1.580	38.10/1.500	17.15/.675	SQ		
-076	2X17	54.6/2.15	48.8/1.92	40.64/1.600	50.29/1.980	48.26/1.900	2.67/.105	RD		
-077	2X17	54.6/2.15	48.8/1.92	40.64/1.600	50.29/1.980	48.26/1.900	17.15/.675	SQ		
-078	2X20	62.2/2.45	56.4/2.22	48.26/1.900	57.91/2.280	55.88/2.200	2.67/.105	RD		
-079	2X20	62.2/2.45	56.4/2.22	48.26/1.900	57.91/2.280	55.88/2.200	17.15/.675	SQ		
-080	2X25	74.9/2.95	69.1/2.72	60.96/2.400	70.61/2.780	68.58/2.700	2.67/.105	RD		
-081	2X25	74.9/2.95	69.1/2.72	60.96/2.400	70.61/2.780	68.58/2.700	17.15/.675	SQ		D
-082	2X5	24.1/.95	18.3/.72	10.16/.400	19.81/.780	17.78/.700	2.67/.105	RD	.38µ/15µ"Au OVER 1.27µ/50µ"Ni	A
-083	2X5	24.1/.95	18.3/.72	10.16/.400	19.81/.780	17.78/.700	3.8/.15	RD		A
-084	2X5	24.1/.95	18.3/.72	10.16/.400	19.81/.780	17.78/.700	17.15/.675	SQ		A
-085	2X7	29.2/1.15	23.4/.92	15.24/.600	24.89/.980	22.86/.900	2.67/.105	RD		C
-086	2X7	29.2/1.15	23.4/.92	15.24/.600	24.89/.980	22.86/.900	3.8/.15	RD		C
-087	2X7	29.2/1.15	23.4/.92	15.24/.600	24.89/.980	22.86/.900	17.15/.675	SQ		C
-088	2X8	31.8/1.25	25.9/1.02	17.78/.700	27.43/1.080	25.40/1.000	2.67/.105	RD		D
-089	2X8	31.8/1.25	25.9/1.02	17.78/.700	27.43/1.080	25.40/1.000	3.8/.15	RD		
-090	2X8	31.8/1.25	25.9/1.02	17.78/.700	27.43/1.080	25.40/1.000	17.15/.675	SQ		
-091	2X10	36.8/1.45	30.9/1.22	22.86/.900	32.51/1.280	30.48/1.200	2.67/.105	RD		
-092	2X10	36.8/1.45	30.9/1.22	22.86/.900	32.51/1.280	30.48/1.200	3.8/.15	RD		
-093	2X10	36.8/1.45	30.9/1.22	22.86/.900	32.51/1.280	30.48/1.200	17.15/.675	SQ		
-094	2X13	44.5/1.75	38.6/1.52	30.48/1.200	40.12/1.580	38.10/1.500	2.67/.105	RD		
-095	2X13	44.5/1.75	38.6/1.52	30.48/1.200	40.12/1.580	38.10/1.500	3.8/.15	RD		
-096	2X13	44.5/1.75	38.6/1.52	30.48/1.200	40.12/1.580	38.10/1.500	17.15/.675	SQ		
-097	2X17	54.6/2.15	48.8/1.92	40.64/1.600	50.29/1.980	48.26/1.900	2.67/.105	RD		
-098	2X17	54.6/2.15	48.8/1.92	40.64/1.600	50.29/1.980	48.26/1.900	3.8/.15	RD		
-099	2X17	54.6/2.15	48.8/1.92	40.64/1.600	50.29/1.980	48.26/1.900	17.15/.675	SQ		
65692-100	2X20	62.2/2.45	56.4/2.22	48.26/1.900	57.91/2.280	55.88/2.200	2.67/.105	RD		D

REVISIONS			
REV	DESCRIPTION	BY	DATE
A			

CUSTOMER COPY

CODE IDENT 28884

www.fciconnect.com

TITLE: HEADER, QUICKIE SLIM LINE, VERTICAL

SIZE D | DWG NO 65692 | SHEET 5

SHEET SIZE D | SHEET NO 1 | ISSUE A

MODEL XXXX

DO NOT SCALE DRAWING

TOLERANCES UNLESS OTHERWISE SPECIFIED: LINEAR 0.000 ±0.25/.00± .01; 0.0000 ±0.13/.000± .005; 0.00000 ±0.051/.0000± .0020; ANGLES ±2°0'

MATL XXXXXX | FINISH XXXXXX

APP R.SHAFFER 1/6/06 | CHK R.FROST 1/6/06 | DRN R.FROST 1/6/06 | ENG R.FROST 1/6/06

TABULATION SHEETS REQUIRED: YES / NO

SCALE 1/1 | SIZE D | DWG NO 65692 | REV A | SHEET 5

THIS DRAWING IS THE PROPERTY OF FCI ELECTRONICS (SINGAPORE) PTE LTD. IT IS NOT TO BE COPIED OR REPRODUCED IN ANY FORM OR MEDIUM, DISCLOSED TO OTHERS OR USED FOR MANUFACTURE OR SALE OF EQUIPMENT OR DEVICES WITHOUT OUR PRIOR WRITTEN CONSENT. ANY SUCH USE OR DISCLOSURE WITHOUT OUR PRIOR WRITTEN CONSENT IS EXPRESSLY FORBIDDEN. ALL RIGHTS RESERVED.

PDM: Rev:W STATUS Released Printed: Jul 05, 2007

PDM: Rev:X STATUS Released Printed: Apr 12, 2011

PRODUCT NO	SIZE	DIM A	DIM B	DIM C	DIM D	DIM E	DIM J	TERM TYPE	TERM PLATING	STYLE
65692-101	2X20	62.2/2.45	56.4/2.22	48.26/1.900	57.91/2.280	55.88/2.200	3.8/.15	RD	.38µm/15µ"Au OVER 1.27µm/50µ"Ni	D
-102	2X20	62.2/2.45	56.4/2.22	48.26/1.900	57.91/2.280	55.88/2.200	17.15/.675	SQ		
-103	2X25	74.9/2.95	69.1/2.72	60.96/2.400	70.61/2.780	68.58/2.700	2.67/.105	RD		
-104	2X25	74.9/2.95	69.1/2.72	60.96/2.400	70.61/2.780	68.58/2.700	3.8/.15	RD		
-105	2X25	74.9/2.95	69.1/2.72	60.96/2.400	70.61/2.780	68.58/2.700	17.15/.675	SQ		
-106	2X30	87.6/3.45	81.8/3.22	73.66/2.900	83.31/3.280	81.28/3.200	2.67/.105	RD		
-107	2X30	87.6/3.45	81.8/3.22	73.66/2.900	83.31/3.280	81.28/3.200	3.8/.15	RD		
-108	2X30	87.6/3.45	81.8/3.22	73.66/2.900	83.31/3.280	81.28/3.200	17.15/.675	SQ		D
-109	2X5	24.1/.95	18.3/.72	10.16/.400	19.81/.780	17.78/.700	2.67/.105	RD	.76µm/30µ"Au OVER 1.27µm/50µ"Ni	B
-110							3.8/.15	RD		
-111							17.15/.675	SQ		
-112							2.67/.105	SQ	3.81µm/150µ" TIN	
-113							3.8/.15	SQ		
-114							17.15/.675	SQ		
-115							2.67/.105	RD	.38µm/15µ"Au OVER 1.27µm/50µ"Ni	
-116							3.8/.15	RD		
-117							17.15/.675	SQ		
-118							2.67/.105	RD	.76µm/30µ" GXT/GOLD FLASH	
-119							3.8/.15	RD		
65692-120	2X8	24.1/.95	18.3/.72	10.16/.400	19.81/.780	17.78/.700	17.15/.675	SQ		B
65692-121	OBSOLETE									
65692-216										
65692-217	2X12	41.9/1.65	36.1/1.42	27.94/1.100	37.59/1.480	35.56/1.400	2.67/.105	RD	.38µm/15µ"Au OVER 1.27µm/50µ"Ni	D
-218							3.81/.150	RD		
-219							17.15/.675	SQ		
-220							2.67/.105	RD	.76µm/30µ"Au OVER 1.27µm/50µ"Ni	
-221							3.81/.150	RD		
-222							17.15/.675	SQ		
-223							2.67/.105	RD	.76µm/30µ" GXT/Au FLASH	
-224							3.81/.150	RD		
-225							17.15/.675	SQ		
-226							2.67/.105	SQ	3.81µm/150µ" TIN	
-227							3.81/.150	SQ		
65692-228	2X12	41.9/1.65	36.1/1.42	27.94/1.100	37.59/1.480	35.56/1.400	17.15/.675	SQ		D

REVISIONS

REV	DESCRIPTION	BY	DATE
SL			

CUSTOMER COPY

CODE IDENT 22535

www.fciconnect.com

TITLE HEADER, QUICKIE SLIM LINE, VERTICAL

SCALE	SIZE	DWG NO	REV
1/1	D	65692	

SHEET 6

PDM: Rev:W STATUS Released Printed: Jul 05, 2007

PDM: Rev:X STATUS Released Printed: Apr 12, 2011

PRODUCT NO	SIZE	DIM A	DIM B	DIM C	DIM D	DIM E	DIM J	TERM TYPE	TERM PLATING	STYLE
65692-229	2X15	49.5/1.95	43.7/1.72	35.56/1.400	45.21/1.780	43.18/1.700	2.67/.105	RD	.38µm/15µ"Au OVER 1.27µm/50µ"Ni	D
-230							3.81/.150	RD		
-231							17.15/.675	SQ		
-232							2.67/.105	RD	.76µm/30µ"Au OVER 1.27µm/50µ"Ni	
-233							3.81/.150	RD		
-234							17.15/.675	SQ		
-235							2.67/.105	RD	.76µm/30µ" GXT/Au FLASH	
-236							3.81/.150	RD		
-237							17.15/.675	SQ		
-238							2.67/.105	SQ	3.81µm/150µ" TIN	
-239							3.81/.150	SQ		
-240	2X15	49.5/1.95	43.7/1.72	35.56/1.400	45.21/1.780	43.18/1.700	17.15/.675	SQ		
-241	2X22	67.3/2.65	61.5/2.42	53.34/2.100	62.99/2.480	60.96/2.400	2.67/.105	RD	.38µm/15µ"Au OVER 1.27µm/50µ"Ni	
-242							3.81/.150	RD		
-243							17.15/.675	SQ		
-244							2.67/.105	RD	.76µm/30µ"Au OVER 1.27µm/50µ"Ni	
-245							3.81/.150	RD		
-246							17.15/.675	SQ		
-247							2.67/.105	RD	.76µm/30µ" GXT/Au FLASH	
-248							3.81/.150	RD		
-249							17.15/.675	SQ		
-250							2.67/.105	SQ	3.81µm/150µ" TIN	
-251							3.81/.150	SQ		
-252	2X22	67.3/2.65	61.5/2.42	53.34/2.100	62.99/2.480	60.96/2.400	17.15/.675	SQ		D
-253	2X5	24.1/.95	18.3/.72	10.16/.400	19.81/.780	17.78/.700	2.67/.105	SQ	.76µm/30µ"Au OVER 1.27µm/50µ"Ni	A
-254	2X10	36.8/1.45	30.9/1.22	22.86/.900	32.51/1.280	30.48/1.200	2.67/.105	SQ		D
-255	2X17	54.6/2.15	48.8/1.92	40.64/1.600	50.29/1.980	48.26/1.900	2.67/.105	SQ		D
-256	2X5									
-257	2X10									
-258	2X20									
-259	2X10									
-260	2X17									
-261	2X20									
-262	2X17									
65692-263	2X5									

CUSTOMER RESTRICTED

CUSTOMER RESTRICTED

REV	DESCRIPTION	BY	DATE
W			

CUSTOMER COPY

CODE IDENT 52984

www.fciconnect.com

TITLE HEADER, QUICKIE SLIM LINE, VERTICAL

SIZE D | DWG NO 65692 | REV W | SHEET 7

MODEL XXXX

DO NOT SCALE DRAWING

MATL XXXXXX | FINISH XXXXXX

DR B.SHAFFER 1/6/98 | CH'K R.FRONT 1/6/98 | APP'D R.FRONT 1/6/98

ANGLES ±2°

PDM: Rev:W STATUS Released Printed: Jul 05, 2007

PDM: Rev:X STATUS Released Printed: Apr 12, 2011



PRODUCT NO	SIZE	DIM A	DIM B	DIM C	DIM D	DIM E	DIM J	TERM TYPE	TERM PLATING	STYLE
65692-264	2X5	CUSTOMER RESTRICTED								
65692-265	2X13									

REVISIONS			
REV	DESCRIPTION	BY	DATE
W			

TITLE	HEADER, QUICKIE SLIM LINE, VERTICAL
SIZE	D
DWG NO	65692
SHEET	1 OF 1

PDM: Rev:W STATUS Released Printed: Jul 05, 2007

PDM: Rev:X STATUS Released Printed: Apr 12, 2011