


Digital Storage Oscilloscope



Features

- Analog channels and 2GSPS real-time sampling rate
- Dual time base function; unrivaled waveform detail observation and analysis capabilities
- 3½ digital multimeter
- Supports plug-and-play USB storage devices and capable of communicating with a computer
- USB drive system software upgrade
- Built-in FFT and Multiple waveform mathematics functions (including add, subtract, multiply and divide)
- Edge, Video, Pulse, Slop and Alternate trigger functions

Specifications

Channels	: 4
Bandwidth	: 300MHz
Sample Rate	: 2GSPS
Rise Time	: $\leq 1.2\text{ns}$
Memory Depth	: 24kpts
Vertical Sensitivity	: 2mV/div to 5V/div
Timebase Range	: 1ns/div to 50s/div
Storage	: Setup, Wave, Bitmap, CSV
Trigger Modes	: Edge, Pulse, Video, Slope, Alternate
Interface	: USB Device, USB Host, Multimeter Interface

Multimeter Specifications

	Range	Best Accuracy
DC Voltage (V)	400mV, 4V, 40V, 400V	$\pm(1\% + 5)$
AC Voltage (V)	4V, 40V, 400V	$\pm(1.2\% + 5)$
DC Current (A)	4mA, 40mA, 400mA, 4A	$\pm(1\% + 5)$, 4A : $\pm(1.5\% + 5)$
Resistance (Ω)	400 Ω , 4k Ω , 40k Ω , 400k Ω , 4M Ω , 40M Ω	$\pm(1.5\% + 5)$
Display Count	4,000	
Auto Range	$\sqrt$	

Digital Storage Oscilloscope



General Characteristic

Power	: 100 - 240V AC, 45 - 440Hz
Display	: 5.7 Inches 64K Colour TFT LCD, 320 × 240
Product Colour	: White and Grey
Product Net Weight	: 3.8 kg
Product Size	: 330mm × 165mm × 165mm
Standard Accessories	: Probex4 (1×,10× switchable), Current-to-Voltage Converter Module, Test Leads, Power Cord, USB Cable, PC Software CD
Safety Rating	: CAT II 300V

Part Number Table

Description	Part Number
Oscilloscope, 4CH, 300MHz, 2GSPS	72-7630

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

