



HHR150AA Cylindrical AA size (HR15/51)

S type


■ Dimensions (with tube) (mm)



■ Typical charge characteristics



■ Typical discharge characteristics



■ Specifications


Diameter	14.5+0 / -0.7mm
Height	50.0+0 / -1.0mm
Approximate Weight	26g

Nominal Voltage		1.2V	
Discharge Capacity ^{*1}	Average ^{*2}	1580mAh	
	Rated (min.)	1500mAh	
Approx. Internal impedance at 1000Hz at charged state.		23m Ω	
Charge		Standard	150mA X 16hrs.
		Rapid	1500mA X 1.2hrs.
Ambient Temperature	Charge	Standard	0℃ to 45℃
		Rapid	0℃ to 40℃
	Discharge		-10℃ to 65℃
	Storage	<1 year	-20℃ to 35℃
		<3 months	-20℃ to 45℃
		<1 month	-20℃ to 55℃

*1 After charging at 0.1It for 16 hours, discharging at 0.2It.

*2 For reference only.

Battery performance and cycle life are strongly affected by how they are used. In order to maximize battery safety, please consult Panasonic when determining charge/discharge specs, warning label contents and unit design.



*The data in this document are for descriptive purposes only and are not intended to make or imply any guarantee or warranty.