



Series: **YFS / YFT** .050" (1,27 mm) SamArray<sup>®</sup> Low Profile Open Pin Field Array Socket / Terminal

**YFS Series – Socket**



**YFT Series – Terminal**



**Other configurations available for:**

YFW - for 7mm, 9mm, 12mm, 19mm, and 25mm Mated Stack Height with YFS

See [www.samtec.com](http://www.samtec.com) for more information.

**Series:** YFS / YFT .050" (1,27 mm) SamArray® Low Profile Open Pin Field Array Socket / Terminal

## 1.0 SCOPE

1.1 This specification covers performance, testing and quality requirements for Samtec's YFS/YFT Series .050" (1,27mm) SamArray® Low Profile Open Pin Field Array Connectors. All information contained in this specification is for a 5,00 mm (.197") mated stack height configuration unless otherwise noted.

## 2.0 DETAILED INFORMATION

2.1 Product prints, footprints, catalog pages, test reports and other specific, detailed information can be found at [www.samtec.com?YFS](http://www.samtec.com?YFS) and [www.samtec.com?YFT](http://www.samtec.com?YFT).

## 3.0 TESTING

3.1 **Current Rating:** 1.5A (32 Pins Powered)

3.2 **Voltage Rating:** 275 VAC

3.3 **Operating Temperature Range:** -55°C to +125°C

3.4 **Operating Humidity Range:** 90% to 95% (Per EIA-364-31)

3.5 **Electrical:**

ITEM	TEST CONDITION	REQUIREMENT	STATUS
Withstanding Voltage	EIA-364-20 (No Flashover, Sparkover, or Breakdown)	825 VAC	Pass
Insulation Resistance	EIA-364-21 (1000 MΩ minimum)	5,000 MΩ	Pass
Contact Resistance (LLCR)	EIA-364-23	Δ 15 mΩ maximum (Samtec defined)/ No damage	Pass

3.6 **Mechanical:**

ITEM	TEST CONDITION	REQUIREMENT	STATUS
Durability	EIA-364-09C	200 cycles	Pass
Random Vibration	EIA-364-28 Condition V, Letter B 7.56 G 'RMS', 50 to 2000 Hz, 2 hours per axis, 3 axis total, PSD 0.04	Visual Inspection: No Damage LLCR: Δ 15 mΩ maximum	Pass
Mechanical Shock	EIA-364-27 100 G, 6 milliseconds, sawtooth wave, 11.3 fps, 3 shocks/direction, 3 axis (18 total shocks)	Visual Inspection: No Damage LLCR: Δ 15 mΩ maximum	Pass
Normal Force	EIA-364-04	30 grams minimum for gold interface	Pass

Series: **YFS / YFT** .050" (1,27 mm) SamArray<sup>®</sup> Low Profile Open Pin Field Array Socket / Terminal

**3.7 Environmental:**

ITEM	TEST CONDITION	REQUIREMENT	STATUS
Thermal Shock	EIA-364-32 Thermal Cycles: 100 (30 minute dwell) Hot Temp: +85°C Cold Temp: -55°C Hot/Cold Transition: Immediate	Visual Inspection: No Damage LLCR: $\Delta$ 15 m $\Omega$ DWV: 825 VAC IR: >5,000 M $\Omega$	Pass
Thermal Aging (Temp Life)	EIA-364-17 Test Condition 4 @ 105°C Condition B for 250 hours	Visual Inspection: No Damage LLCR: $\Delta$ 15 m $\Omega$ DWV: 825 VAC IR: >5,000 M $\Omega$	Pass
Cyclic Humidity	EIA-364-31 Test Temp: +25°C to +65°C Relative Humidity: 90 to 95% Test Duration: 240 hours	Visual Inspection: No Damage LLCR: $\Delta$ 15 m $\Omega$ DWV: 825 VAC IR: >5,000 M $\Omega$	Pass
Gas Tight	EIA-364-36 Gas Exposure: Nitric Acid Vapor Duration: 60 min. Drying Temp.: 50°C +/- 3°C Measurements: Within 1 hour of Exposure	LLCR: $\Delta$ 15 m $\Omega$	Pass


Series: **YFS / YFT** .050" (1,27 mm) SamArray® Low Profile Open Pin Field Array Socket / Terminal

#### 4.0 MATED SYSTEM

Mated view information can be found at link below:

<http://www.samtec.com/documents/webfiles/cpdf/YFX%20Mated%20Document-MKT.pdf>

#### 5.0 POLARIZING FEATURES



#### 6.0 HIGH SPEED PERFORMANCE

6.1 Based on a 3 dB insertion loss

	Single-Ended: 1:1 S/G	Single-Ended: 2:1 S/G	Differential: Optimal Horizontal	Differential: Optimal Vertical	Differential: High Density Vertical
5mm Stack Height	20 GHz / 40 Gbps	14 GHz / 28 Gbps	13 GHz / 26 Gbps	20 GHz / 40 Gbps	13 GHz / 26 Gbps


6.2 System Impedance: 50 ohm for single-ended and 100 ohm for differential pair

Series: YFS / YFT .050" (1,27 mm) SamArray® Low Profile Open Pin Field Array Socket / Terminal

7.0 PROCESSING RECOMMENDATIONS

7.1 Mating Alignment Requirements:

7.1.1 Maximum guidance/capture in applications where at least one half of the interface is free to float.




7.1.2 The parts can be rigidly misaligned by no more than .004" (0,10 mm) in the X- and .004" (0,10 mm) in the Y- direction to ensure a good mate.




Series: YFS / YFT .050" (1,27 mm) SamArray® Low Profile Open Pin Field Array Socket / Terminal

7.2 Mating Angle Requirements: The connector can be zippered in the longitudinal and lateral direction.



7.2.1



7.2.2


**Series:** YFS / YFT .050" (1,27 mm) SamArray® Low Profile Open Pin Field Array Socket / Terminal

7.3 Due to variances in equipment, solder pastes and applications (board design, component density, etc.), Samtec does not specify a recommended reflow profile for our connectors. The processing parameters provided by the solder paste manufacturer should be employed and can usually be found on their website.

**Samtec Recommended Temperature Profile Ranges (SMT)**

**Sn-Pb Eutectic Assembly**

Preheat/Soak (100°C-150°C)	Max Ramp Up Rate	Reflow Time (above 183°C)	Peak Temp	Time within 5°C of 235°C	Max Ramp Down Rate	Time 25°C to Peak Temp
60-120 sec.	3°C/s max.	40-150 sec.	235°C	20 sec. max.	6°C/s max.	6 min. max.



7.3.1

These guidelines should not be considered design requirements for all applications. Samtec recommends testing interconnects on your boards in your process to guarantee optimum results.

**7.4 Maximum Reflow Passes:** The parts can withstand three reflow passes at a maximum component temperature of 240°C.

**7.5 Stencil Thickness:** The stencil thickness is .006" (0,15mm).

**7.6 Placement:** Machine placement and complete seating of the parts in the Z-axis is strongly recommended.

**Series:** [YFS / YFT](#) .050" (1,27 mm) SamArray<sup>®</sup> Low Profile Open Pin Field Array Socket / Terminal

**7.7 Hardware:** Board-to-board standoffs are recommended to provide a robust mechanical connection. Samtec offers two different types:

**7.7.1 Traditional Standoffs (SO)** – Rigid design to statically support board-to-board applications. See options here: [SO - Board Stacking Standoff](#)

**7.7.2 Jack Screw Standoffs (JSO)** – Serve same function as traditional standoffs but unique, nested construction facilitates the mating and unmating process. This is especially helpful for multiple connector applications where the mating and unmating forces increase with the number of connectors used. See options here: [JSO - Jack Screw Standoffs](#)

**7.8 Reflow Environment:** Samtec recommends the use of a low level oxygen environment (typically achieved through nitrogen gas infusion) in the reflow process to improve solderability.

**7.9 Cleaning:** Samtec, Inc. has verified that our connectors may be cleaned in accordance with the solvents and conditions designated in the EIA-364-11A standard.

**7.10 Rework Guidelines:** Samtec recommends following these rework guidelines as needed: [Reworking Grid Array Connectors](#)

**7.10.1** Samtec recommends a minimum spacing of .125" (3,18mm) between adjacent connectors to allow adequate room for hot-air rework equipment.

## 8.0 ADDITIONAL RESOURCES

**8.1** For additional mechanical testing or product information, contact our Customer Engineering Support Group at [CES@samtec.com](mailto:CES@samtec.com)

**8.2** For additional information on high speed performance testing, contact our Signal Integrity Group at [SIG@samtec.com](mailto:SIG@samtec.com)

**8.3** For additional processing information, contact our Interconnect Processing Group at [IPG@samtec.com](mailto:IPG@samtec.com).

**8.4** For RoHS, REACH or other environmental compliance information, contact our Product Environmental Compliance Group at [PEC@samtec.com](mailto:PEC@samtec.com)

### USE OF PRODUCT SPECIFICATION SHEET

This Product Specification Sheet ("PSS") is a brief summary of information related to the Product identified. As a summary, it should only be used for the limited purpose of considering the purchase/use of Product. For specific, detailed information, including but not limited to testing and Product footprint, refer to Section 2.0 of this document and the links there provided to test reports and prints. This PSS is the property of Samtec, Inc. ("Samtec") and contains proprietary information of Samtec, our various licensors, or both. Samtec does not grant express or implied rights or license under any patent, copyright, trademark or other proprietary rights and the use of the PSS for building, reverse engineering or replication is strictly prohibited. By using the PSS, the user agrees to not infringe, directly or indirectly, upon any intellectual property rights of Samtec and acknowledges that Samtec, our various licensors, or both own all intellectual property therein. The PSS is presented "AS IS". While Samtec makes every effort to present excellent information, the PSS is only provided as a guideline and does not, therefore, warrant it is without error or defect or that the PSS contains all necessary and/or relevant information about the Product. The user agrees that all access and use of the PSS is at its own risk. **NO WARRANTIES EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR OF ANY KIND WHATSOEVER ARE PROVIDED.**